


DO NOT SCALE

DIMENSIONS IN mm

METRIC

THIRD ANGLE

PROJECTION



WIRE RANGE :


0,3-0,6 mm²

22-20AWG


INSULATION RANGE :

1,3-2,0 DIA .050-.080 DIA


0,5 MAX.



3,7



0,25



2,2

5,5

0,96

FOR 0,8 TAB-THK.

NOTE:

⚠ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

TINPLATED	PH. BRONZE		160173-7
UNPLATED	PH. BRONZE		160173-6
GOLDPLATED	BRASS	⚠	160173-5
NICKELPLATED	BRASS		160173-4
SILVERPLATED	BRASS	⚠	160173-3
TINPLATED	BRASS		160173-2
UNPLATED	BRASS		160173-1
FINISH		MATERIAL	PARTNUMBER

—	—	—	—	—
—	—	—	—	—
—	—	—	—	—
—	—	—	—	—
—	—	—	—	—
D1	ECO-10-000443	KK	HMR	18JAN10
D	EH-0065-95	DK	PB	18 JAN 95
LTR.	REVISION RECORD	DR.	CHK.	DATE

CUSTOMER DRAWING

FOR REFERENCE ONLY
WILL NOT BE UPDATED

© COPYRIGHT 19 — BY AMP HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE
COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.
THIS DRAWING IS UNPUBLISHED
RELEASED FOR PUBLICATION —, 19 —

AMPAMP HOLLAND B.V.
's-Hertogenbosch,
The Netherlands.

NAME

.110 SRS FASTIN-ON
RECEPTACLE

DR.: D.KESSLER	CHK.: P.BEIJNON	APP.: L.v.SOEST
DATE: 18 JAN 95	DATE: —	DATE: —

DWG.No. C- 160173	REV.LTR. D1	SHEET 1 OF 1	A4
----------------------	----------------	-----------------	----