

Printed-circuit board connector - DFK-MSTB 2,5/ 5-G WW(1X1) - 0708140

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Header, Nominal current: 12 A, Number of positions: 5, Pitch: 5 mm, Connection method: Solder/
Slip-on connection, Color: green, Contact surface: Tin

Product description

Header, Nominal current: 12 A, Number of positions: 5, Pitch: 5 mm, Connection method: Solder/Slip-on connection, Color: green, Contact surface: Tin

Key commercial data

Packing unit	1
Minimum order quantity	50
GTIN	 4 017918 004460
Weight per piece (including packing)	0.0 GRM
Weight per Piece (excluding packing)	5.2 GRM
Country of origin	GERMANY

Technical data

Dimensions / positions

Pitch	5 mm
Dimension a	20 mm
Number of positions	5

Technical data

Range of articles	DFK-MSTB 2,5/..-G
Connection in acc. with standard	EN-VDE
Nominal current IN	12 A
Nominal voltage UN	320 V
Color	green
Nominal voltage, UL/CUL Use Group B	250 V
Nominal current, UL/CUL Use Group B	12 A
Nominal voltage, UL/CUL Use Group D	300 V
Nominal current, UL/CUL Use Group D	10 A

Classifications

eClass

eClass 4.0	272607xx
eClass 4.1	27260701
eClass 5.0	27260701

Printed-circuit board connector - DFK-MSTB 2,5/ 5-G WW(1X1) - 0708140

Classifications

eclass

eClass 5.1	27260701
eClass 6.0	27260704

etim

ETIM 3.0	EC000897
ETIM 4.0	EC001283

unspsc

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Certificates

Certification

UL Recognized / cUL Recognized / GOST / cULus Recognized

Certification EX

Certification submitted

Approval details

UL Recognized
cUL Recognized
GOST
cULus Recognized
