

10BASE-T LAN MAGNETICS

Filtered Modules



LM00506

- Compatible with a variety of 10Base-T transceiver chipsets
- Conforms to IEEE 802.3 standards
- Through hole and surface mount packaging
- Operating temperature 0° to 70° C
- Minimum interwinding breakdown voltage of 1500 Vrms

ELECTRICAL SPECIFICATIONS AT 25° C

Part Number	Configuration		Insertion Loss dB max	Attenuation dB min @30MHz		Return Loss dB min	Common to Common Mode Rejection dB min			Crosstalk dB min
	TX	RX	1MHz to 10MHz	TX	RX	1MHz to 10MHz	30MHz	50MHz	100MHz	1MHz to 10MHz
S556-5999-A4	RFTC	RFTC	-1.0	-28	-16	-15	-40	-30	-30	-35
S556-5999-32	FTC	FTC	-1.0	-28	-16	-15	-45	-45	-35	-35
A556-2006-02*	FTC	FTC	-1.0	-27	-17.5	-20	-35	-30	-25	-45
S556-5999-02	FTC	FTC	-1.0	-27	-17.5	-20	-35	-30	-25	-45
A556-2006-03	FTC	FTC	-1.0	-27	-17.5	-20	-35	-30	-25	-45
0556-2006-14	FTC	FTC	-1.0	-28	-17.5	-20	-40	-40	-30	-35
0556-3873-03	FTC	FTC	-1.0	-27	-20	-15	-40	-35	-30	-35
A556-2006-00	FTC	FT	-1.0	-27	-17.5	-20	-35	-30	-25	-45
A556-2006-DE	FT	FT	-1.0	-27	-17.5	-20	---	---	---	-45
S556-5999-DE	FT	FT	-1.0	-27	-17	-15	---	---	---	-35

*Operating temperature range -40° to +85° C

Configuration Guide	
T	Transformer
C	Choke
F	Low Pass Filters
R	Predistortion Resistors


©2002 Bel Fuse Inc. Specifications subject to change without notice. 09.02

Bel Fuse Inc. 206 Van Vorst Street, Jersey City, NJ 07302 • Tel 201-432-0463 • Fax 201-432-9542 • www.belfuse.com


10BASE-T LAN MAGNETICS Filtered Modules

SCHEMATICS


S556-5999-A4



S556-5999-32



A556-2006-02
S556-5999-02



10BASE-T LAN MAGNETICS


Filtered Modules




LM00506

SCHEMATICS


A556-2006-03



0556-2006-14



0556-3873-03




10BASE-T LAN MAGNETICS


Filtered Modules

SCHEMATICS

A556-2006-00



A556-2006-DE
S556-5999-DE



10BASE-T LAN MAGNETICS




Filtered Modules



LM00506




MECHANICALS

S556-5999-32
S556-5999-A4



Dimensions are in inches [millimeters].
Standard dimension tolerance is ±0.005 [0.13] unless otherwise noted.

S556-5999-02
S556-5999-DE




Dimensions are in inches [millimeters].
Standard dimension tolerance is ±0.005 [0.13] unless otherwise noted.

LM00506


MECHANICALS

0556-3873-03



Dimensions are in inches [millimeters].
Standard dimension tolerance is ± 0.005 [0.13] unless otherwise noted.

0556-2006-14



Dimensions are in inches [millimeters].
Standard dimension tolerance is ± 0.005 [0.13] unless otherwise noted.

Dimensions are in inches [millimeters].
Standard dimension tolerance is ± 0.005 [0.13] unless otherwise noted.

©2002 Bel Fuse Inc. Specifications subject to change without notice. 09.02

CORPORATE

Bel Fuse Inc.
206 Van Vorst Street
Jersey City, NJ 07302
Tel 201-432-0463
Fax 201-432-9542
www.belfuse.com

L5-28

FAR EAST

Bel Fuse Ltd.
8F / 8 Luk Hop Street
San Po Kong
Kowloon, Hong Kong
Tel 852-2328-5515
Fax 852-2352-3706
www.belfuse.com

EUROPE

Bel Fuse Europe Ltd.
Preston Technology Management Centre
Marsh Lane, Suite G7, Preston
Lancashire, PR1 8UD, U.K.
Tel 44-1772-556601
Fax 44-1772-888366
www.belfuse.com