



EVERLIGHT ELECTRONICS CO., LTD.

DEVICE NUMBER : DPT-020-110

REV : 1.0

ECN : _____

PAGE : 1/7

3mm Phototransistor

MODEL NO : PT202C-3

■ Features :

- Fast response times
- High photo sensitivity

■ Description :

- PT202C-3 is a high speed and high sensitive silicon NPN epitaxial planar phototransistor in a standard $\phi 3$ mm package. Due to its water clear epoxy the device is sensitive to visible and near infrared radiation.

■ Applications :

- Optoelectronic switches
- VCRs ,Video cameras
- Floppy disk drives
- Infrared applied systems

PART NO.	CHIP	LENS COLOR
	MATERIAL	
PT	Silicon	Water Clear



EVERLIGHT ELECTRONICS CO., LTD.


DEVICE NUMBER : DPT-020-110
ECN : _____

REV : 1.0
PAGE : 2/7

3mm Phototransistor

MODEL NO : PT202C-3

■ Package Dimension :



■ Notes :

- 1.All dimensions are in millimeter.
- 2.Protruded resin under flange 1.5 mm Max.
- 3.Lead spacing is measured where the lead emerge from the package.
- 4.Lens color : Water clear.
- 5.Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 6.These specification sheets include materials protected under copyright of EVERLIGHT corporation . Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.
- 7.When using this product , please observe the absolute maximum ratings and the instructions for use outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.



EVERLIGHT ELECTRONICS CO., LTD.

DEVICE NUMBER : DPT-020-110 REV : 1.0
ECN : _____ PAGE : 3/7

3mm Phototransistor

MODEL NO : PT202C-3

■ Absolute Maximum Ratings at $T_A = 25^{\circ}\text{C}$

Parameter	Symbol	Rating	Unit	Notice
Collector-Emitter Voltage	V_{CEO}	30	V	
Emitter-Collector- Voltage	V_{ECO}	5	V	
Collector Current	I_C	20	mA	
Operating Temperature	T_{opr}	-25 ~ +85	$^{\circ}\text{C}$	
Storage Temperature	T_{stg}	-40 ~ +85	$^{\circ}\text{C}$	
Soldering Temperature	T_{sol}	260	$^{\circ}\text{C}$	4mm from mold body less than 5 seconds
Power Dissipation at(or below) 25 $^{\circ}\text{C}$ Free Air Temperature	P_C	75	mW	

■ Electronic Optical Characteristics :

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Collector-Emitter Breakdown Voltage	BV_{CEO}	30	----	----	V	$I_C=100\mu\text{A}$ $E_e=0\text{mW}/\text{cm}^2$
Emitter-Collector Breakdown Voltage	BV_{ECO}	5	----	----	V	$I_E=100\mu\text{A}$ $E_e=0\text{mW}/\text{cm}^2$
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	----	----	0.4	V	$I_C=2\text{mA}$ $E_e=1\text{mW}/\text{cm}^2$
Rise Time	t_r	----	15	----	μS	$V_{CE}=5\text{V}$ $I_C=1\text{mA}$ $R_L=1000\Omega$
Fall Time	t_f	----	15	----		
Collector Dark Current	I_{CEO}	----	----	100	nA	$V_{CE}=20\text{V}$ $E_e=0\text{mW}/\text{cm}^2$
On State Collector Current	$I_{C(on)}$	1.0	3.0	----	mA	$V_{CE}=5\text{V}$ $E_e=1\text{mW}/\text{cm}^2$
Wavelength of Peak Sensitivity	λ_p	----	860	----	nm	----
Rang of Spectral Bandwidth	$\lambda_{0.5}$	----	400---1200	----	nm	----



3mm Phototransistor

MODEL NO : PT202C-3

Typical Electrical/Optical/Characteristics Curves






Fig.4 Collector Current vs. Irradiance




Fig.5 Spectral Sensitivity





Fig.6 Collector Current vs. Collector-Emitter Voltage





EVERLIGHT ELECTRONICS CO., LTD.

DEVICE NUMBER : DPT-020-110

REV : 1.0

ECN : _____

PAGE : 5/7

3mm Phototransistor

MODEL NO : PT202C-3

■ Reliability Test Item And Condition

The reliability of products shall be satisfied with items listed below.

Confidence level:90%

LTPD:10%

NO.	Item	Test Conditions	Test Hours/ Cycle	Sample Size	Failure Judgement Criteria	Ac/Re
1	Solder Heat	TEMP : 260°C ± 5 °C	5 sec	22 PCs	$I_{c(on)} \leq L \times 0.8$ L :Lower specification limit	0/1
2	Temperature Cycle	H : +85°C 30 min ↓ 5 min ↓ L : -55°C 30 min	50 cycle	22 PCs		0/1
3	Thermal Shock	H : +100°C 5 min ↓ 10 sec ↓ L : -10°C 30 min	50 cycle	22 PCs		0/1
4	High Temperature Storage	TEMP. : +100°C	1000 hrs	22 PCs		0/1
5	Low Temperature Storage	TEMP. : -55°C	1000 hrs	22 PCs		0/1
6	DC Operating Life	V _{CE} =5V	1000 hrs	22 PCs		0/1
7	High Temperature / High Humidity	85°C / 85% R.H.	1000 hrs	22 PCs		0/1



EVERLIGHT ELECTRONICS CO., LTD.

DEVICE NUMBER : DPT-020-110

REV : 1.0

ECN : _____

PAGE : 6/7

3mm Phototransistor


MODEL NO : PT202C-3

Test Method For On State Collector Current :

Condition : $E_e=1\text{mW/cm}^2$, $V_{CE}=5\text{V}$

Test Item : Collector Current [$I_{C(on)}$]

Unit : mA





EVERLIGHT ELECTRONICS CO., LTD.


DEVICE NUMBER : DPT-020-110
ECN : _____

REV : 1.0
PAGE : 7/7

3mm Phototransistor

MODEL NO : PT202C-3

■ Packing Specifications



■ Packing Quantity Specification

1. 1000 Pcs/1Bag , 6 Bags/1Box
2. 10 Boxes/1Carton