

1.9mm Round Subminiature "Gull Wing" Lead (Square Base) LEDs

 MODEL NO : 95-21SYGC/S530-E1/TR7

Features :

- Package in 12mm tape on 7" diameter reels.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- I.C. compatible.
- EIA std package.
- Mono-color type.


Description :

- The 95-21 SMD taping is much smaller than leaded compoments. Thusenable smaller board size.Higher packing density. Reduced storage space and finally smaller equipment to be obtained.
- Besides, light weight makes them ideal for miniature application, ect.
- Furthermore by automation assembly machines the accuracy is anticipated.

Applications :

- Small indicator for outdoor appications.
- Flat backlight for LCD, switch and symbol.
- Indicator and backlight in offie equipment.
- Indicator and backlight for battery driven equipment.
- Indicator and backlight for audio and video equipment.
- Automotive : backlighting in dashboard and switch.
- Telecommunication : indicator and backlighting in telephone and fax.
- General use.

Package Dimensions :



PART NO.	CHIP		Lens Color
	Material	Emitted Color	
95-21SYGC/S530-E1/TR7	AlGaInP	Super Yellow Green	Water Clear

OFFICE : NO. 25,Lane 76,Sec.3, Chung Yang Rd., Tucheng 236, Taipei, Taiwan, R.O.C.

TEL : 886-2-2267-2000,2267-9936

FAX : 886-2-2267-6244,22676189,22676306

<http://www.everlight.com>



EVERLIGHT ELECTRONICS CO.,LTD.


DEVICE NUMBER : DLE-952-160 REV : 1.1

ECN : PAGE : 2/5


1.9mm Round Subminiature "Gull Wing" Lead (Square Base) LEDs

MODEL NO : 95-21SYGC/S530-E1/TR7

■ Package Dimensions



■ Loaded Quantity Per Reel 1000 Pcs/Reel



1. All dimensions are in millimeters .
2. Lead spacing is measured where the leads emerge from the package.
3. Protruded resin under flange 1.5 mm (0.59") max.

**1.9mm Round Subminiature "Gull Wing" Lead (Square Base) LEDs**MODEL NO : 95-21SYGC/S530-E1/TR7**■ Absolute Maximum Ratings at Ta = 25°C**

Parameter	Symbol	Rating	Unit
Reverse Voltage	Vr	5	V
Forward Current	If	25	mA
Operating Temperature	Topr	-40 ~ +85	°C
Storage Temperature	Tstg	-40 ~ +100	°C
Soldering Temperature	Tsol	260 ± 5 for 5 sec	°C
Electrostatic Discharge	ESD	2000	V
Power Dissipation	Pd	60	mW
Peak Forward Current(Duty 1/10 @ 1KHZ)	If(Peak)	160	mA

■ Electronic Optical Characteristics :

Parameter	Symbol	MIN.	TYP.	MAX.	Unit	Condition
Luminous intensity	Iv	----	12	----	mcd	If = 2mA
Luminous intensity	Iv	132	198	----	mcd	If = 20mA
Viewing Angle	2 θ 1/2	----	25	----	deg	
Peak Wavelength	λ p	----	575	----	nm	
Dominant Wavelength	λ d	----	573	----	nm	
Spectrum Radiation Bandwidth	△ λ	----	20	----	nm	
Forward Voltage	Vf	----	2.0	2.4	V	Vr=5V
Reverse Current	Ir	----	----	10	μ A	



EVERLIGHT ELECTRONICS CO.,LTD.

DEVICE NUMBER : DLE-952-160 REV : 1.1

ECN : PAGE : 4/5

1.9mm Round Subminiature "Gull Wing" Lead (Square Base) LEDs

MODEL NO : 95-21SYGC/S530-E1/TR7

■ Reliability Test Items And Conditions

NO.	Item	Test Conditions	Test Hours/ Cycle	Sample Size	Ac/Re
1	Solder Heat	TEMP : 260°C ± 5 °C	5 SEC	76 PCS	0/1
2	Temperature Cycle	H : +85°C 30 min ↑ 5 min ↓ L : -55°C 30 min	50 Cycle	76 PCS	0/1
3	Thermal Shock	H : +100°C 5 min ↑ 10 sec ↓ L : -10°C 30 min	50 Cycle	76 PCS	0/1
4	High Temperature Storage	TEMP. : +100°C	1000 HRS	76 PCS	0/1
5	Low Temperature Storage	TEMP. : -55°C	1000 HRS	76 PCS	0/1
6	DC Operating Life	If = 20 mA	1000 HRS	76 PCS	0/1
7	High Temperature / High Humidity	85°C / 85% R.H.	1000 HRS	76 PCS	0/1



EVERLIGHT ELECTRONICS CO.,LTD.

DEVICE NUMBER : DLE-952-160

REV : 1.1

ECN :

PAGE : 5/5

1.9mm Round Subminiature "Gull Wing" Lead (Square Base) LEDs

MODEL NO : 95-21SYGC/S530-E1/TR7

Typical Electro-Optical Characteristic Curves

