




NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 4A @125VAC, 2A @250VAC
5. CONTACT RESISTANCE: 10mILLI-OHMS
6. DIELECTRIC STRENGTH: 1500 VAC-1Minute
7. INSULATION RESISTANCE: 200 Mega-OHMS
8. MATERIALS:
 - HOUSING: ZINC ALLOY DIE CAST
 - CYLINDER: ZINC ALLOY W/CHROME PLATE
 - CONTACTS: SILVER PLATE
 - CRISS CROSS TUMBLERS. (11 BLADE)
9. KEYLOCK, KEYS, AND HEX NUT YO BE PACKED TOGETHER IN INDIVIDUAL BAGS.

LEGEND

- = INDICATE NO KEY PULL
- ⊙ = INDICATES KEY PULL POSSIBLE

CIRCUIT: SPST
CONTACT CONFIGURATION

SWITCH FUNCTION	
POS 1	POS 2
↑	→
DTF	DN

RECOMMENDED PANEL CUTOUT

C	18008	ADD NOTE 9	3/12/08	RC	 K0128B-2007				
B	12872	REMOVE TERM /NOTE 8	3/4/03	CJB					
A	11754	RELEASED FOR PRODUCTION	10/17/01	CJB					
REV.	ECN NO.	DESCRIPTION	DATE	CHKD					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED									
					SCALE	DATE	DR	DWG	REV
					1.5:1	10/17/01	CJB	K200202	C