

QUICK CONNECT (CO-AX)

The *ULTEMate* electrical connection solution for harsh environments.

Being constructed from Ultem®, a high temperature and corrosion resistant composite material, makes this the '*ULTEMate*' electrical connection solution. The Quick Connect series co-ax composite connector is chemical resistant and environmentally sealed up to IP68. It is ideal for the most rigorous applications.

FEATURES

- Quick latch mechanism
- Contacts use lock nut and soldered conductors
- Universal mounting
- Choice of cable gland & over moulding options
- Standard sealing O-ring
- Constructed from Ultem®, a high temperature resistant composite material
- Meets UL94 Class V-0 flammability requirements
- Can be sealed against dust and moisture up to IP68

BENEFITS

- Positive location
- No costly crimp tooling
- Flexible panel mounting of both halves
- Variety of options for maximum design-in flexibility
- Cost Effective
- O-ring's match design requirements
- Prevents mis-mating
- Key prevents damage to connector and cable
- Can be washed, sterilised and autoclaved without performance degradation
- Withstands heat, dust, moisture



GENERAL SPECIFICATION

Crimp contacts, insert / extraction tools, dust caps and back fittings

Materials

Shell / Insulators: Temperature and corrosion resistant composite, Ultem®

Contacts:

Back Fitting Options

Cable Gland:	Strain Relief
Over-mould:	Cable Sealing
Panel Nut:	Universal Mount
Conduit Adapter:	Wire management
Heat Shrink:	One-stop-shop kit option

Recommended Cable

50 Ω URM 43/72/76/108, RG58C/U

75 Ω URM 41/56/70, T3242

Voltage: Up to 1000 Vac (rms)

Insulation Resistance: 1000 MΩ

Temperature Rating [connector]

-55°C to 150°C (The upper limit is the maximum internal hot-spot temperature resulting from the combination of ambient temperature and heating due to current)




DEUTSCH


Dimensions (mm)

	A	B	C	D
QC2	25	16	33	22.5

Envelope dimensions are for reference only.
Contact Deutsch Ltd if more detail is required.



Construction



Ordering Information

Plug

Description	Part No.
200 series in/lp 50Ω	QC26-5001S
200 series in/lp 75Ω	QC26-7501S

Receptacle

Description	Part No.
200 series in/lr 50Ω	QC24-5001P
200 series in/lr 75Ω	QC24-7501P

Plug Sealing Cap

Description	Part No.
200 series pro-cap	IMC 29



A step ahead in technology

Castleham Industrial Estate
2 Stanier Road
St Leonards on Sea
East Sussex
TN38 9RP England
Telephone +44 (0) 1424 852722
Fax +44 (0) 1424 855979
Email industrial@deutsch.co.uk
www.deutschltd.com



DEUTSCH

Subject to change without prior notification

©2004 Deutsch DS/80/1 03/05