




Mechanical Specifications (mm)

D:	20.0	± 1
T:	5.0	± 1
Lead Diameter	1.0	± .1
S:	7.8	± 2
L:	38.0	± 9.0
Coating Lead Run Down (straight Leads)		±
B:	9.35	± .60
C:	3.50	± .5



Electrical Specifications

Resistance:	10.0 Ω	± 20 %
Max Steady State Current upto 65°C:	8.00	A
Max Rec. Energy Rating:	90	J
Maximum Capacitance @ 120 VAC:	6,000	μ f
Maximum Capacitance @ 240 VAC:	1,400	μ f
Resistance @ 100% Max Current:	0.13	Ω
Resistance @ 50% Max Current:	0.31	Ω
Body Temperature at 100% Max Current:	182.00	°C
Dissipation Constant:	32.4	mw/°C
Thermal Time Constant:	122	Sec.
Material Type (for Beta and Curve):	H	

SL22 10008

Date: 01/12/2016	Drawn by: Erin Landis
Ametherm, Inc. 961 Fairview Drive Carson City, Nevada USA 89701 www.ametherm.com	Approved By: Chad Terry
	Revision: B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[SL2210008B](#)

[Vishay:](#)

[SL22 10008](#)