



FEATURES:

- Replaceable tip probe set with sharp stainless steel tips included. (Other tips are available, see model 6475.)
- Designed for DMM's with non-sheathed banana jacks
- Also fits newer DMM's with safety-sheathed banana jacks
- Thermoplastic elastomer outer coat provides comfortable grip and flexible strain relief
- Tough polymer undercoat provides strength
- Probe and banana plug are molded directly onto the wire for robust pull strength
- Wire is a high-strand count silicone wire for extreme flexibility and high temperature resistance

MATERIALS:

Probe:

Outer Insulation: Santoprene[®] rubber, color: gray
Inner Insulation: polypropylene, color: one black, one red
Tip: stainless steel

Wire: 18 AWG

Banana Plug: Nickel-plated Brass

Spring – Nickel-plated Beryllium Copper

Plug Insulation: polypropylene, color: one black, one red

RATINGS:

Operating Voltage: Hand-held testing: 30VAC/60VDC

Hands free testing in controlled voltage environments: 1000 VRMS Max.

Current: 5 Amperes Max.

ORDERING INFORMATION: Model 5950A

Includes a set of one black and one red test lead with two replaceable tips.

All dimensions are in inches.

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90657 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[5950A](#)