

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

19



(C) COPYRIGHT 19

BY AMP INCORPORATED, ALL RIGHTS RESERVED.


LOC		DIST		REVISIONS					
CM		52		P	LTR	DESCRIPTION	DATE	DWN	APVD
					Y	REV & REDWN PER EC 0L30-0146-97	5-15-97	TB	RS

- 1 0.00076 MIN SELECTIVE GOLD PLATING ON INSIDE OF RECEPTACLE OVER NICKEL OVER ALL UNDERPLATE.
2. WIRE RANGE: 0.12 - 0.4 MM² (26 - 22 AWG)
3. INSULATION RANGE: 0.89 - 1.65
4. PARTS ARE REVERSED REELED. FOR USE WITH MINI APPLICATORS SEE PART NUMBER 60888.


POINT OF MEASUREMENT
1 90° FROM SEAM



SECTION A-A



SECTION B-B



SECTION C-C

1	0.25 BE COPPER	60804-4
MATTE TIN	0.25 BE COPPER	60804-3
PRE-TIN	0.25 PH BRZ	60804-2
2	0.25 PH BRZ	60804-1
FINISH	MATERIAL	PART NUMBER

1.359	.0535	1.91	.075	2.79	.110	-	-
1.02	.040	1.65	.065	2.67	.105	-	-
0.89	.035	1.63	.064	2.41	.095	9.65	.380
0.25	.010	1.486	.0585	2.29	.090	6.55	.258
0.13	.005	1.47	.058	2.06	.081	6.40	.252
0.00076	.000030	1.40	.055	1.96	.077	3.94	.155
MM	IN	MM	IN	MM	IN	MM	IN

CONVERSION TABLE

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±0.13
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL SEE TABLE

FINISH SEE TABLE

DWN T. BECK 5-15-97
CHK R. SWING 5-15-97
APVD A. BEDDICK 8-08-97

PRODUCT SPEC
108-1025
APPLICATION SPEC
114-1008
WEIGHT -

CUSTOMER DRAWING

NAME RECEPTACLE, .058 DIAMETER, 26-22 AWG, .035-.065 INSULATION, P.C. CONTACT

SIZE A2
CAGE CODE 00779
DRAWING NO 60804

RESTRICTED TO -

SCALE 10:1
SHEET 1 OF 1
REV Y