




LSS, LSK Series




LSK-420201Ax (x for Actuator Length)




LSK-430201Ax (x for Actuator Length)



LSS-420101Ax (x for Actuator Length)



LSS-430101Ax (x for Actuator Length)



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

Series	Number of Poles / Positions	Model	Terminal Type	Actuator Type	Actuator Height
LSK - Side Knob	42 - 4 Pole, On-On	For LSK Series: 020 - 22.0 x 9.3	1 - PCB Pin	A - Rounded Ridged	5 - 5mm (Standard)
LSS - Vertical Knob	43 - 4 Pole, On-On-On				X - Varies From 2 to 20

For LSS Series:
010 - 22.0 x 9.3

FEATURES:

- Compact Size, Multiple Functions
- RoHS and Lead-Free Compliant
- Customizable Actuator Height

SPECIFICATIONS:

Rating: 0.5A 50VDC
Temperature: -30°C to 105°C
Electrical Life: 10,000 Cycles
Contact Resistance: 30mΩ Max.
Insulation Resistance: 500MΩ Min. at 500VDC
Dielectric Strength: 500VAC for 1 Minute

MATERIALS:

Body: Steel
Actuator: Polyoxyethylene
Base: Phenolic Board
Contacts: Silver Plated Copper
Terminals: Silver Plated Brass



LSS-430101A4



LSK-420201A7

EXAMPLE PART NUMBERS:

LSK-420201A5	4P2T On-On
Model 020, PCB Pins, 5.0mm Side Actuator	
LSK-430201A5	4P3T On-On-On
Model 020, PCB Pins, 5.0mm Side Actuator	
LSS-420101A5	4P2T On-On
Model 010, PCB Pins, 5.0mm Vert. Actuator	
LSS-430101A5	4P3T On-On-On
Model 010, PCB Pins, 5.0mm Vert. Actuator	



E-SWITCH®

www.e-switch.com

800.867.2717

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[LSS-130511A7-G](#) [LSS-120352B5](#) [LSS-120312B5-G](#) [LSS-130401B7](#) [LSS-130501A7](#) [LSS-420101A5](#) [LSS-120352B5-G](#) [LSS-120332B5-G](#) [LSS-120701B8.5](#) [LSS-120312B4-G](#) [LSS-430101A5](#)