

## Single-Phase Metered PDU, 3.2-3.8kW 16/20A 200-240V, 1U Horizontal Rackmount, 2 C19 and 8 C13 outlets, C20 input with NEMA L6-20P adapter

MODEL NUMBER: PDUMH20HV



### Description

Tripp Lite Metered PDU / Power Distribution Units offer real-time local reporting of load level in amps via built-in digital meter. Enables visual current monitoring of PDU output current to prevent circuit overloads as additional equipment is added. Offers reliable rackmount multi-outlet power distribution from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

### Features

- 16/20A single phase 200-240V Metered Power Distribution Unit / PDU (Agency de-rated to 16A continuous)
- Built-in 2 digit visual meter continuously reports PDU load level in amps
- C20 inlet with C20 input cable and L6-20P adapter; 12 ft. / 3.7m line cord
- 1U horizontal rackmount format installs in one rack space
- 10 total outlets (8 C13 / 2 C19)
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Mounting ears are reversible for front or rear facing rackmount installation
- Optional PDUSIDEBRKT enables 0U vertical rackmount in compatible racks
- Back panel grounding lug
- TAA Compliant Version Available - Order Tripp Lite PDUMH20HVTAA

### Specifications

General Info	
Product Group	PDUS
OVERVIEW	

### Highlights

- Metered single phase 16/20A 200-240V PDU
- 1U horizontal rackmount; digital current meter
- C20 input with L6-20P plug adapter; 12 ft. / 3.7m line cord
- 10 total outlets (8 C13, 2 C19)
- Reversible housing; 6.5 in. / 16.5 cm depth

### Applications

- Ideal for network configurations requiring a metered PDU

### Package Includes

- Rackmount PDU
- C19 to L6-20P plug adapter
- Rack mounting brackets

PDU Type	Metered
<b>OUTPUT</b>	
Output Capacity Details	3.3kW (208V input), 3.5kW (220V input), 3.7kW (230V input), 3.8kW (240V input), 3.2kW (200V input); 20A maximum (Agency de-rated to 16A continuous)
Frequency Compatibility	50 / 60 Hz
Output Nominal Voltage	200-240V nominal, single phase
Overload Protection	Outlets are arranged in a single unbreakered load bank
Outlet Quantity / Type	8 C13 and 2 C19 outlets
Outlet Type	IEC-C13, IEC-C19
Customized Load Management Receptacles	Each outlet is individually controllable via remote interface
<b>INPUT</b>	
PDU Input Voltage	200; 208; 220; 230; 240
Maximum Input Amps	20
Maximum Input Amps Details	Agency de-rated to 16A continuous
PDU Plug Type	NEMA L6-20P; IEC-320 C20
Input Cord Length (ft.)	12
Input Cord Length (m)	3.7
Input Phase	Single-Phase
<b>LEDS ALARMS &amp; SWITCHES</b>	
Switches	n/a
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	2.25 x 20.5 x 10.5
Shipping Dimensions (hwd / cm)	5.7 x 52.1 x 26.7
Shipping Weight (lbs.)	7.2
Shipping Weight (kg)	3.3
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 6.5
Unit Dimensions (hwd / cm)	2.87 x 44.4 x 16.5
Unit Weight (lbs.)	6.8
Unit Weight (kg)	3.1
Material of Construction	Steel
Style	Rackmount
Form Factors Supported	1U rackmount. Includes mounting accessories for 2-4 post racks

PDU Form Factor	Horizontal (1U, 2U, etc)
<b>ENVIRONMENTAL</b>	
Relative Humidity	0-95% non-condensing
<b>CERTIFICATIONS</b>	
TAA Compliant Option	TAA Compliant Version Available - Order Tripp Lite PDUMH20HVTAA
Certifications	Tested to UL 60950-1 (USA, Canada), Class A (Emissions), NOM (Mexico), CE (IEC 60950), (RoHS compliant)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.