


AA8038 SERIES

External Dimensions




Frame:Aluminum Alloy
Impeller:Plastic(UL:94V-0)
Motor Structure:Shaded Pole Induction Motor.
Motor Protection:Impedance Protect.
Lead wire:UL1430AWG22
Wire Type:-AT Terminal/ -AW Wires
OPERATING TEMP*:-10°C~70°C
*:-10°C~60°C for fans with sieve/ball combination bearings.

Specifications(Nominal)

Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing													
Frame size (mm)	Model No.	Bearing System Type	Volt. (VAC)	Freq. (Hz)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM) (CFM)		Maximum Pressure (InAq) (mmAq)		*Noise Level (dB/A)	Weight (g)
80x80x38	AA8381MB-AT	◎ ※ ●	115	50/60	0.07/0.06	7.60/6.50	2300/2400	0.622/0.679	22.0/24.0	0.107/0.110	2.717/2.794	25.3/26.2	320
	AA8382MB-AT		230		0.06/0.05	10.60/8.60							
	AA8381HB-AT	◎ ※ ●	115	50/60	0.14/0.11	10.90/8.10	2400/2800	0.679/0.837	24.0/29.6	0.110/0.166	2.794/4.216	26.2/31.6	
	AA8382HB-AT		230		0.07/0.06	13.60/10.10							
Specifications subject to change without notice.													

The specification for bearing type is for reference only , for more bearing types information, please contact with your ADDA sales representative, thanks!!
(網頁上呈現產品軸承資訊均以2Ball為主，若需其他產品資訊請聯絡您在ADDA的業務代表，謝謝！！)



*Safety approvals				
✓	✓		✓	✓