










11 MOUNTED COVER OPTIONS
Befestigungsmoeglichkeiten der Kappe




TE LOGO RELATED TO MOLDING TOOL
TE Logo abhaengig von Spritzgusswerkzeug

G2

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
G		ECR-09-012156 (PCN E-09-012061 F. PART CHANGE)	04MAR2009	SJ
G1		DETAILS SEE PCN E-10-002668	04FEB2010	SJ
G2		New view added with TE Logo depending on mold	28NOV2017	MAH.

NOTES
Bemerkungen

- TE LOGO
TE Logo
- TE ORDER-NO.
TE Bestell-Nr.
- PRODUCTION DATE
Produktionsdatum
- LETTER-INSERT FOR THE REVISION STATUS OF THE MOLD
Schriftsatz fuer Aenderungszustand des Werkzeuges
ACTUAL STATUS: SEE TABLE
Aktueller Stand: siehe Tabelle
- MATERIAL MARKING ACCORDING TO VDA 260
Werkstoffkennzeichnung nach VDA 260
- BULK PACKAGING IN CORRUGATED BOX
Schuetftgut im Versandkarton
- CABLE EXIT DESIGNED FOR CORRUGATED TUBE NW 13
Kabelabgang ausgelegt fuer Wellrohr NW 13
- MALFUNCTION CAUSED BY LAQUER IS NOT COVERED
BY TE WARRANTY
Funktionsbeeintraechtigung durch Lackieren liegt nicht
im Einfluss und Gewaehrleistungsumfang von TE
- WARPAGE UP TO -1.0mm FROM NOM. DIMENSION PERMITTED
Verzug zulaessig bis -1.0mm vom Nennmass
- MAX. CABLE TIE WIDTH: 3.8mm
max. Kabelbinderbreite: 3.8mm
- SUITABLE FOR TAB AND RECEPTACLE HOUSING GROUP D
SEE PRODUCT GROUP DRAWING 1563709
Passend fuer Flachstecker- und Buchsengehaeuse der Gruppe D
siehe Produktgruppenzeichnung 1563709



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. Goetz 21JUN2007	 TE Connectivity	
DIMENSIONS: mm		CHK J. Granzow 22JUN2007		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD K. Eberwein 25JUN2007	NAME COVER, 90 Kappe, 90 Grad HDSCS - GROUP D	
		PRODUCT SPEC 108-94020	SIZE A1	
	ANGLES FINISH	APPLICATION SPEC 116-18756		CAGE CODE 00779
		WEIGHT 5.9g	DRAWING NO 1563110	
CUSTOMER DRAWING		SCALE 5:1	SHEET 1	REV. G2

0-1563110-1	G	COVER 90° Kappe 90°	1
TE ORDER-NO. TE Bestell-Nr.	REV.	DESCRIPTION Beschreibung	ITEM