



PRODUCT NUMBER
73306-XXXLF

PLATING OPTION	PACKAGE OPTION	TERMINAL LOADING
1 = GXT 0.76 μ m	1 = TAPE ON REEL	1 = FULLY LOADED
3 = GOLD 0.76 μ m	2 = TUBE	
5 = GOLD 1.27 μ m	3 = TAPE ON REEL IN PLASTIC BAG	

WHEN NEEDED, SUFFIX LETTER "LF" INDICATES THE PRODUCT IS ROHS COMPATIBLE, SEE NOTE 4.



CUSTOMER COPY FOR REFERENCE ONLY


mat'l. code	ISO 1302	tolerance	ISO 406	ISO 1101	projection	product family	MOD JACK
tr	ecm no	dr	date	ISO 1302	tolerance unless otherwise specified	ISO 406	ISO 1101
H	F05-0247	DLE	05.09.12	angle	linear	±0.13	
J	F06-0240	DLE	06.07.18	linear			
K	F09-0076	LSA	09.07.23	±2°			
L	B-15798	JFA	13.09.09	dr	D LEGRAND	04.10.18	
F	F03020	DLE	03.01.27	chr	D LEGRAND	04.10.18	
G	F04-0363	DLE	04.10.18	qppd	P NZ	04.10.18	
sheet	revision	L	F	B			
index	sheet	1	2	3			

- NOTES:
- 1 - MATERIAL: HOUSING: HIGH TEMP. NYLON, COLOUR BLACK.
TERMINAL: PHOSPHOR BRONZE.
 - 2 - PLATING: CONTACT AREA: SEE TABLE.
SOLDER TAIL : 90/10 SnPb 2 μ m MIN.
WHEN SUFFIX "LF" IS REQUIRED, 2 μ m MIN MATTE TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.
NO RAW EDGES EXCEPT SOLDER TAIL TIPS
 - 3 - SOLDER TAILS COPLANARITY : 0.1 mm
 - 4 - ROHS COMPATIBLE. PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, 2 μ m MINIMUM MATTE TIN OVER 1.27 μ m MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 245°C PEAK TEMPERATURE FOR 30 SECONDS MAX IN A CONVECTION, INFRA-RED OR VAPOR PHASE OR REFLOW OVEN.
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-22-008
 - 5 - PACKAGING FOR OPTION 3: EACH REEL IS WRAPPED INTO A PLASTIC BAG TO PROTECT FROM MOISTURE DURING STACKING TIME.



FCIconnect.com

Copyright FCI



CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface ISO 1302		✓	tolerance ISO 406 ISO 1101		projection 		product family MOD JACK									
ltr	ecn no	dr	date	tolerances unless otherwise specified							title									
A	F04.0363	DLE	04.10.18	angles	linear	±0.13					SMT RA JACK									
B	F06-0240	DLE	06.07.18							4 POS NARROW OUTSIDE										
				±2°						scale 2:1										
				dr	D LEGRAND	04.10.18														
				engr	P NIZZI	04.10.18														
				chr	D LEGRAND	04.10.18														
				appd	P NZ	04.10.18				dwg no										
sheet index		revision									sheet 3 of -				size					
		sheet									73306				A4					
											type									
											CUSTOMER Drawing									