

## MTK BU

Order No.: 3101197

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=3101197>

Disconnect and test disconnect terminal block, Connection type: Screw connection, Cross section: 0.2 mm<sup>2</sup> - 4 mm<sup>2</sup>, AWG: 24 - 12, Nominal current: 16 A, Nominal voltage: 400 V, Length: 46 mm, Width: 5.2 mm, Color: blue, Assembly: NS 35/7,5, NS 35/15, NS 32

### Commercial data

|                          |                    |
|--------------------------|--------------------|
| EAN                      | 4017918092641      |
| Pack                     | 50 pcs.            |
| Customs tariff           | 85369010           |
| Weight/Piece             | 0.009766 KG        |
| Catalog page information | Page 381 (CL-2009) |

### Product notes

WEEE/RoHS-compliant since:  
01/01/2003



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

### Technical data

#### General

|                       |      |
|-----------------------|------|
| Number of levels      | 1    |
| Number of connections | 2    |
| Color                 | blue |

|                                    |    |
|------------------------------------|----|
| Insulating material                | PA |
| Inflammability class acc. to UL 94 | V0 |

**Dimensions**

|                  |         |
|------------------|---------|
| Width            | 5.2 mm  |
| Length           | 46 mm   |
| Height NS 35/7,5 | 51.5 mm |
| Height NS 35/15  | 59 mm   |
| Height NS 32     | 56 mm   |

**Technical data**

|                           |                                                       |
|---------------------------|-------------------------------------------------------|
| Maximum load current      | 16 A (with 4 mm <sup>2</sup> conductor cross section) |
| Rated surge voltage       | 6 kV                                                  |
| Pollution degree          | 3                                                     |
| Surge voltage category    | III                                                   |
| Insulating material group | I                                                     |
| Nominal current $I_N$     | 16 A                                                  |
| Nominal voltage $U_N$     | 400 V                                                 |

**Connection data**

|                                                                            |                      |
|----------------------------------------------------------------------------|----------------------|
| Conductor cross section solid min.                                         | 0.2 mm <sup>2</sup>  |
| Conductor cross section solid max.                                         | 4 mm <sup>2</sup>    |
| Conductor cross section stranded min.                                      | 0.2 mm <sup>2</sup>  |
| Conductor cross section stranded max.                                      | 2.5 mm <sup>2</sup>  |
| Conductor cross section AWG/kcmil min.                                     | 24                   |
| Conductor cross section AWG/kcmil max                                      | 12                   |
| Conductor cross section stranded, with ferrule without plastic sleeve min. | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule without plastic sleeve max. | 2.5 mm <sup>2</sup>  |
| Conductor cross section stranded, with ferrule with plastic sleeve min.    | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule with plastic sleeve max.    | 1.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, solid min.                           | 0.2 mm <sup>2</sup>  |
| 2 conductors with same cross section, solid max.                           | 1.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded min.                        | 0.2 mm <sup>2</sup>  |

|                                                                                         |                      |
|-----------------------------------------------------------------------------------------|----------------------|
| 2 conductors with same cross section, stranded max.                                     | 1.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.   | 0.25 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.   | 1.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min. | 0.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max. | 1.5 mm <sup>2</sup>  |
| Cross-section with insertion bridge, solid max.                                         | 4 mm <sup>2</sup>    |
| Cross-section with insertion bridge, stranded max.                                      | 2.5 mm <sup>2</sup>  |
| Type of connection                                                                      | Screw connection     |
| Stripping length                                                                        | 7 mm                 |
| Internal cylindrical gage                                                               | A3                   |
| Screw thread                                                                            | M3                   |
| Tightening torque, min                                                                  | 0.5 Nm               |
| Tightening torque max                                                                   | 0.6 Nm               |

#### Certificates / Approvals



Certification

CSA, CUL, DNV, GL, GOST, UL

#### CSA

|                       |       |
|-----------------------|-------|
| Nominal voltage $U_N$ | 300 V |
| Nominal current $I_N$ | 15 A  |
| AWG/kcmil             | 28-12 |

#### CUL

|                       |       |
|-----------------------|-------|
| Nominal voltage $U_N$ | 300 V |
| Nominal current $I_N$ | 10 A  |
| AWG/kcmil             | 28-12 |

#### UL

|                       |       |
|-----------------------|-------|
| Nominal voltage $U_N$ | 300 V |
| Nominal current $I_N$ | 10 A  |
| AWG/kcmil             | 28-12 |

**Accessories**

| Item            | Designation                   | Description                                                                                                                                                                    |
|-----------------|-------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Assembly</b> |                               |                                                                                                                                                                                |
| 3101223         | ATS-MTK                       | Partition plate, Width: 1 mm, Color: gray                                                                                                                                      |
| 3022218         | CLIPFIX 35                    | Snap-on end bracket, for 35 mm NS 35/7.5 or NS 35/15 DIN rail, can be fitted with Zack strip ZB 8 and ZB 8/27, terminal strip marker KLM 2 and KLM, width: 9.5 mm, color: gray |
| 3101029         | D-MTK                         | End cover, Length: 46 mm, Width: 1 mm, Height: 28.7 mm, Color: gray                                                                                                            |
| 3101090         | D-MTK BU                      | End cover, Length: 46 mm, Width: 1 mm, Color: blue                                                                                                                             |
| 1201442         | E/UK                          | End clamp, for assembly on NS 32 or NS 35/7,5 DIN rail                                                                                                                         |
| 1201028         | NS 32 AL UNPERF 2000MM        | G rail 32 mm (NS 32)                                                                                                                                                           |
| 1201280         | NS 32 CU/120QMM UNPERF 2000MM | G-profile DIN rail, deep-drawn, material: Copper, unperforated, height 15 mm, width 32 mm, length 2 m                                                                          |
| 1201358         | NS 32 CU/35QMM UNPERF 2000MM  | G-profile DIN rail, material: Copper, unperforated, height 15 mm, width 32 mm, length 2 m                                                                                      |
| 1201002         | NS 32 PERF 2000MM             | G-profile DIN rail, material: Steel, perforated, height 15 mm, width 32 mm, length 2 m                                                                                         |
| 1201015         | NS 32 UNPERF 2000MM           | G-profile DIN rail, material: Steel, unperforated, height 15 mm, width 32 mm, length 2 m                                                                                       |
| 0801762         | NS 35/ 7,5 CU UNPERF 2000MM   | DIN rail, material: Copper, unperforated, height 7.5 mm, width 35 mm, length: 2 m                                                                                              |
| 0801733         | NS 35/ 7,5 PERF 2000MM        | DIN rail, material: Steel, galvanized and passivated with a thick layer, perforated, height 7.5 mm, width 35 mm, length: 2 m                                                   |
| 0801681         | NS 35/ 7,5 UNPERF 2000MM      | DIN rail, material: Steel, unperforated, height 7.5 mm, width 35 mm, length: 2 m                                                                                               |
| 1201756         | NS 35/15 AL UNPERF 2000MM     | DIN rail, deep-drawn, high profile, unperforated, 1.5 mm thick, material: Aluminum, height 15 mm, width 35 mm, length 2 m                                                      |
| 1201895         | NS 35/15 CU UNPERF 2000MM     | DIN rail, material: Copper, unperforated, 1.5 mm thick, height 15 mm, width 35 mm, length: 2 m                                                                                 |
| 1201730         | NS 35/15 PERF 2000MM          | DIN rail, material: Steel, perforated, height 15 mm, width 35 mm, length: 2 m                                                                                                  |
| 1201714         | NS 35/15 UNPERF 2000MM        | DIN rail, material: Steel, unperforated, height 15 mm, width 35 mm, length: 2 m                                                                                                |
| 1201798         | NS 35/15-2,3 UNPERF 2000MM    | DIN rail, material: Steel, unperforated, 2.3 mm thick, height 15 mm, width 35 mm, length: 2 m                                                                                  |

**Bridges**

|         |           |                                                              |
|---------|-----------|--------------------------------------------------------------|
| 2303145 | EBL 2- 5  | Cross connector/bridge, Number of positions: 2, Color: gray  |
| 2303158 | EBL 3- 5  | Cross connector/bridge, Number of positions: 3, Color: gray  |
| 2303132 | EBL 10- 5 | Cross connector/bridge, Number of positions: 10, Color: gray |

**Marking**


|         |                  |                                                                                                 |
|---------|------------------|-------------------------------------------------------------------------------------------------|
| 1007219 | SBS 5:UNBEDRUCKT | Marker cards for modular terminal blocks, color: white                                          |
| 1050295 | ZB 5:SO/CMS      | Zack strip, 10-section, divisible, special printing, marking according to customer requirements |

**Tools**

|         |             |                                                                                                                                                               |
|---------|-------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1205121 | SZG 0,6X3,5 | Screwdriver, bladed. with stepped blade, matches all screw terminal blocks with 2.3 mm diameter test socket screws and test plug sockets, blade width: 3.5 mm |
|---------|-------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|

**Diagrams/Drawings**

Circuit diagram



**Address**

PHOENIX CONTACT Inc., USA  
586 Fulling Mill Road  
Middletown, PA 17057, USA  
Phone (800) 888-7388  
Fax (717) 944-1625  
<http://www.phoenixcon.com>



© 2010 Phoenix Contact  
Technical modifications reserved;