

TRIAC(Surface Mount Device / Non-isolated)

TMG2D60D

(Sensitive Gate)


SanRex Triac TMG2D60D is designed for full wave AC control applications. It can be used as an ON/OFF function or for phase control operation.

Typical Applications

- Home Appliances : Washing Machines, Vacuum Cleaners, Rice Cookers, Micro Wave Ovens, Hair Dryers, other control applications
- Industrial Use : SMPS, Copier Machines, Motor Controls, Dimmer, SSR, Heater Controls, Vending Machines, other control applications

Features

- $I_T(RMS)=2A$
- High Surge Current
- Lead-Free Package



Maximum Ratings





($T_j=25^{\circ}C$ unless otherwise specified)

Symbol	Item	Reference	Ratings	Unit
V_{DRM}	Repetitive Peak Off-State Voltage		600	V
$I_T(RMS)$	R.M.S. On-State Current	$T_c=109^{\circ}C$	2	A
I_{TSM}	Surge On-State Current	One cycle, 50Hz/60Hz, Peak value non-repetitive	18/20	A
I^2t	I^2t (for fusing)		1.67	A^2S
P_{GM}	Peak Gate Power Dissipation		1.5	W
$P_{G(AV)}$	Average Gate Power Dissipation		0.1	W
I_{GM}	Peak Gate Current		1	A
V_{GM}	Peak Gate Voltage		7	V
T_j	Operating Junction Temperature		$-40 \sim +125$	$^{\circ}C$
T_{stg}	Storage Temperature		$-40 \sim +150$	$^{\circ}C$
	Mass		0.32	g


Electrical Characteristics

Symbol	Item		Reference	Ratings			Unit
				Min.	Typ.	Max.	
IDRM	Repetitive Peak Off-State Current		VD=VDRM, Single phase, half wave, Tj=125°C			1	mA
VTM	Peak On-State Voltage		IT=3A, Inst. measurement			1.6	V
IGT1 ⁺	1	Gate Trigger Current	VD=6V, RL=10 Ω			5	mA
IGT1 ⁻	2					5	
IGT3 ⁺	3					10	
IGT3 ⁻	4					5	
VGT1 ⁺	1	Gate Trigger Voltage				1.5	V
VGT1 ⁻	2					1.5	
VGT3 ⁺	3					2.0	
VGT3 ⁻	4					1.5	
VGD	Non-Trigger Gate Voltage		Tj=125°C, VD=½VDRM	0.2			V
(dv/dt)c	Critical Rate of Rise of Off-State Voltage at Commutation		Tj=125°C, [di/dt]c=−1A/ms, VD=⅔VDRM	3			V/μs
IH	Holding Current				2		mA
Rth(j-c)	Thermal Resistance		Junction to case			5.8	°C/W
Rth(j-a)			Junction to ambient			60	°C/W


Trigger mode of the triac




Gate Characteristics




On-State Characteristics (MAX)




RMS On-State Current vs Maximum Power Dissipation




RMS On-State vs Allowable Case Temperature




Surge On-State Current Rating (Non-Repetitive)



Transient Thermal Impedance



$I_{GT} - T_J$ (Typical)



$V_{GT} - T_J$ (Typical)

