


2mm x 5mm Discrete LED
Rectangular
Tinted, Diffused

Dialight

521-9332, -9452, -9499, -9718



PART NO.	COLOR	DRAWING
521-9332	Green	A
521-9452	Yellow	A
521-9499	Red	B
521-9718	Blue	B

ABSOLUTE MAXIMUM RATINGS ($T_A=25^\circ\text{C}$)	Green -9332	Yellow -9452	Red -9499	Blue -9718
Power Dissipation (mW)	135	85	100	189
Forward Current (mA)	30	20	30	30
Derating (mA/ $^\circ\text{C}$) From 50°C 1. mW/ $^\circ\text{C}$ From 25°C	.5	.34	.4	.45 ¹
Peak Current (mA)	500*	500*	120	180
Pulse width = 1 ms *Pulse width = 10 μs				
Operating Temperature ($^\circ\text{C}$)	-20/+100	-55/+100	-55/+100	-25/+75
Storage Temperature ($^\circ\text{C}$)	-55/+100	-55/+100	-55/+100	-25/+100
Soldering Temperature	260 $^\circ\text{C}$, 5 seconds, 1.6 mm from case			

Solder Adherence per MIL-STD-202E, Method 208C

OPERATING CHARACTERISTICS ($T_A=25^\circ\text{C}$)		Green -9332	Yellow -9452	Red -9499	Blue -9718
Luminous Intensity (mcd)	Min.	2.6	2.2	3	9
	Typical	4	3.5	7.4	18
Peak Wavelength (nm)	Typical	565	583	635	430
λ Peak					
Viewing Angle (2θ $^\circ$)	Typical	110 $^\circ$	110 $^\circ$	140 $^\circ$	120 $^\circ$
Forward Voltage (V)	Typical	2.2	2.1	2	5.3
	Max.	3	2.6	2.8	6
Reverse Voltage (V), $I_R=100\mu\text{A}$	Min.	5	5	5	5

θ $^\circ$ is the off axis angle at which the luminous intensity is half the axial luminous intensity