





7 0.000762 [0.00030] GOLD ON CONTACT AREA, 0.00254-0.00508 [0.000100-0.000200]
MATTE TIN ON SOLDER TAIL, ALL OVER 0.00127 [0.00050] NICKEL.



RECOMENDED PCB LAYOUT
FOR USE WITH 0.20 [.008] THICK STENCIL

	-	35.56 [1.400]	14	37.69 [1.484]	30	6-147447-4	
	-	33.02[1.300]	13	34.23 [1.384]	28	6-147447-3	
	-	30.48[1.200]	12	32.61 [1.284]	26	6-147447-2	
	-	27.94[1.100]	11	30.07[1.184]	24	6-147447-1	
	-	25.40[1.000]	10	27.53[1.084]	22	6-147447-0	
	-	22.86 [.900]	9	25.00 [.984]	20	5-147447-9	
	-	20.32 [.800]	8	22.45 [.884]	18	5-147447-8	
	-	17.78 [.700]	7	19.91 [.784]	16	5-147447-7	
	-	15.24 [.600]	6	17.37 [.684]	14	5-147447-6	
	32 mm	10.16 [.400]	4	12.29 [.484]	10	5-147447-5	
	-	12.70 [.500]	5	14.83 [.584]	12	5-147447-4	
	-	7.62 [.300]	3	9.75 [.384]	8	5-147447-3	
		5.08 [.200]	2	7.21 [.284]	6	5-147447-2	
	24 mm	2.54 [.100]	1	4.67 [.184]	4	5-147447-1	
	44 mm	17.78 [.700]	7	19.91 [.784]	16	+47447-8	
	44 mm	15.24 [.600]	6	17.37 [.684]	14	+47447-7	
	32 mm	12.70 [.500]	5	14.83 [.584]	12	+47447-6	
	32 mm	10.16 [.400]	4	12.29 [.484]	10	+47447-5	
	56 mm	35.56 [1.400]	14	37.69 [1.484]	30	+47447-4	
	24 mm	2.54 [.100]	1	4.67 [.184]	4	+47447-3	
	44 mm	22.86 [.900]	9	25.00 [.984]	20	+47447-2	
	32 mm	7.62 [.300]	3	9.75 [.384]	8	+47447-1	

PLATING	TAPE WIDTH	C	B	A	NO OF POSN	PART NUMBER
---------	---------------	---	---	---	---------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER 17APR00		 TE Connectivity	
		CHK J. GESFORD 17APR00			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±0.13 [.005] 4 PLC ±- ANGLES ±-		NAME SURFACE MOUNT HDR ASSY, MOD 11, B/A, VERT, D/R, 100 C/L, .025 SQ. POST, WITH PICK AND PLACE CAP	
		PRODUCT SPEC - APPLICATION SPEC -			
MATERIAL 		FINISH SEE TABLE -		SIZE A2	
		WEIGHT -		CAGE CODE 00779	
		Customer Drawing		DRAWING NO C-147447	
				RESTRICTED TO -	
				SCALE 4:1	
				SHEET OF	
				REV G1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-147447-5](#)