



**600F005**  
**MIL-C-27599 and MIL-C-38999 Series I**  
**Plug and Receptacle Holder**



**NO POLARIZATION REQUIRED**



| Shell Size | Max. Recommended Torque (Inch Pounds) | A Dia. Max.  | B Dia. Max.  | C Dim. Max.  |
|------------|---------------------------------------|--------------|--------------|--------------|
| 09         | 40                                    | .577 (14.7)  | .438 (11.1)  | 1.031 (26.2) |
| 11         | 40                                    | .709 (18.0)  | .566 (14.4)  | 1.031 (26.2) |
| 13         | 40                                    | .829 (21.1)  | .678 (17.2)  | 1.031 (26.2) |
| 15         | 40                                    | .954 (24.2)  | .803 (20.4)  | 1.031 (26.2) |
| 17         | 40                                    | 1.107 (28.1) | .928 (23.6)  | 1.031 (26.2) |
| 19         | 40                                    | 1.190 (30.2) | 1.033 (26.2) | 1.031 (26.2) |
| 21         | 80                                    | 1.315 (33.4) | 1.158 (29.4) | 1.031 (26.2) |
| 23         | 80                                    | 1.440 (36.6) | 1.283 (32.6) | 1.031 (26.2) |
| 25         | 80                                    | 1.565 (39.8) | 1.408 (35.8) | 1.031 (26.2) |

**APPLICATION NOTES**

1. Metric dimensions (mm) are indicated in parentheses.
2. Material: Case hardened carbon steel with electroless nickel finish.
3. Receptacle and plug holder drives: 1/4" - Shell sizes 08, 10, 12; 3/8" - Shell sizes 14 and up.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[600F005-11P](#) [600F005-11R](#) [600F005-15P](#) [600F005-15R](#) [600F005-17P](#) [600F005-17R](#)