

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AD	00		B1	ECO-07-005143	10JUL2007	RB DR

D



C

B

A




RECOMMENDED HOLE LAYOUT
TOLERANCE: ±.002
UNLESS OTHERWISE NOTED



NOTES:

1. MATERIALS:
CONTACT: COPPER ALLOY, .000180 MIN TIN PLATE
OVER .000050 MIN NICKEL.
INSULATOR: PPS, 40% GLASS FILLED, UL 94V-0
2. ELECTRICAL:
CURRENT CAPACITY: 1 AMP.
LOW LEVEL CONTACT RESISTANCE: 30 MILLIOHMS MAX.
CAPACITANCE (CONTACT TO CONTACT: 1 pF MAX.
@ 1kHz, MIL-STD-202, METHOD 305.
DIELECTRIC WITHSTANDING VOLTAGE: 600 VAC PER
MIL-STD-1344, METHOD 3001.1.
3. MECHANICAL:
FORCE, INSERTION: 310g MAX. PER LINE.
FORCE, WITHDRAWAL: 31g MIN. PER LINE.
FORCE, NORMAL: 200g MIN. PER LINE.
4. ENVIRONMENTAL:
OPERATING TEMPERATURE: -67°F TO +221°F
(-55°C TO +105°C.)
STORAGE TEMPERATURE: -67°F TO +221°F
(-55°C TO +105°C.)
5. INTERPRET DRAWING PER ASME Y14.5M-1994.
6. DATE CODE (PER BELOW) TO BE LASER CODED
AND CENTERED ON THIS SURFACE.



7. UL RECOGNITION E28476.

PART NO.	POS.	DIM "A"	DIM "B"	DIM "C"	DIM "D"	DIM "E"	DIM "F"
1571539-1	20	.590	.360	.200	.400	.390	.105
1571539-2	28	.690	.460	.300	.500	.490	.105

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. MURREN 25AUG03	Tyco Electronics Corporation Harrisburg, Pa. 17105			
DIMENSIONS: INCHES		CHK K. WRIGHT 24APR03				
		APVD K. WRIGHT 24APR03	NAME OUTLINE DRAWING PLCC SOCKET			
		PRODUCT SPEC				
MATERIAL		APPLICATION SPEC	SIZE A2	CAGE CODE 00779	DRAWING NO C=1571539	RESTRICTED TO -
		FINISH	WEIGHT	SCALE 3:1	SHEET 1 OF 1	REV B1
1		1	CUSTOMER DRAWING			