




Metallized Polyester Film Capacitor

series for 105°C (Electrical Appliance and Material Safety Law (Japan) approved for AC power source)


- Highly reliable and superior in high frequency applications, self-healing and non-inductive construction, using a dielectric of metallized polyester film.
- Finished by inner dipping, with liquid epoxy resin and outer coating with flame-retardant epoxy resin, those double coatings provide excellent humidity resistance.
- Designed in a small and compact size, but yet with higher capacitance, for high density mounting.
- Adapted to the RoHS directive (2002/95/EC).



## ■ Specifications

Item	Performance Characteristics
Category Temperature Range	-40 ~ +105°C
Rated Voltage	125, 250VAC
Rated Capacitance Range	Safety performance A1 0.01 ~ 0.47μF Safety performance C1 0.01 ~ 1.0μF
Capacitance Tolerance	±10% (K)
Dielectric Loss Tangent	1.0% or less (at 1kHz 20°C)
Insulation Resistance	C ≤ 0.47μF 2000 MΩ or more C > 0.47μF 1000 ΩF or more
Withstand Voltage	Between Terminals : Rated Voltage × 2.3VAC 1min. (Safety performance : A1) Between Terminals Coverage : (Rated Voltage 125VAC) 1000VAC 1 min. (Rated Voltage 250VAC) 1500VAC 1 min.
Encapsulation	Flame-retardant epoxy resin

Type numbering system (Example : 250VAC 0.1μF)




## ■ Safety performance

Symbol	A1		C1	
	Connected with load in parallel	Connected with load in series	Connected with load in parallel	Connected with load in series
Connecting Condition				
Capacitance	0.01 ~ 0.47μF		0.1 ~ 1.0μF	

Note : When using capacitors as an across-the-line capacitor, at least either one of the conditions shown below has to be fulfilled:

- 1) A varistor of 2 times or below of rated voltage shall be connected with a capacitor in parallel.
- 2) Pulse of higher than rated voltage × 2 shall not be applied to both terminals of capacitor.

## ■ Drawing



## ■ Dimensions

Unit : mm

Cap.(μF)	V(Code)	125VAC (2B)						250VAC (2E)					
		T	W	H	d	P	F	T	W	H	d	P	F
0.01	103							4.4	13.5	9.5	0.6	10.0	10.0
0.015	153							4.7	13.5	9.8	0.6	10.0	10.0
0.022	223	4.3	11.0	7.9	0.6	7.5	7.5	5.1	13.5	10.8	0.6	10.0	10.0
0.033	333	4.6	11.0	8.2	0.6	7.5	7.5	5.9	13.5	11.6	0.6	10.0	10.0
0.047	473	5.1	11.0	8.8	0.6	7.5	7.5	6.4	13.5	13.7	0.6	10.0	10.0
0.068	683	5.8	11.0	9.5	0.6	7.5	7.5	5.8	18.5	11.5	0.6	15.0	15.0
0.1	104	6.8	11.0	10.4	0.6	7.5	7.5	6.4	18.5	13.7	0.6	15.0	15.0
0.15	154	6.5	13.5	11.1	0.6	10.0	10.0	7.1	18.5	15.9	0.6	15.0	15.0
0.22	224	7.6	13.5	12.2	0.6	10.0	10.0	9.6	18.5	15.3	0.6	15.0	15.0
0.33	334	6.7	18.5	11.9	0.6	15.0	15.0	7.9	25.5	16.7	0.8	22.5	22.5
0.47	474	7.7	18.5	12.9	0.6	15.0	15.0	9.4	25.5	18.2	0.8	22.5	22.5
0.68	684	9.1	18.5	14.3	0.6	15.0	15.0						
1.0	105	8.0	25.5	15.3	0.8	22.5	22.5						

F : lead pitch for cut / formed lead wires.

\* We can also custom-make. 125VAC (2B) ~ 3.3μF

Please contact us and let us know the specification you need.