

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

	DIST
--	------

REVISIONS

G

14

	F
--	---

LTR

DESCRIPTION

DATE _____

	DWN
--	-----

	APVD
--	------

02

REV PER ECR 07-020486


28AUG07

JR

TM


AMP
WIRE RANGE

22 AWG
SOLID OR STRANDED



- 1 STAMP AMP 22, LOCATE APPROX AS SHOWN.
- 2 WIRE INSULATION DIA IS 0.9-2.5 [0.035-.100]
- 3 TONGUE MATERIAL THK IS 0.79±0.05 [0.031±.002]
- 4 DIMENSION APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- 5 MATERIAL: BODY-COPPER PER ASTM B-152
SLEEVE-NYLON, BLACK
- 6 FINISH: BODY-TIN PLATE PER ASTM B-545
- 7 MAX RECOMMENDED OPERATING 105°C
- 8 VOLTAGE RATING 300V MAX
- 9 CIRCULAR MIL AREA 0.26-0.41mm² [509-810] CMA.

500	LOOSE PIECE	151440
QTY	PACKAGE TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 09MAY06		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		CHK T MICHELUTTI 09MAY06		TERMINAL, RING TONGUE, PIDG, WIRE SIZE: 22 AWG —	
		APVD T MICHELUTTI 09MAY06			
		PRODUCT SPEC —			
		APPLICATION SPEC —		SIZE	CAGE CODE
MATERIAL		WEIGHT —		DRAWING NO	
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± 5°		FINISH		RESTRICTED TO	
— 		— 		A3 00779 C-151440	
CUSTOMER DRAWING				SCALE 8:1	SHEET 1 OF 1
				REV	02