





NOTES:

- MATERIALS AND FINISHES:
BODY - BRASS, NICKEL PLATING
BAYONET - ZINC DIECAST, NICKEL PLATING
CONTACT - BRASS, GOLD PLATING
INSULATOR - PTFE
- ELECTRICAL:
A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC 0-4 GHz
C. VSWR(RETURN LOSS): 1.3 (17.7 dB), MAX.
D. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.
- MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: - 65°C to +165°C
- CRIMPED FERRULE
HEX CRIMP SIZE .429"
- CRIMPED CONTACT PIN
HEX CRIMP SIZE .116"

31-5998-RFX

REVISIONS

PART NO.	REV	DESCRIPTION	DATE	ECO	APPR
THIRD ANGLE PROJ.	C	BAYONET WAS BRASS	7/13/06	46154	GH

RECOMMENDED
CABLE STRIPPING DIM'S

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
0.5 - 6mm ±0.1mm
6 - 30mm ±0.2mm
30 - 120mm ±0.3mm
ANGLES ±1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL

REFERENCE

FINISH

DRAWN
GARRA

ENGINEER

APPROVED

CAD FILE

F:\DWG\B\112186\9913-50\NT3G-ASZ

DATE
23-Jun-06DATE
23-Jun-06DATE
7/13/06

TITLE

BNC CRIMP PLUG
(FOR BELDEN 8214,9913,9914)

SCALE: 3/1

DWG SIZE
B

SHEET 2 OF 2

CODE ID
74868

REV

C

Amphenol RF

Donbury CT USA, Tainan Taiwan, Shenzhen China
www.amphenolrf.com

DRAWING NO. B112186-NT3G-9913-50

ITEM NO. 011121ALL93NA5F

PART NO. 31-5998-RFX