

System No. N/A		MDSM-4R		D10-5277																																													
<table><tr><th colspan="4">ELECTRICAL RATINGS</th></tr><tr><th>CONTACT FORM</th><th colspan="2">WATTS</th><th>A</th></tr><tr><td>CONTACT RATING</td><td colspan="2"></td><td>10</td></tr><tr><td>RATING SENSITIVITY</td><td>AMPERE</td><td>URNS</td><td>20</td></tr><tr><td rowspan="3">VOLTAGE</td><td>SWITCHING</td><td>VDC-MAX.</td><td>200</td></tr><tr><td>BREAKDOWN</td><td>VDC-MIN.</td><td>250</td></tr><tr><td>ARC-QUENCH</td><td>VDC-MIN.</td><td>200</td></tr><tr><td rowspan="2">CURRENT</td><td>SWITCHING</td><td>AMPERES-MAX.</td><td>0.5</td></tr><tr><td>CARRY</td><td>AMPERES-MAX.</td><td>1.2</td></tr><tr><td rowspan="2">RESISTANCE</td><td>CONTACT, INITIAL</td><td>OHMS-MAX.</td><td>0.10</td></tr><tr><td>INSULATION</td><td>OHMS-MIN.</td><td>10¹⁰</td></tr><tr><td>CAPACITANCE</td><td colspan="2">PICOFARADS-TYP.</td><td>0.2</td></tr></table>				ELECTRICAL RATINGS				CONTACT FORM	WATTS		A	CONTACT RATING			10	RATING SENSITIVITY	AMPERE	URNS	20	VOLTAGE	SWITCHING	VDC-MAX.	200	BREAKDOWN	VDC-MIN.	250	ARC-QUENCH	VDC-MIN.	200	CURRENT	SWITCHING	AMPERES-MAX.	0.5	CARRY	AMPERES-MAX.	1.2	RESISTANCE	CONTACT, INITIAL	OHMS-MAX.	0.10	INSULATION	OHMS-MIN.	10 ¹⁰	CAPACITANCE	PICOFARADS-TYP.		0.2	SEE REED SWITCH CATALOG FOR DEFINITION OF TERMS	
ELECTRICAL RATINGS																																																	
CONTACT FORM	WATTS		A																																														
CONTACT RATING			10																																														
RATING SENSITIVITY	AMPERE	URNS	20																																														
VOLTAGE	SWITCHING	VDC-MAX.	200																																														
	BREAKDOWN	VDC-MIN.	250																																														
	ARC-QUENCH	VDC-MIN.	200																																														
CURRENT	SWITCHING	AMPERES-MAX.	0.5																																														
	CARRY	AMPERES-MAX.	1.2																																														
RESISTANCE	CONTACT, INITIAL	OHMS-MAX.	0.10																																														
	INSULATION	OHMS-MIN.	10 ¹⁰																																														
CAPACITANCE	PICOFARADS-TYP.		0.2																																														
TIN PLATED LEADS				<table><tr><th colspan="2">OPERATING CHARACTERISTICS</th></tr><tr><td>OPERATE TIME</td><td>ms-MAX. 0.5</td></tr><tr><td>RELEASE TIME</td><td>ms-MAX. 0.2</td></tr><tr><td>SHOCK</td><td>G'S MAX., 11ms 1/2 SINE WAVE 100</td></tr><tr><td>VIBRATION</td><td>G'S MAX., 50-2000 HERTZ 30</td></tr><tr><td>RESONANT FREQUENCY</td><td>HERTZ, TYP. 3900</td></tr><tr><td>TEMPERATURE</td><td>OPERATING DEGREES, CELSIUS -40 TO +125</td></tr><tr><td></td><td>STORAGE DEGREES, CELSIUS -65 TO +125</td></tr></table>		OPERATING CHARACTERISTICS		OPERATE TIME	ms-MAX. 0.5	RELEASE TIME	ms-MAX. 0.2	SHOCK	G'S MAX., 11ms 1/2 SINE WAVE 100	VIBRATION	G'S MAX., 50-2000 HERTZ 30	RESONANT FREQUENCY	HERTZ, TYP. 3900	TEMPERATURE	OPERATING DEGREES, CELSIUS -40 TO +125		STORAGE DEGREES, CELSIUS -65 TO +125																												
OPERATING CHARACTERISTICS																																																	
OPERATE TIME	ms-MAX. 0.5																																																
RELEASE TIME	ms-MAX. 0.2																																																
SHOCK	G'S MAX., 11ms 1/2 SINE WAVE 100																																																
VIBRATION	G'S MAX., 50-2000 HERTZ 30																																																
RESONANT FREQUENCY	HERTZ, TYP. 3900																																																
TEMPERATURE	OPERATING DEGREES, CELSIUS -40 TO +125																																																
	STORAGE DEGREES, CELSIUS -65 TO +125																																																
				<table><tr><th colspan="2">MAGNETIC CHARACTERISTICS</th></tr><tr><td>TEST COIL</td><td>L4989</td></tr><tr><td>STANDARD TOLERANCE</td><td>AMPERE TURNS 12-23</td></tr><tr><td>PULL-IN RANGES BEFORE MOD.</td><td>17-28</td></tr><tr><td></td><td>22-33</td></tr><tr><td></td><td>27-38</td></tr></table>		MAGNETIC CHARACTERISTICS		TEST COIL	L4989	STANDARD TOLERANCE	AMPERE TURNS 12-23	PULL-IN RANGES BEFORE MOD.	17-28		22-33		27-38																																
MAGNETIC CHARACTERISTICS																																																	
TEST COIL	L4989																																																
STANDARD TOLERANCE	AMPERE TURNS 12-23																																																
PULL-IN RANGES BEFORE MOD.	17-28																																																
	22-33																																																
	27-38																																																
© HAMLIN, Incorporated 1996 This design and print is copyright and is the property of HAMLIN, Inc. It must not be copied or permitted to be copied, nor may its contents be divulged to any third party without the prior written permission from the company.				PACKAGING TAPE AND REEL -3000/REEL SEE PAGE 2 OF 2 FOR TAPE AND REEL DETAIL.																																													
HAMLIN, Inc.				DCR No. A5406																																													
AD	ADD DIM TO OUTSIDE LEG FORM	A9340	GJ	11/5/01	GJ	11/7/01																																											
REV.	DESCRIPTION OF REVISION	DCR No.	BY	DATE	APP.	DATE																																											

