

Midget Fuse, 10.3 x 38 mm, 1000 VDC, Photovoltaic, gPV

new



Standard

PCB version

1000VDC · gPV



Description

- Meets the new UL and IEC photovoltaic standards
- UL Recognized for 1000 VDC
- High breaking capacity of 20 kA @ 1000 VDC
- Low min. interrupting rating of 1.35 x In
- Meets the requirements of IEC 61730-2 for PV module safety

Standards

- IEC 60269-6
- UL 2579

Approvals

- VDE Certificate Number: 40033592
- UL File Number: E345791

Applications

- All photovoltaic applications
- Inverters
- Battery charge controllers
- In-line protection
- String fuse

References

Corresponding Fuseholder [FSO](#); [CSO](#); [231660](#)

Corresponding Cover [ESO 10.3x38](#)

Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Accessories](#), [Detailed request for product](#)

Technical Data



Rated Voltage	1000VDC
Rated current	1 - 30A
Breaking Capacity	20kA
Characteristic	gPV
Mounting	Insert, PCB/THT
Admissible Ambient Air Temp.	-50 °C to 125 °C
Unit Weight	8.3 g
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	 Type, Current, Rated voltage, Breaking Capacity, Characteristic, Approvals

Dimension


Standard

10.3 mm

PCB




Derating Curves



Pre-Arcing Time

Rated Current I_n	$1.0 \times I_n$ min.	$1.13 \times I_n$ min.	$1.35 \times I_n$ min.	$1.45 \times I_n$ max.	$2.0 \times I_n$ max.
1 A - 30 A	60 min	60 min	60 min	60 min	4 min

Time-Current-Curves



Variants

Rated Current [A]	Mounting	Rated Voltage [VDC]	Breaking Capacity	Power Dissipation 1.0 I _n typ. [mW]	Melting I ² t 20 kA typ. [A²s]			Order Number	
1	Standard	1000	1)	602	0.554	●	●	0090.0001	■
2	Standard	1000	1)	1586	4.755	●	●	0090.0002	■
3	Standard	1000	1)	1504	7.882	●	●	0090.0003	■
4	Standard	1000	1)	1491	23.03	●	●	0090.0004	■
5	Standard	1000	1)	1465	42.6	●	●	0090.0005	■
6	Standard	1000	1)	1348	80.25	●	●	0090.0006	■
8	Standard	1000	1)	1610	199	●	●	0090.0008	■
10	Standard	1000	1)	1760	401	●	●	0090.0010	■
12	Standard	1000	1)	1965	642	●	●	0090.0012	■
15	Standard	1000	1)	1914	505	●	●	0090.0015	■
20	Standard	1000	1)	2810	1313	●	●	0090.0020	■
25	Standard	1000	1)	2981	2371	●	●	0090.0025	■
30	Standard	1000	1)	3923	2679	●	●	0090.0030	■
1	PCB	1000	1)	602	0.554	●	●	0090.1001	
2	PCB	1000	1)	1586	4.755	●	●	0090.1002	
3	PCB	1000	1)	1504	7.882	●	●	0090.1003	
4	PCB	1000	1)	1491	23.03	●	●	0090.1004	
5	PCB	1000	1)	1465	42.6	●	●	0090.1005	
6	PCB	1000	1)	1348	80.25	●	●	0090.1006	
8	PCB	1000	1)	1610	199	●	●	0090.1008	
10	PCB	1000	1)	1760	401	●	●	0090.1010	
12	PCB	1000	1)	1965	642	●	●	0090.1012	
15	PCB	1000	1)	1914	505	●	●	0090.1015	
20	PCB	1000	1)	2810	1313	●	●	0090.1020	
25	PCB	1000	1)	2981	2371	●	●	0090.1025	
30	PCB	1000	1)	3923	2679	●	●	0090.1030	

■ Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

1) 20 kA @ 1000 VDC, L/R < 2ms

Packaging Unit	Standard version	Bulk (10 pcs.)
	PCB version	Bulk (100 pcs.)

Zubehör

Description



ESO 10.3x38
Fuse Inserter/Extraktor with Cover Function for 10.3x38 mm Fuses in Clips