

HZU-L Series

Silicon Epitaxial Planar Zener Diode for Low Noise Application

REJ03G0043-0300Z

Rev.3.00

Jul.28.2004


Features

- Diode noise level of this series is approximately 1/3-1/10 lower than the HZ series.
- Low leakage and low zener impedance.
- Wide spectrum from 5.2V through 38V of zener voltage provide flexible application.
- Ultra small Resin Package (URP) is suitable for surface mount design.

Ordering Information

Type No.	Laser Mark	Package Code
HZU-L Series	Type No.	URP

Pin Arrangement



Absolute Maximum Ratings

(Ta = 25°C)

Item	Symbol	Value	Unit
Power dissipation	Pd	150	mW
Junction temperature	Tj	150	°C
Storage temperature	Tstg	-55 to +150	°C

Electrical Characteristics

(Ta = 25°C)

Type	Grade	Zener Voltage		Reverse Current		Dynamic Resistance		ESD-Capability	
		V _Z (V)* ¹		Test Condition	I _R (μA)	Test Condition	r _d (Ω)	Test Condition	(V) * ²
		Min	Max	I _Z (mA)	Max	V _R (V)	Max	I _Z (mA)	Min
HZU6L	A1	5.2	5.5	0.5	1	2.0	150	0.5	200
	A2	5.3	5.6						
	A3	5.4	5.7						
	B1	5.5	5.8				80	0.5	
	B2	5.6	5.9						
	B3	5.7	6.0						
	C1	5.8	6.1				60	0.5	
	C2	6.0	6.3						
	C3	6.1	6.4						
HZU7L	A1	6.3	6.6	0.5	1	3.5	60	0.5	200
	A2	6.4	6.7						
	A3	6.6	6.9						
	B1	6.7	7.0						
	B2	6.9	7.2						
	B3	7.0	7.3						
	C1	7.2	7.6						
	C2	7.3	7.7						
	C3	7.5	7.9						
HZU9L	A1	7.7	8.1	0.5	1	6.0	60	0.5	200
	A2	7.9	8.3						
	A3	8.1	8.5						
	B1	8.3	8.7						
	B2	8.5	8.9						
	B3	8.7	9.1						
	C1	8.9	9.3						
	C2	9.1	9.5						
	C3	9.3	9.7						
HZU11L	A1	9.5	9.9	0.5	1	8.0	80	0.5	200
	A2	9.7	10.1						
	A3	9.9	10.3						
	B1	10.2	10.6						
	B2	10.4	10.8						
	B3	10.7	11.1						

Notes: 1. Tested with DC.

2. C = 200 pF, R = 0 Ω, Both forward and reverse direction 1 pulse.
Failure criterion ; According to IR spec.

Type	Grade	Zener Voltage		Test Condition	Reverse Current		Dynamic Resistance		ESD-Capability
		V _Z (V)* ¹			I _R (μA)	Test Condition	r _d (Ω)	Test Condition	(V) * ²
		Min	Max	I _Z (mA)	Max	V _R (V)	Max	I _Z (mA)	Min
HZU11L	C1	10.9	11.3	0.5	1	8.0	80	0.5	200
	C2	11.1	11.6						
	C3	11.4	11.9						
HZU12L	A1	11.6	12.1	0.5	1	10.5	80	0.5	200
	A2	11.9	12.4						
	A3	12.2	12.7						
	B1	12.4	12.9						
	B2	12.6	13.1						
	B3	12.9	13.4						
	C1	13.2	13.7						
	C2	13.5	14.0						
	C3	13.8	14.3						
HZU15L	−1	14.1	14.7	0.5	1	13.0	80	0.5	200
	−2	14.5	15.1						
	−3	14.9	15.5						
HZU16L	−1	15.3	15.9	0.5	1	14.0	80	0.5	200
	−2	15.7	16.5						
	−3	16.3	17.1						
HZU18L	−1	16.9	17.7	0.5	1	15.0	80	0.5	200
	−2	17.5	18.3						
	−3	18.1	19.0						
HZU20L	−1	18.8	19.7	0.5	1	18.0	100	0.5	200
	−2	19.5	20.4						
	−3	20.2	21.1						
HZU22L	−1	20.9	21.9	0.5	1	20.0	100	0.5	200
	−2	21.6	22.6						
	−3	22.3	23.3						
HZU24L	−1	22.9	24.0	0.5	1	22.0	120	0.5	200
	−2	23.6	24.7						
	−3	24.3	25.5						
HZU27L	−1	25.2	26.6	0.5	1	24.0	150	0.5	200
	−2	26.2	27.6						
	−3	27.2	28.6						
HZU30L	−1	28.2	29.6	0.5	1	27.0	200	0.5	200
	−2	29.2	30.6						
	−3	30.2	31.6						
HZU33L	−1	31.2	32.6	0.5	1	30.0	250	0.5	200
	−2	32.2	33.6						
	−3	33.2	34.6						
HZU36L	−1	34.2	35.7	0.5	1	33.0	300	0.5	200
	−2	35.3	36.8						
	−3	36.4	38.0						

Notes: 1. Tested with DC.



2. C = 200 pF, R = 0 Ω, Both forward and reverse direction 1 pulse.
Failure criterion ; According to IR spec.

Mark Code

Type	Grade	Mark No.	Type	Grade	Mark No.	Type	Grade	Mark No.
HZU6L	A1	061	HZU11L	A1	111	HZU20L	-1	201
	A2	062		A2	112		-2	202
	A3	063		A3	113		-3	203
	B1	064		B1	114	HZU22L	-1	221
	B2	065		B2	115		-2	222
	B3	066		B3	116		-3	223
	C1	067		C1	117	HZU24L	-1	241
	C2	068		C2	118		-2	242
	C3	069		C3	119		-3	243
HZU7L	A1	071	HZU12L	A1	121	HZU27L	-1	271
	A2	072		A2	122		-2	272
	A3	073		A3	123		-3	273
	B1	074		B1	124	HZU30L	-1	301
	B2	075		B2	125		-2	302
	B3	076		B3	126		-3	303
	C1	077		C1	127	HZU33L	-1	331
	C2	078		C2	128		-2	332
	C3	079		C3	129		-3	333
HZU9L	A1	091	HZU15L	-1	151	HZU36L	-1	361
	A2	092		-2	152		-2	362
	A3	093		-3	153		-3	363
	B1	094	HZU16L	-1	161			
	B2	095		-2	162			
	B3	096		-3	163			
	C1	097	HZU18L	-1	181			
	C2	098		-2	182			
	C3	099		-3	183			

Notes: 1. Example of Marking

(1) HZU6A1L to HZU9C3L Example of Marking (2) HZU11A1L to HZU36-3L Example of Marking



2. Type No. is as follows; HZU6A1L, HZU6A2L, ... HZU12C3L
3. Type No. is as follows; HZU15 - 1L, HZU15 - 2L, ... HZU36 - 3L

Main Characteristic




Fig.1 Zener current vs. Zener voltage




Fig.2 Temperature Coefficient vs. Zener voltage





Fig.3 Power Dissipation vs. Ambient Temperature

Package Dimensions

As of January, 2003
Unit: mm



Package Code	URP
JEDEC	Conforms
JEITA	—
Mass (reference value)	0.004 g

Renesas Technology Corp. Sales Strategic Planning Div. Nippon Bldg., 2-6-2, Ohte-machi, Chiyoda-ku, Tokyo 100-0004, Japan

Keep safety first in your circuit designs!

1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage.
Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. or a third party.
2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors.
Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corp. semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.



RENESAS SALES OFFICES

<http://www.renesas.com>

Renesas Technology America, Inc.

450 Holger Way, San Jose, CA 95134-1368, U.S.A
Tel: <1> (408) 382-7500 Fax: <1> (408) 382-7501

Renesas Technology Europe Limited.

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, United Kingdom
Tel: <44> (1628) 585 100, Fax: <44> (1628) 585 900

Renesas Technology Europe GmbH

Dornacher Str. 3, D-85622 Feldkirchen, Germany
Tel: <49> (89) 380 70 0, Fax: <49> (89) 929 30 11

Renesas Technology Hong Kong Ltd.

7/F., North Tower, World Finance Centre, Harbour City, Canton Road, Hong Kong
Tel: <852> 2265-6688, Fax: <852> 2375-6836

Renesas Technology Taiwan Co., Ltd.

FL 10, #99, Fu-Hsing N. Rd., Taipei, Taiwan
Tel: <886> (2) 2715-2888, Fax: <886> (2) 2713-2999

Renesas Technology (Shanghai) Co., Ltd.

26/F., Ruijin Building, No.205 Maoming Road (S), Shanghai 200020, China
Tel: <86> (21) 6472-1001, Fax: <86> (21) 6415-2952

Renesas Technology Singapore Pte. Ltd.

1, Harbour Front Avenue, #06-10, Keppel Bay Tower, Singapore 098632
Tel: <65> 6213-0200, Fax: <65> 6278-8001