

ADHESIVE BACKING
PRESSURE SENSITIVE
FOAM .040 (1.0) THICK
WITH PROTECTIVE LINER.

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
2. PART IS DESIGNED TO SUPPORT MAXIMUM WEIGHT ON A CLEAN, DRY, SMOOTH SURFACE. SEE TABLE.

Technical drawing of a cross-section of a mechanical part. The drawing shows a profile with a rounded top and a complex internal feature. Dimensions are indicated with arrows and text:

- Top horizontal dimension: 0.47 (11.9) REF.
- Internal horizontal dimension: REF. 0.62
- Bottom horizontal dimension: 0.78

G00430BB_PB_LC3_A_02

TINLEY PARK, ILLINOIS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.05 (1.3) (.XXX) ± 0.010 (0.25)
(.XX) ± 0.02 (0.5) ANGLES $\pm 5^\circ$

AT'L:

RIGID PVC

A
SIZE

													PANDUIT CORP.	TINLEY PARK, ILLINOIS
													LATCHING CLIP (LC3-A)	
2	6-29-01	LGG		UPDATED AND ADDED REF.	GB0430BB	2							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (.XX) ±0.02 (0.5) ANGLES ±5°	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
1	6-2-98	MLD		MADE OVERALL HEIGHT DIM A REF. DIM	GB0430BB	1								
				CHANGED CAD FILE NAME FROM GB0430BB_PB_LC3_A_00								DRAWN BY SJSU	MAT'L:	SCALE NONE
R	03/29/94	SJSU		INITIAL RELEASE	GB0430BB	R						DATE 03/29/94	RIGID PVC	DRAWING NO. GB0430BB
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP					CHK'D		DWG A SIZE