


REV. V

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED	TOLERANCES ARE:
ONE PLACE DECIMALS $\pm .1$	THREE PLACE DECIMALS $\pm .005$	ANGLES	$\pm 2^\circ$
TWO PLACE DECIMALS $\pm .01$	FOUR PLACE DECIMALS $\pm .0020$		

TITLE: ZSS-ASSEMBLY

 DWG NO: ZSS-1XX-XX-XXX-X-XXXX-XX-XX
 SHEET 1 OF 1

 ZSS-1XX-XX-XXX-X-XXXX-XX-XX
 NO. OF POSITIONS
 (02 THRU 18, 20, 24,
 22, 25, 28, 30, 32, 36)

 LEAD STYLE
 SEE TABLE 1

PLATING OPTION



- G: 10 μ " GOLD IN CONTACT AREA, 3 μ " GOLD ON TAIL
- T: MATTE TIN CONTACT AND TAIL
- S: 30 μ " SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- H: 30 μ " GOLD IN CONTACT AREA, 3 μ " GOLD ON TAIL
- L: 10 μ " SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- F: 3 μ " SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- STL: 30 μ " SELECTIVE GOLD IN CONTACT AREA, (90/10 $\pm$ 5%) TAIL
 (ONLY AVAILABLE IN -06 LEAD STYLE)

 POLARIZED OPTION
 SPECIFY POSITION TO
 BE REMOVED (XX)
 OPTION
 -LL: LOCKING LEAD
 (SEE SECT. 'A-A' & FIG. 1)
 STACKING HEIGHT
 .450 MIN. STACKING HEIGHT
 (.535 MIN. BOARD SPACING
 WHEN MATED WITH SAMTEC SSW)


 ROW OPTION
 -D DOUBLE
 -S SINGLE

TABLE 1

LEAD STYLE	TERMINAL	MAX. STACKING HEIGHT	"A"
-01	T-1S6-15-XX-2	.540	.630
-02	T-1S6-09-XX-2	.640	.730
-03	T-1S6-10-XX-2	.740	.830
-04	T-1S6-11-XX-2	.840	.930
-05	T-1S6-12-XX-2	.940	1.030
-06	T-1S6-20-XX-2	1.040	1.130
-07	T-1S6-13-XX-2	1.140	1.230
-08	T-1S6-19-XX-2	1.240	1.330
-09	T-1S6-14-XX-2	1.340	1.430




DO NOT SCALE FROM THIS PRINT

 SINGLE -LL
 FIG. 1
 DOUBLE -LL

PROPRIETARY NOTE
 THIS DOCUMENT CONTAINS INFORMATION
 CONFIDENTIAL AND PROPRIETARY TO
 SAMTEC INC. AND SHALL NOT BE
 REPRODUCED OR TRANSMITTED IN
 ANY FORM OR BY ANY MEANS, ELECTRONIC
 OR MECHANICAL, INCLUDING PHOTOCOPYING,
 RECORDING, OR BY ANY INFORMATION
 STORAGE AND RETRIEVAL SYSTEM, WITHOUT
 THE WRITTEN CONSENT OF SAMTEC INC.

NOTES:

1. TERMINAL PUSHOUT FORCE 3 LBS.
2. ASSEMBLY GOLD PLATE END AS SHOWN.
3. (Ⓢ) REPRESENTS CRITICAL DIMENSION FOR STATISTICAL PROCESS CONTROL.
4. TERMINALS TO BE FLUSH TO .010 BELOW TOP OF SHROUD.
5. INSULATOR MATERIALS: PBT, UL 94 V0
6. FOR ADDED MECHANICAL STABILITY, SAMTEC RECOMMENDS MECHANICAL BOARD SPACERS BE USED IN APPLICATIONS WITH GOLD OR SELECTIVE GOLD PLATED CONNECTORS. CONTACT IPG@SAMTEC.COM FOR MORE INFORMATION.



SECTION A-A

samtec
MISC/UKCTO
ZSS-MKT
 520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
 PHONE (812) 944-6733 P.O. BOX 1147
 CODE 55322

MADE BY: TIM PLUMMER

 ZSS-1XX-XX-XXX-X-XXXX-XX-XX
 SHEET 1 OF 1