




D

C

B

A



- 1

POLYOLEFIN, BLACK.
- 2

NYLON, BLACK.
- 3

NOMINAL WALL THICKNESS, EXPANDED.
- 4

LENGTH OF SEALANT.
- 5

EXPANDED INSIDE DIAMETER.
- 6

12.70[.500] MAXIMUM RECOVERED INSIDE DIAMETER.
- 7

ASSEMBLY WILL PASS 0.0703 KG PER SQ CENTIMETER [ONE POUND PER SQ IN.] WATER PRESSURE TEST.
- 8

121°C [250°F] SHRINK TEMPERATURE.
- 9

-55°C TO 110°C [-67°F TO 230°F] OPERATING TEMPERATURE.
- 10

THIS PART WILL ACCOMODATE $\varnothing$ 13.97 - $\varnothing$ 31.75 [$\varnothing$.550 - $\varnothing$ 1.250] CABLE RANGE.
- 11

NO SEALANT APPLIED.
- 12

ACTUAL SHAPE MAY VARY DUE TO PROCESS VARIANCE.
- 13

OBSOLETE PARTS.
- 14

SEE P/N CHART FOR MARKING. WHITE CHARACTERS .15 MIN HIGH AND LOCATED ON THE OUTSIDE SURFACE OF THE TUBING.
- 15

PRELIMINARY PART - NOT FOR PRODUCTION

TE 54012-7

MARKING DETAIL

13	TE 54012-7	1 3/8-18 UNEF-2B	54012-7
11 13	NONE	1 7/16-18 UNEF-2B	54012-6
11 13	NONE	1 3/8-18 UNEF-2B	54012-5
	NONE	1 7/16-18 UNEF-2B	54012-4
13	NONE	1 3/16-18 UNEF-2B	54012-3
	NONE	1 3/8-18 UNEF-2B	54012-1
MARKING		THREAD "A"	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.REIFSNYDER 10 APR 96		 TE Connectivity				
DIMENSIONS: INCHES		CHK R.STONE 15 APR 95						
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH -		APVD T.A.WETZEL 03 MAY 96		NAME STRAIN RELIEF ASSY, SHELL SIZE 23, CPC			
			PRODUCT SPEC —					
			APPLICATION SPEC —					
			—					
MATERIAL TUBING:  SLEEVE: 		WEIGHT —		SIZE A2	CAGE CODE 00779	DRAWING NO C=54012	RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 2:1	SHEET 1 of 1	REV W		

54012

B

A