




- NOTES:
1. MATERIALS AND FINISHES:
BODY - STAINLESS STEEL,PASSIVATED
HOUSING - BRASS, GOLD PLATING
CONTACT - BeCu, GOLD PLATING
INSULATOR - PTFE
2. ELECTRICAL:
A. IMPEDANCE : 50 OHM
B. FREQUENCY RANGE : DC - 12 GHz
C. VSWR : 1.25 MAX.
D. DIELECTRIC WITHSTANDING VOLTAGE : 500 VRMS, MIN.
3. MECHANICAL:
A. DURABILITY : 500 CYCLES MIN.
B. TEMPERATURE RANGE : -65° C TO +165° C
4. PACKAGING: SINGLE PACK, LABEL BAG & BOXES:
AMPHENOL RF P/N: SMP-MSLD-PCT-6
HARRIS P/N: J92-0001-050
HARRIS B.O.M. REV.: REV -
SUPPLIER CODE: 01002002
DATE CODE: WWYY

INTERFACE PER
MIL-STD-348
SERIES:SMP JACK LIMITED DETENT



REVISIONS				
REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	05-Nov-10'	--	BZ
B	SYNC ARFA AND DANBURY DRAWING	08-Jun-11'	48632	SCOTT
C	REDESIGN TO PREVENT RING BURR AND INTERNAL CHIPS AND ADDED CHAMFER ON HOUSING / RD-DMI3011501J6	11-Dec-12	49029	MJN
D	UPDATED NOTE 4: PACKAGING\RD-DMI3112001R3	03-Dec-13	49440	MJD



RECOMMENDED MOUNTING
HOLE DIMENSION

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES $\pm 0.05\text{mm}$ $\pm 0.1\text{mm}$ $\pm 0.2\text{mm}$ $\pm 0.3\text{mm}$ $\pm 1^\circ$	MATERIAL		DRAWN R. MAO	DATE 28-Nov-13	TITLE SMP JACK R/A LIMITED DETENT PCB MOUNT		Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com	
	REFERENCE EAR # 3786		ENGINEER A ARUN PRABU	DATE 30-Oct-09'				
	FINISH		APPROVED S. HSIEH	DATE 03-Dec-13	SCALE: 11.5:1.0	SHEET 2 OF 2	DRAWING NO. SMP-MSLD-PCT-6	ITEM NO. SMP-MSLD-PCT-6
			CAD FILE		DWG SIZE B	REV D	PART NO. SMP-MSLD-PCT-6	