

## Small Signal Zener Diodes



### FEATURES

- Very sharp reverse characteristic
- Low reverse current level
- Very high stability
- Low noise
- High reliability
- AEC-Q101 qualified
- Material categorization: For definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**

### PRIMARY CHARACTERISTICS

| PARAMETER             | VALUE         | UNIT |
|-----------------------|---------------|------|
| $V_Z$ range nom.      | 2.4 to 56     | V    |
| Test current $I_{ZT}$ | 5 to 20       | mA   |
| $V_Z$ specification   | Pulse current |      |
| Int. construction     | Single        |      |

### APPLICATIONS

- Voltage stabilization

### ORDERING INFORMATION

| DEVICE NAME | ORDERING CODE   | TAPED UNITS PER REEL           | MINIMUM ORDER QUANTITY |
|-------------|-----------------|--------------------------------|------------------------|
| TLZ-series  | TLZ-series-GS18 | 10 000 (8 mm tape on 13" reel) | 10 000/box             |
| TLZ-series  | TLZ-series-GS08 | 2500 (8 mm tape on 7" reel)    | 12 500/box             |

### PACKAGE

| PACKAGE NAME    | WEIGHT | MOLDING COMPOUND<br>FLAMMABILITY RATING | MOISTURE SENSITIVITY<br>LEVEL        | SOLDERING<br>CONDITIONS  |
|-----------------|--------|-----------------------------------------|--------------------------------------|--------------------------|
| MiniMELF SOD-80 | 31 mg  | -                                       | MSL level 1<br>(according J-STD-020) | 260 °C/10 s at terminals |

### ABSOLUTE MAXIMUM RATINGS ( $T_{amb} = 25\text{ °C}$ , unless otherwise specified)

| PARAMETER                 | TEST CONDITION                     | SYMBOL     | VALUE         | UNIT |
|---------------------------|------------------------------------|------------|---------------|------|
| Power dissipation         | $R_{thJA} \leq 300\text{ K/W}$     | $P_{tot}$  | 500           | mW   |
| Zener current             |                                    | $I_Z$      | $P_{tot}/V_Z$ | mA   |
| Junction to ambient air   | On PC board 50 mm x 50 mm x 1.6 mm | $R_{thJA}$ | 500           | K/W  |
| Junction temperature      |                                    | $T_j$      | 175           | °C   |
| Storage temperature range |                                    | $T_{stg}$  | - 65 to + 175 | °C   |
| Forward voltage (max.)    | $I_F = 200\text{ mA}$              | $V_F$      | 1.5           | V    |



| <b>ELECTRICAL CHARACTERISTICS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) |              |                     |      |       |              |           |                         |      |                    |                       |
|----------------------------------------------------------------------------------------------------------|--------------|---------------------|------|-------|--------------|-----------|-------------------------|------|--------------------|-----------------------|
| PART NUMBER                                                                                              | MARKING CODE | ZENER VOLTAGE RANGE |      |       | TEST CURRENT |           | REVERSE LEAKAGE CURRENT |      | DYNAMIC RESISTANCE |                       |
|                                                                                                          |              | $V_Z$ at $I_{ZT1}$  |      |       | $I_{ZT1}$    | $I_{ZT2}$ | $I_R$ at $V_R$          |      | $Z_Z$ at $I_{ZT1}$ | $Z_{ZK}$ at $I_{ZT2}$ |
|                                                                                                          |              | V                   |      |       | mA           |           | $\mu\text{A}$           | V    | $\Omega$           |                       |
|                                                                                                          |              | MIN.                | NOM. | MAX.  |              |           | MAX.                    |      | MAX.               | MAX.                  |
| TLZ2V4A                                                                                                  | 2A4          | 2.33                | 2.4  | 2.52  | 20           | 1         | 70                      | 1    | 100                | 2000                  |
| TLZ2V4B                                                                                                  | 2B4          | 2.43                | 2.4  | 2.63  | 20           | 1         | 70                      | 1    | 100                | 2000                  |
| TLZ2V7A                                                                                                  | 2A7          | 2.54                | 2.7  | 2.75  | 20           | 1         | 50                      | 1    | 100                | 1000                  |
| TLZ2V7B                                                                                                  | 2B7          | 2.69                | 2.7  | 2.91  | 20           | 1         | 50                      | 1    | 100                | 1000                  |
| TLZ3V0A                                                                                                  | 3A0          | 2.85                | 3.0  | 3.07  | 20           | 1         | 50                      | 1    | 80                 | 1000                  |
| TLZ3V0B                                                                                                  | 3B0          | 3.01                | 3.0  | 3.22  | 20           | 1         | 10                      | 1    | 80                 | 1000                  |
| TLZ3V3A                                                                                                  | 3A3          | 3.16                | 3.3  | 3.38  | 20           | 1         | 10                      | 1    | 70                 | 1000                  |
| TLZ3V3B                                                                                                  | 3B3          | 3.32                | 3.3  | 3.53  | 20           | 1         | 10                      | 1    | 70                 | 1000                  |
| TLZ3V6A                                                                                                  | 3A6          | 3.455               | 3.6  | 3.695 | 20           | 1         | 5                       | 1    | 60                 | 1000                  |
| TLZ3V6B                                                                                                  | 3B6          | 3.6                 | 3.6  | 3.845 | 20           | 1         | 5                       | 1    | 60                 | 1000                  |
| TLZ3V9A                                                                                                  | 3A9          | 3.74                | 3.9  | 4.01  | 20           | 1         | 3                       | 1    | 50                 | 1000                  |
| TLZ3V9B                                                                                                  | 3B9          | 3.89                | 3.9  | 4.16  | 20           | 1         | 3                       | 1    | 50                 | 1000                  |
| TLZ4V3A                                                                                                  | 4A3          | 4.04                | 4.3  | 4.29  | 20           | 1         | 3                       | 1    | 40                 | 1000                  |
| TLZ4V3B                                                                                                  | 4B3          | 4.17                | 4.3  | 4.43  | 20           | 1         | 3                       | 1    | 40                 | 1000                  |
| TLZ4V3C                                                                                                  | 4C3          | 4.3                 | 4.3  | 4.57  | 20           | 1         | 3                       | 1    | 40                 | 1000                  |
| TLZ4V7A                                                                                                  | 4A7          | 4.44                | 4.7  | 4.68  | 20           | 1         | 5                       | 1    | 25                 | 900                   |
| TLZ4V7B                                                                                                  | 4B7          | 4.55                | 4.7  | 4.8   | 20           | 1         | 5                       | 1    | 25                 | 900                   |
| TLZ4V7C                                                                                                  | 4C7          | 4.68                | 4.7  | 4.93  | 20           | 1         | 5                       | 1    | 25                 | 900                   |
| TLZ5V1A                                                                                                  | 5A1          | 4.81                | 5.1  | 5.07  | 20           | 1         | 2                       | 2    | 20                 | 800                   |
| TLZ5V1B                                                                                                  | 5B1          | 4.94                | 5.1  | 5.2   | 20           | 1         | 2                       | 2    | 20                 | 800                   |
| TLZ5V1C                                                                                                  | 5C1          | 5.09                | 5.1  | 5.37  | 20           | 1         | 2                       | 2    | 20                 | 800                   |
| TLZ5V6A                                                                                                  | 5A6          | 5.28                | 5.6  | 5.55  | 20           | 1         | 1                       | 2    | 13                 | 500                   |
| TLZ5V6B                                                                                                  | 5B6          | 5.45                | 5.6  | 5.73  | 20           | 1         | 1                       | 2    | 13                 | 500                   |
| TLZ5V6C                                                                                                  | 5C6          | 5.61                | 5.6  | 5.91  | 20           | 1         | 1                       | 2    | 13                 | 500                   |
| TLZ6V2A                                                                                                  | 6A2          | 5.78                | 6.2  | 6.09  | 20           | 1         | 3                       | 4    | 10                 | 300                   |
| TLZ6V2B                                                                                                  | 6B2          | 5.96                | 6.2  | 6.27  | 20           | 1         | 3                       | 4    | 10                 | 300                   |
| TLZ6V2C                                                                                                  | 6C2          | 6.12                | 6.2  | 6.44  | 20           | 1         | 3                       | 4    | 10                 | 300                   |
| TLZ6V8A                                                                                                  | 6A8          | 6.29                | 6.8  | 6.63  | 20           | 0.5       | 2                       | 4    | 8                  | 150                   |
| TLZ6V8B                                                                                                  | 6B8          | 6.49                | 6.8  | 6.83  | 20           | 0.5       | 2                       | 4    | 8                  | 150                   |
| TLZ6V8C                                                                                                  | 6C8          | 6.66                | 6.8  | 7.01  | 20           | 0.5       | 2                       | 4    | 8                  | 150                   |
| TLZ7V5A                                                                                                  | 7A5          | 6.85                | 7.5  | 7.22  | 20           | 0.5       | 3                       | 6.5  | 8                  | 120                   |
| TLZ7V5B                                                                                                  | 7B5          | 7.07                | 7.5  | 7.45  | 20           | 0.5       | 3                       | 6.73 | 8                  | 120                   |
| TLZ7V5C                                                                                                  | 7C5          | 7.29                | 7.5  | 7.67  | 20           | 0.5       | 3                       | 6.93 | 8                  | 120                   |
| TLZ8V2A                                                                                                  | 8A2          | 7.53                | 8.2  | 7.92  | 20           | 0.5       | 7.5                     | 7.15 | 8                  | 120                   |
| TLZ8V2B                                                                                                  | 8B2          | 7.78                | 8.2  | 8.19  | 20           | 0.5       | 7.5                     | 7.39 | 8                  | 120                   |
| TLZ8V2C                                                                                                  | 8C2          | 8.03                | 8.2  | 8.45  | 20           | 0.5       | 7.5                     | 7.63 | 8                  | 120                   |
| TLZ9V1A                                                                                                  | 9A1          | 8.29                | 9.1  | 8.73  | 20           | 0.5       | 0.04                    | 7.88 | 8                  | 120                   |
| TLZ9V1B                                                                                                  | 9B1          | 8.57                | 9.1  | 9.01  | 20           | 0.5       | 0.04                    | 8.14 | 8                  | 120                   |
| TLZ9V1C                                                                                                  | 9C1          | 8.83                | 9.1  | 9.3   | 20           | 0.5       | 0.04                    | 8.39 | 8                  | 120                   |
| TLZ10A                                                                                                   | 10A          | 9.12                | 10   | 9.59  | 20           | 0.5       | 0.04                    | 8.66 | 8                  | 120                   |
| TLZ10B                                                                                                   | 10B          | 9.41                | 10   | 9.9   | 20           | 0.5       | 0.04                    | 8.94 | 8                  | 120                   |
| TLZ10C                                                                                                   | 10C          | 9.7                 | 10   | 10.2  | 20           | 0.5       | 0.04                    | 9.22 | 8                  | 120                   |
| TLZ10D                                                                                                   | 10D          | 9.94                | 10   | 10.44 | 20           | 0.5       | 0.04                    | 9.44 | 8                  | 120                   |

**ELECTRICAL CHARACTERISTICS** ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)

| PART NUMBER | MARKING CODE | ZENER VOLTAGE RANGE |      |       | TEST CURRENT |           | REVERSE LEAKAGE CURRENT |       | DYNAMIC RESISTANCE |                       |
|-------------|--------------|---------------------|------|-------|--------------|-----------|-------------------------|-------|--------------------|-----------------------|
|             |              | $V_Z$ at $I_{ZT1}$  |      |       | $I_{ZT1}$    | $I_{ZT2}$ | $I_R$ at $V_R$          |       | $Z_Z$ at $I_{ZT1}$ | $Z_{ZK}$ at $I_{ZT2}$ |
|             |              | V                   |      |       | mA           |           | $\mu\text{A}$           | V     | $\Omega$           |                       |
|             |              | MIN.                | NOM. | MAX.  |              |           | MAX.                    |       | MAX.               | MAX.                  |
| TLZ11A      | 11A          | 10.18               | 11   | 10.71 | 10           | 0.5       | 0.04                    | 9.67  | 10                 | 120                   |
| TLZ11B      | 11B          | 10.5                | 11   | 11.05 | 10           | 0.5       | 0.04                    | 9.98  | 10                 | 120                   |
| TLZ11C      | 11C          | 10.82               | 11   | 11.38 | 10           | 0.5       | 0.04                    | 10.28 | 10                 | 120                   |
| TLZ12A      | 12A          | 11.13               | 12   | 11.71 | 10           | 0.5       | 0.04                    | 10.6  | 12                 | 110                   |
| TLZ12B      | 12B          | 11.44               | 12   | 12.03 | 10           | 0.5       | 0.04                    | 10.9  | 12                 | 110                   |
| TLZ12C      | 12C          | 11.74               | 12   | 12.35 | 10           | 0.5       | 0.04                    | 11.2  | 12                 | 110                   |
| TLZ13A      | 13A          | 12.11               | 13   | 12.75 | 10           | 0.5       | 0.04                    | 11.5  | 14                 | 110                   |
| TLZ13B      | 13B          | 12.55               | 13   | 13.21 | 10           | 0.5       | 0.04                    | 11.9  | 14                 | 110                   |
| TLZ13C      | 13C          | 12.99               | 13   | 13.66 | 10           | 0.5       | 0.04                    | 12.3  | 14                 | 110                   |
| TLZ15A      | 15A          | 13.44               | 15   | 14.13 | 10           | 0.5       | 0.04                    | 12.8  | 16                 | 110                   |
| TLZ15B      | 15B          | 13.89               | 15   | 14.62 | 10           | 0.5       | 0.04                    | 13.2  | 16                 | 110                   |
| TLZ15C      | 15C          | 14.35               | 15   | 15.09 | 10           | 0.5       | 0.04                    | 13.6  | 16                 | 110                   |
| TLZ16A      | 16A          | 14.8                | 16   | 15.57 | 10           | 0.5       | 0.04                    | 14.1  | 18                 | 150                   |
| TLZ16B      | 16B          | 15.25               | 16   | 16.04 | 10           | 0.5       | 0.04                    | 14.5  | 18                 | 150                   |
| TLZ16C      | 16C          | 15.69               | 16   | 16.51 | 10           | 0.5       | 0.04                    | 14.9  | 18                 | 150                   |
| TLZ18A      | 18A          | 16.22               | 18   | 17.06 | 10           | 0.5       | 0.04                    | 15.4  | 23                 | 150                   |
| TLZ18B      | 18B          | 16.82               | 18   | 17.7  | 10           | 0.5       | 0.04                    | 16    | 23                 | 150                   |
| TLZ18C      | 18C          | 17.42               | 18   | 18.33 | 10           | 0.5       | 0.04                    | 16.5  | 23                 | 150                   |
| TLZ20A      | 20A          | 18.02               | 20   | 18.96 | 10           | 0.5       | 0.04                    | 17.1  | 28                 | 200                   |
| TLZ20B      | 20B          | 18.63               | 20   | 19.59 | 10           | 0.5       | 0.04                    | 17.7  | 28                 | 200                   |
| TLZ20C      | 20C          | 19.23               | 20   | 20.22 | 10           | 0.5       | 0.04                    | 18.3  | 28                 | 200                   |
| TLZ20D      | 20D          | 19.72               | 20   | 20.72 | 10           | 0.5       | 0.04                    | 18.7  | 28                 | 200                   |
| TLZ22A      | 22A          | 20.15               | 22   | 21.2  | 5            | 0.5       | 0.04                    | 19.1  | 30                 | 200                   |
| TLZ22B      | 22B          | 20.64               | 22   | 21.71 | 5            | 0.5       | 0.04                    | 19.6  | 30                 | 200                   |
| TLZ22C      | 22C          | 21.08               | 22   | 22.17 | 5            | 0.5       | 0.04                    | 20    | 30                 | 200                   |
| TLZ22D      | 22D          | 21.52               | 22   | 22.63 | 5            | 0.5       | 0.04                    | 20.4  | 30                 | 200                   |
| TLZ24A      | 24A          | 22.05               | 24   | 23.18 | 5            | 0.5       | 0.04                    | 20.9  | 35                 | 200                   |
| TLZ24B      | 24B          | 22.61               | 24   | 23.77 | 5            | 0.5       | 0.04                    | 21.5  | 35                 | 200                   |
| TLZ24C      | 24C          | 23.12               | 24   | 24.31 | 5            | 0.5       | 0.04                    | 22    | 35                 | 200                   |
| TLZ24D      | 24D          | 23.63               | 24   | 24.85 | 5            | 0.5       | 0.04                    | 22.4  | 35                 | 200                   |
| TLZ27A      | 27A          | 24.26               | 27   | 25.52 | 5            | 0.5       | 0.04                    | 23    | 45                 | 250                   |
| TLZ27B      | 27B          | 24.97               | 27   | 26.26 | 5            | 0.5       | 0.04                    | 23.7  | 45                 | 250                   |
| TLZ27C      | 27C          | 25.63               | 27   | 26.95 | 5            | 0.5       | 0.04                    | 24.3  | 45                 | 250                   |
| TLZ27D      | 27D          | 26.29               | 27   | 27.64 | 5            | 0.5       | 0.04                    | 25    | 45                 | 250                   |
| TLZ30A      | 30A          | 26.99               | 30   | 28.39 | 5            | 0.5       | 0.04                    | 25.6  | 55                 | 250                   |
| TLZ30B      | 30B          | 27.7                | 30   | 29.13 | 5            | 0.5       | 0.04                    | 26.3  | 55                 | 250                   |
| TLZ30C      | 30C          | 28.36               | 30   | 29.82 | 5            | 0.5       | 0.04                    | 26.9  | 55                 | 250                   |
| TLZ30D      | 30D          | 29.02               | 30   | 30.51 | 5            | 0.5       | 0.04                    | 27.6  | 55                 | 250                   |
| TLZ33A      | 33A          | 29.68               | 33   | 31.22 | 5            | 0.5       | 0.04                    | 28.2  | 65                 | 250                   |
| TLZ33B      | 33B          | 30.32               | 33   | 31.88 | 5            | 0.5       | 0.04                    | 28.8  | 65                 | 250                   |
| TLZ33C      | 33C          | 30.9                | 33   | 32.5  | 5            | 0.5       | 0.04                    | 29.4  | 65                 | 250                   |
| TLZ33D      | 33D          | 31.49               | 33   | 33.11 | 5            | 0.5       | 0.04                    | 29.9  | 65                 | 250                   |
| TLZ36A      | 36A          | 32.14               | 36   | 33.79 | 5            | 0.5       | 0.04                    | 30.5  | 75                 | 250                   |
| TLZ36B      | 36B          | 32.79               | 36   | 34.49 | 5            | 0.5       | 0.04                    | 31.2  | 75                 | 250                   |
| TLZ36C      | 36C          | 33.4                | 36   | 35.13 | 5            | 0.5       | 0.04                    | 31.7  | 75                 | 250                   |
| TLZ36D      | 36D          | 34.01               | 36   | 35.77 | 5            | 0.5       | 0.04                    | 32.3  | 75                 | 250                   |

| <b>ELECTRICAL CHARACTERISTICS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) |              |                     |      |       |              |           |                         |      |                    |                       |
|----------------------------------------------------------------------------------------------------------|--------------|---------------------|------|-------|--------------|-----------|-------------------------|------|--------------------|-----------------------|
| PART NUMBER                                                                                              | MARKING CODE | ZENER VOLTAGE RANGE |      |       | TEST CURRENT |           | REVERSE LEAKAGE CURRENT |      | DYNAMIC RESISTANCE |                       |
|                                                                                                          |              | $V_Z$ at $I_{ZT1}$  |      |       | $I_{ZT1}$    | $I_{ZT2}$ | $I_R$ at $V_R$          |      | $Z_Z$ at $I_{ZT1}$ | $Z_{ZK}$ at $I_{ZT2}$ |
|                                                                                                          |              | V                   |      |       | mA           |           | $\mu\text{A}$           | V    | $\Omega$           |                       |
|                                                                                                          |              | MIN.                | NOM. | MAX.  |              |           | MAX.                    |      | MAX.               | MAX.                  |
| TLZ39A                                                                                                   | 39A          | 34.68               | 39   | 36.47 | 5            | 0.5       | 0.04                    | 32.9 | 85                 | 250                   |
| TLZ39B                                                                                                   | 39B          | 35.36               | 39   | 37.19 | 5            | 0.5       | 0.04                    | 33.6 | 85                 | 250                   |
| TLZ39C                                                                                                   | 39C          | 36                  | 39   | 37.85 | 5            | 0.5       | 0.04                    | 34.2 | 85                 | 250                   |
| TLZ39D                                                                                                   | 39D          | 36.63               | 39   | 38.52 | 5            | 0.5       | 0.04                    | 34.8 | 85                 | 250                   |
| TLZ39E                                                                                                   | 39E          | 37.36               | 39   | 39.29 | 5            | 0.5       | 0.04                    | 35.5 | 85                 | 250                   |
| TLZ39F                                                                                                   | 39F          | 38.14               | 39   | 40.11 | 5            | 0.5       | 0.04                    | 36.2 | 85                 | 250                   |
| TLZ39G                                                                                                   | 39G          | 38.94               | 39   | 40.8  | 5            | 0.5       | 0.04                    | 37   | 85                 | 250                   |
| TLZ43                                                                                                    | 43           | 40                  | 43   | 45    | 5            | -         | 0.04                    | 38   | 90                 | -                     |
| TLZ47                                                                                                    | 47           | 44                  | 47   | 49    | 5            | -         | 0.04                    | 41.8 | 90                 | -                     |
| TLZ51                                                                                                    | 51           | 48                  | 51   | 54    | 5            | -         | 0.04                    | 45.6 | 100                | -                     |
| TLZ56                                                                                                    | 56           | 53                  | 56   | 60    | 5            | -         | 0.04                    | 50.4 | 100                | -                     |

**BASIC CHARACTERISTICS** ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)


Fig. 1 - Total Power Dissipation vs. Ambient Temperature




Fig. 3 - Typical Change of Working Voltage vs. Junction Temperature




Fig. 2 - Typical Change of Working Voltage under Operating Conditions at  $T_{amb} = 25\text{ }^{\circ}\text{C}$ 

Fig. 4 - Temperature Coefficient of  $V_Z$  vs. Z-Voltage



Fig. 5 - Diode Capacitance vs. Z-Voltage



Fig. 8 - Z-Current vs. Z-Voltage



Fig. 6 - Forward Current vs. Forward Voltage



Fig. 9 - Differential Z-Resistance vs. Z-Voltage




Fig. 7 - Z-Current vs. Z-Voltage



Fig. 10 - Thermal Response

## MARKING VOLTAGE GROUP

### TLZ2V4A



18660\_2

## Remark

The Zener voltage group TLZ2V4A is printed with max 3 digits 3 times on the surface. The marking should be readable at minimum 2 times. The third print is allowed to be incomplete due to tolerances in diameter of the glass body.




**PACKAGE DIMENSIONS** in millimeters (inches): **MiniMELF SOD-80**



\* The gap between plug and glass can be either on cathode or anode side

Foot print recommendation:



Document no.: 6.560-5005.01-4  
Rev. 8 - Date: 07.June.2006  
96 12070



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[TLZ10-GS08](#) [TLZ10-GS18](#) [TLZ10A-GS08](#) [TLZ10A-GS18](#) [TLZ10B-GS08](#) [TLZ10B-GS18](#) [TLZ10C-GS08](#) [TLZ10C-GS18](#) [TLZ10D-GS08](#) [TLZ10D-GS18](#) [TLZ11-GS08](#) [TLZ11-GS18](#) [TLZ11A-GS08](#) [TLZ11A-GS18](#) [TLZ11B-GS08](#) [TLZ11B-GS18](#) [TLZ11C-GS08](#) [TLZ11C-GS18](#) [TLZ12-GS08](#) [TLZ12-GS18](#) [TLZ12A-GS08](#) [TLZ12A-GS18](#) [TLZ12B-GS08](#) [TLZ12B-GS18](#) [TLZ12C-GS08](#) [TLZ12C-GS18](#) [TLZ13-GS08](#) [TLZ13-GS18](#) [TLZ13A-GS08](#) [TLZ13A-GS18](#) [TLZ13B-GS08](#) [TLZ13B-GS18](#) [TLZ13C-GS08](#) [TLZ13C-GS18](#) [TLZ15-GS08](#) [TLZ15-GS18](#) [TLZ15A-GS08](#) [TLZ15A-GS18](#) [TLZ15B-GS08](#) [TLZ15B-GS18](#) [TLZ15C-GS08](#) [TLZ15C-GS18](#) [TLZ16-GS08](#) [TLZ16-GS18](#) [TLZ16A-GS08](#) [TLZ16A-GS18](#) [TLZ16B-GS08](#) [TLZ16B-GS18](#) [TLZ16C-GS08](#) [TLZ16C-GS18](#) [TLZ18-GS08](#) [TLZ18-GS18](#) [TLZ18A-GS08](#) [TLZ18A-GS18](#) [TLZ18B-GS08](#) [TLZ18B-GS18](#) [TLZ18C-GS08](#) [TLZ18C-GS18](#) [TLZ2V4-GS08](#) [TLZ2V4-GS18](#) [TLZ2V4A-GS08](#) [TLZ2V4A-GS18](#) [TLZ2V4B-GS08](#) [TLZ2V4B-GS18](#) [TLZ2V7-GS08](#) [TLZ2V7-GS18](#) [TLZ2V7A-GS08](#) [TLZ2V7A-GS18](#) [TLZ2V7B-GS08](#) [TLZ2V7B-GS18](#) [TLZ20-GS08](#) [TLZ20-GS18](#) [TLZ20A-GS08](#) [TLZ20A-GS18](#) [TLZ20B-GS08](#) [TLZ20B-GS18](#) [TLZ20C-GS08](#) [TLZ20C-GS18](#) [TLZ20D-GS08](#) [TLZ20D-GS18](#) [TLZ22-GS08](#) [TLZ22-GS18](#) [TLZ22A-GS08](#) [TLZ22A-GS18](#) [TLZ22B-GS08](#) [TLZ22B-GS18](#) [TLZ22C-GS08](#) [TLZ22C-GS18](#) [TLZ22D-GS08](#) [TLZ22D-GS18](#) [TLZ24-GS08](#) [TLZ24-GS18](#) [TLZ24A-GS08](#) [TLZ24A-GS18](#) [TLZ24B-GS08](#) [TLZ24B-GS18](#) [TLZ24C-GS08](#) [TLZ24C-GS18](#) [TLZ24D-GS08](#) [TLZ24D-GS18](#)