


NUMBER 200334

©1959 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

REVISIONS

SYM	ZONE	DESCRIPTION	DATE	APPROVAL
AJ		OBsolete -4-5-6 PER ECN BD 3038	10-11-89	R.L.
AK		OBsolete -9-1-0 PER ECN PL5-6	1-14-92	RW



WHEN ORDERING CONTACT ON TAPE, ORDER BY THE TAPE NUMBER PLUS THE PACKAGING CODE AS FOLLOWS:
 1. FOR USE WITH AMP TAPETRONIC, PNEUMATIC TOOL -
 A. 1000 PARTS TO A BOX ADD PACKAGING CODE INBOX
 2. FOR USE WITH 4/8 INDENT STRIPPER CRIMPER -
 A. 1000 PARTS TO A REEL ADD PACKAGING CODE INREEL
 B. 5000 PARTS TO A REEL ADD PACKAGING CODE INREEL

OBsolete	1-200334-1	COPPER ALLOY-.00005 GOLD OVER .000030 NICKEL	1-200334-2	OBsolete
OBsolete	200334-3	COPPER ALLOY-.00005 GOLD OVER .000030 NICKEL		
OBsolete	200334-6	COPPER ALLOY-.000100 MIN GOLD OVER .000050 MIN NICKEL		
OBsolete	200334-5	COPPER ALLOY-.000015 MIN GOLD OVER .000050 MIN NICKEL	1-200334-0	OBsolete
OBsolete	200334-4	COPPER ALLOY-.0001 MIN GOLD OVER .0001 MIN SILVER		STAINLESS STEEL
OBsolete	200334-8	COPPER ALLOY-.00004 GOLD OVER .00003 NICKEL	200334-9	OBsolete
OBsolete	200334-2	COPPER ALLOY-.0001 SILVER OVER .00003 NICKEL	200334-8	OBsolete
	200334-1	COPPER ALLOY-.00003 MIN GOLD OVER .00005 MIN NICKEL		
	ASS'Y. NO.	BODY	TAPE MTD ASSY NO	RETAINER

NOTE - PLATING THICKNESS TO BE MEASURED ON SURFACES ACCESSIBLE WITH 1/4 INCH DIAMETER SPHERE.

QTY REQD	REVISIONS	DATE	NAME
LIST OF MATERIALS OR PARTS LIST			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON FRACTIONS DECIMALS ANGLES ± 1/64 ± .015 ± 1°		SIGNATURE	DATE
MATERIAL		OR	
SEE TABLE		CHK	
HEAT TREAT		DSGN ENGR	
FINISH		APPD	
SEE TABLE		DSGN APPD	
		OTHER APPD	
AMP INFO		AMP INCORPORATED HARRISBURG, PENNSYLVANIA	
M	LOC	NAME	
7	BD	# 20 CONTACT PIN TYPE II WIRE SIZE 20 TO 24	
39		CODE IDENT NO	
		00779	
		SIZE	
		B	
		NUMBER	
		200334	
SCALE		CALC	
1/1		ACTUAL	
		SHEET 1 OF 1	