




LEAD FINISH: SOLDER	
EYELET FINISH: SOLDER	
CAPACITANCE	1500pF GMV
TEMP. RANGE	-55°C TO 125°C
CURRENT	10AMP MAX.
WORKING VOLTAGE	85°C 350VDC MAX. 125°C 200VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
1	--
10	5
100	45
1 GHz	70
10 GHz	--
SCHEMATIC	
MARKING: PART: NONE	
BAG: 1203-050	
DATE CODE	
QTY./BAG (200 MAX.)	

NOTES:
1. SUGGESTED MOUNTING HOLE = $\phi .160$

	CN.184999	REV. 3 CHANGE NOTICE NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	 SPECTRUM CONTROL INC.	ERIE, FAIRVIEW PENNSYLVANIA Description Pi SOLDER-IN FILTER 1203-050
			Fract. $\pm .001$		
			Dec. $.xx \pm$		
			Dec. $.xxx \pm 0.10$		
			Angles $\pm 0^\circ 30'$		
			CODE IDENT. NO.	Apvd.	
			OLSP2	Scale NONE	