





PART NUMBER	CUSTOMER P/N	CUSTOMER'S DRAWING REVISION	COVER COLOR
10086246-101LF	50-F8633-2	B	BLACK
10086246-201LF	N/A	N/A	MAGENTA



NOTES:


1. MATERIAL: ABS/POLYCARBONATE (ABS/PC), CYCOLOY CX7211, COLOR: SEE TABLE, REGRIND NOT PERMITTED;
2. SURFACE CONDITION: SPI B3 OR BETTER AND EXTERNAL SURFACE TO BE MOLD-TECH STANDARD FINISH NUMBER MT-11020;
3. LEAD FREE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008;
4. MARKING: INK STAMPED
 - A. DATE CODE FORMAT: MM-DD-YYYY(MONTH-DAY-YEAR), SUCH AS 03-01-2008
 - B. CUSTOMER DRAWING REVISION: SEE TABLE
 - C. REVISION OF RDL: TO BE PROVIDED BY CUSTOMER WITH EACH ORDER
5. PACKAGING OF LEAD FREE PRODUCTS MEETS LABELING AND PACKING SPECIFICATION GS-14-920.

rev	ecn no	dr	date
A	N08-0055	R.B	2008/03/31
B	N08-0178	R.B	2008/08/25
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface 		tolerance std		projection 		MM 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	Rick Bian	2008/02/01	ANGULAR	LINEAR	0.X	±0.50	size	A4	Scale	NTS	
Eng	Rick Bian	2008/02/01			0.XX	±0.30					
Chr	Daniel Tao	2008/02/01			0°	±3°					0.XXX
Appr	Joseph Hsia	2008/02/01	Product family					ECN			
			Spec ref								
		title BOTTOM COVER				dwg no 10086246				Rev. B	
		EXPRESS CARD									
		catalog no				CUSTOMER		sheet 1 of 2			



Copyright FCI.



- NOTES:
1. MATERIAL: PS. THICKNESS:0.60mm;
2. ALLOWED RADIUS 1.0mm MAXIMUM UNLESS SPECIFIED;
3. DRAFT ANGLE: 5° MAXIMUM;
4. 24 PCS/TRAY.

www.fciconnect.com			surface 		tolerance std		projection 		MM 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	Rick Bian	2008/02/01	ANGULAR	LINEAR	0.X	±0.50	size A4	Scale			
Eng	Rick Bian	2008/02/01			0.XX	±0.30					
Chr	Daniel Tao	2008/02/01			0.XXX	±					
Appr	Joseph Hsia	2008/02/01	Product family					ECN Spec ref			
			title BOTTOM COVER EXPRESS CARD				dwg no 10086246		Rev. B		
catalog no							CUSTOMER		sheet 2 of 2		

REV F - 2008-06-17