



PLATING SPECIFICATIONS		
	CONTACT	TERMINAL
A	.000015" GOLD	.0001" TIN/LEAD
D	.00003" GOLD	.00003" GOLD OVERALL
G	.00001" GOLD	.000005" GOLD
M	.00003" GOLD	.00001" GOLD OVERALL
N	.00005" GOLD	.0001" TIN/LEAD
O	.00003" GOLD	.0001" TIN/LEAD
P	GOLD FLASH	GOLD FLASH
R	.00002" GOLD	.0001" TIN/LEAD
S	.00001" GOLD	.00001" GOLD OVERALL
T	.0001" TIN/LEAD	.0001" TIN/LEAD OVERALL
V	.00003" GOLD	.000005" GOLD
W	GOLD FLASH	.0001" TIN/LEAD
X	.00003" GOLD	.0001" TIN/LEAD
Y	.00003" GOLD	.000005" GOLD
Z	.00001" GOLD	.0001" TIN/LEAD

PART NUMBER	CONTACT PIN	HEAD LENGTH	TAIL LENGTH
GTC_SABN-M30	ETC-SAB	0.230 [5.84]	0.320 [8.13]
GZC_SABN-M30	EZC-SAB	0.230 [5.84]	0.320 [8.13]
GTC_SFBN-M30	ETC-SFB	0.318 [8.08]	0.300 [7.62]
GZC_SFBN-M30	EZC-SFB	0.318 [8.08]	0.300 [7.62]



COMPUTER
GENERATED
DOCUMENT DO
NOT CHANGE
MANUALLY

PROPRIETARY AND CONFIDENTIAL
THIS DRAWING AND DESIGN IS THE
PROPERTY OF SULLINS ELECTRONICS.
IT MAY NOT BE USED FOR ANY
PURPOSE OTHER THAN BY THE OWNER.
SULLINS ELECTRONICS DOES NOT
AUTHORIZE THE REPRODUCTION OR
CONVEYANCE OF ANY INFORMATION
CONTAINED HEREIN.

PART NUMBER	BODY NUMBER	A
G_C01S_N-M30	H01S-A360	0.100 [2.54]
G_C02S_N-M30	H02S-A360	0.200 [5.08]
G_C03S_N-M30	H03S-A360	0.300 [7.62]
G_C04S_N-M30	H04S-A360	0.400 [10.16]
G_C05S_N-M30	H05S-A360	0.500 [12.70]
G_C06S_N-M30	H06S-A360	0.600 [15.24]
G_C07S_N-M30	H07S-A360	0.700 [17.78]
G_C08S_N-M30	H08S-A360	0.800 [20.32]
G_C09S_N-M30	H09S-A360	0.900 [22.86]
G_C10S_N-M30	H10S-A360	1.000 [25.40]
G_C11S_N-M30	H11S-A360	1.100 [27.94]
G_C12S_N-M30	H12S-A360	1.200 [30.48]
G_C13S_N-M30	H13S-A360	1.300 [33.02]
G_C14S_N-M30	H14S-A360	1.400 [35.56]
G_C15S_N-M30	H15S-A360	1.500 [38.10]
G_C16S_N-M30	H16S-A360	1.600 [40.64]
G_C17S_N-M30	H17S-A360	1.700 [43.18]
G_C18S_N-M30	H18S-A360	1.800 [45.72]
G_C19S_N-M30	H19S-A360	1.900 [48.26]
G_C20S_N-M30	H20S-A360	2.000 [50.80]
G_C21S_N-M30	H21S-A360	2.100 [53.34]
G_C22S_N-M30	H22S-A360	2.200 [55.88]
G_C23S_N-M30	H23S-A360	2.300 [58.42]
G_C24S_N-M30	H24S-A360	2.400 [60.96]
G_C25S_N-M30	H25S-A360	2.500 [63.50]
G_C26S_N-M30	H26S-A360	2.600 [66.04]
G_C27S_N-M30	H27S-A360	2.700 [68.58]
G_C28S_N-M30	H28S-A360	2.800 [71.12]
G_C29S_N-M30	H29S-A360	2.900 [73.66]
G_C30S_N-M30	H30S-A360	3.000 [76.20]
G_C31S_N-M30	H31S-A360	3.100 [78.74]
G_C32S_N-M30	H32S-A360	3.200 [81.28]
G_C33S_N-M30	H33S-A360	3.300 [83.82]
G_C34S_N-M30	H34S-A360	3.400 [86.36]
G_C35S_N-M30	H35S-A360	3.500 [88.90]
G_C36S_N-M30	H36S-A360	3.600 [91.44]

A	62	ORIGINAL RELEASE			9/19/03	JFW	AJT
REV.	ECO NO.	DESCRIPTION			DATE	BY	APP'VD
		UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± 1/32 ANGULAR: ± 1° TWO PLACE DECIMAL ± .02 THREE PLACE DECIMAL ± .005 FOUR PLACE DECIMAL ± .0005 INTERPRET GEOMETRIC TOLERANCING PER: MATERIAL: NOTED FINISH: N/A	DRAWN	DATE	NAME	SULLINS ELECTRONICS PART NO./DESCRIPTION: HEADERS G_C__S__ N-M30	
			CHECKED	9/19/03	JWHITE		
			CHECKED	9/19/03	AJT		
			COMMENTS:				
NEXT ASSY	USED ON				SIZE DWG. NO.	REV A	
APPLICATION		DO NOT SCALE DRAWING			10058		
					SCALE: 1:1		SHEET 1 OF 1