



PLATING SPECIFICATIONS			
CONTACT		TERMINAL	
A	.000015" GOLD		.0001" TIN/LEAD
D	.00003" GOLD		.00003" GOLD OVERALL
G	.00001" GOLD		.000005" GOLD
M	.00003" GOLD		.00001" GOLD OVERALL
N	.00005" GOLD		.0001" TIN/LEAD
O	.00003" GOLD		.0001" TIN/LEAD
P	GOLD FLASH		GOLD FLASH
R	.00002" GOLD		.0001" TIN/LEAD
S	.00001" GOLD		.00001" GOLD OVERALL
T	.0001" TIN/LEAD		.0001" TIN/LEAD OVERALL
V	.00003" GOLD		.000005" GOLD
W	GOLD FLASH		.0001" TIN/LEAD
X	.00003" GOLD		.0001" TIN/LEAD
Y	.00003" GOLD		.000005" GOLD
Z	.00001" GOLD		.0001" TIN/LEAD

*ALL CONTACT PINS HAVE A .00005" NICKEL UNDERPLATE.

TERMINATION TYPES		
P/N CODE	HEAD DIMENSIONS	TAIL DIMENSIONS
BS	0.230 [5.84]	.180 [4.57]
GS	0.318 [8.08]	.180 [4.57]

PART NUMBER	BODY NUMBER	A
G_C01S__N-M89	H01R-A360	0.100 [2.54]
G_C02S__N-M89	H02R-A360	0.200 [5.08]
G_C03S__N-M89	H03R-A360	0.300 [7.62]
G_C04S__N-M89	H04R-A360	0.400 [10.16]
G_C05S__N-M89	H05R-A360	0.500 [12.70]
G_C06S__N-M89	H06R-A360	0.600 [15.24]
G_C07S__N-M89	H07R-A360	0.700 [17.78]
G_C08S__N-M89	H08R-A360	0.800 [20.32]
G_C09S__N-M89	H09R-A360	0.900 [22.86]
G_C10S__N-M89	H10R-A360	1.000 [25.40]
G_C11S__N-M89	H11R-A360	1.100 [27.94]
G_C12S__N-M89	H12R-A360	1.200 [30.48]
G_C13S__N-M89	H13R-A360	1.300 [33.02]
G_C14S__N-M89	H14R-A360	1.400 [35.56]
G_C15S__N-M89	H15R-A360	1.500 [38.10]
G_C16S__N-M89	H16R-A360	1.600 [40.64]
G_C17S__N-M89	H17R-A360	1.700 [43.18]
G_C18S__N-M89	H18R-A360	1.800 [45.72]
G_C19S__N-M89	H19R-A360	1.900 [48.26]
G_C20S__N-M89	H20R-A360	2.000 [50.80]
G_C21S__N-M89	H21R-A360	2.100 [53.34]
G_C22S__N-M89	H22R-A360	2.200 [55.88]
G_C23S__N-M89	H23R-A360	2.300 [58.42]
G_C24S__N-M89	H24R-A360	2.400 [60.96]
G_C25S__N-M89	H25R-A360	2.500 [63.50]
G_C26S__N-M89	H26R-A360	2.600 [66.04]
G_C27S__N-M89	H27R-A360	2.700 [68.58]
G_C28S__N-M89	H28R-A360	2.800 [71.12]
G_C29S__N-M89	H29R-A360	2.900 [73.66]
G_C30S__N-M89	H30R-A360	3.000 [76.20]
G_C31S__N-M89	H31R-A360	3.100 [78.74]
G_C32S__N-M89	H32R-A360	3.200 [81.28]
G_C33S__N-M89	H33R-A360	3.300 [83.82]
G_C34S__N-M89	H34R-A360	3.400 [86.36]
G_C35S__N-M89	H35R-A360	3.500 [88.90]
G_C36S__N-M89	H36R-A360	3.600 [91.44]



SAMPLE PART NUMBER: GTC16SBSN-M89

PLATING SPECIFICATION

TERMINATION TYPE

COMPUTER
GENERATED
DOCUMENT DO
NOT CHANGE
MANUALLY

PROPRIETARY AND CONFIDENTIAL
THIS DRAWING AND DESIGN IS THE
PROPERTY OF SULLINS ELECTRONICS.
IT MAY NOT BE USED FOR ANY
PURPOSE OTHER THAN BY THE OWNER.
SULLINS ELECTRONICS DOES NOT
AUTHORIZE THE REPRODUCTION OR
CONVEYANCE OF ANY INFORMATION
CONTAINED HEREIN.

A	62	ORIGINAL RELEASE		9/24/03	JFW	AJT
REV.	ECO NO.	DESCRIPTION		DATE	BY	APP'VD
		UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES FRACTIONAL ± 1/32 ANGULAR ± 1° TWO PLACE DECIMAL ± .02 THREE PLACE DECIMAL ± .005 FOUR PLACE DECIMAL ± .0005 INTERPRET GEOMETRIC TOLERANCING PER:		DRAWN 9/24/03	DATE 9/24/03	NAME JWHITE AJT
		MATERIAL NOTED		COMMENTS:		
		FINISH N/A				
NEXT ASSY		USED ON		SCALE: 5:1		
APPLICATION		DO NOT SCALE DRAWING		SHEET 1 OF 1		

⊙

⌵

⊙

⌵

SULLINS
ELECTRONICS

HEADERS
G_C__S__N-M89

SIZE
C

DWG. NO.
10060

REV
A