



2SA608N/2SC536N

Bipolar Transistor

(-50V, (-)150mA, Low $V_{CE(sat)}$ (PNP)NPN Single NPA-WA

ON Semiconductor®

<http://onsemi.com>

Applicaitions

- Capable of being used in the low frequency to high frequency range

Features

- Large current capacity and wide ASO

Specifications () : 2SA608N

Absolute Maximum Ratings at $T_a=25^{\circ}\text{C}$


Parameter	Symbol	Conditions	Ratings	Unit
Collector to Base Voltage	V_{CBO}		(-50)60	V
Collector to Emitter Voltage	V_{CEO}		(-)50	V
Emitter to Base Voltage	V_{EBO}		(-)6	V
Collector Current	I_C		(-)150	mA
Collector Current (Pulse)	I_{CP}		(-)400	mA
Collector Dissipation	P_C		500	mW
Junction Temperature	T_j		150	$^{\circ}\text{C}$
Storage Temperature	T_{stg}		-55 to +150	$^{\circ}\text{C}$

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

Package Dimensions

unit : mm (typ)


7542-001



Ordering & Package Information

Device	Package	Shipping	memo
2SA608NF-NPA-AT	NPA SC-43A, TO-92, TO-226AA, SOT-54	1,500 pcs./box	Pb-Free
2SA608NG-NPA-AT	NPA SC-43A, TO-92, TO-226AA, SOT-54	1,500 pcs./box	
2SC536NF-NPA-AT	NPA SC-43A, TO-92, TO-226AA, SOT-54	1,500 pcs./box	
2SC536NG-NPA-AT	NPA SC-43A, TO-92, TO-226AA, SOT-54	1,500 pcs./box	

Marking







2SA608N/2SC536N

Electrical Characteristics at Ta=25°C









Parameter	Symbol	Conditions	Ratings			Unit
			min	typ	max	
Collector Cutoff Current	I_{CBO}	$V_{CB}=(-)40V, I_E=0A$			$(-)0.1$	μA
Emitter Cutoff Current	I_{EBO}	$V_{EB}=(-)5V, I_C=0A$			$(-)0.1$	μA
DC Current Gain	h_{FE1}	$V_{CE}=(-)6V, I_C=(-)1mA$	160*		560*	
	h_{FE2}	$V_{CE}=(-)6V, I_C=(-)0.1mA$	70			
Gain-Bandwidth Product	f_T	$V_{CE}=(-)6V, I_C=(-)10mA$		200		MHz
Output Capacitance	C_{ob}	$V_{CB}=(-)6V, f=1MHz$		(4.5)3.0		pF
Collector to Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C=(-)100mA, I_B=(-)10mA$			$(-)0.3$	V
Base to Emitter Saturation Voltage	$V_{BE(sat)}$	$I_C=(-)100mA, I_B=(-)10mA$			$(-)1.0$	V
Collector to Base Breakdown Voltage	$V_{(BR)CBO}$	$I_C=(-)10\mu A, I_E=0A$	$(-)60$			V
Collector to Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C=(-)1mA, R_{BE}=\infty$	$(-)50$			V
Emitter to Base Breakdown Voltage	$V_{(BR)EBO}$	$I_E=(-)10\mu A, I_C=0A$	$(-)6$			V

* : The 2SA608N / 2SC536N are classified by 1mA h_{FE} as follow :



Rank	F	G
h_{FE}	160 to 320	280 to 560



2SA608N/2SC536N



2SA608N/2SC536N



ON Semiconductor and the ON logo are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.