



SAW Components

SAW Rx filter

WCDMA band I

Series/type:	B9433
Ordering code:	B39212-B9433-M410
Date:	Mar. 26, 2007
Version:	2.0



SAW Components

B9433

SAW Rx filter

2140.0 MHz

Data Sheet




Application

- Low-loss RF filter for mobile telephone WCDMA Band 1 systems, receive path (RX)
- Unbalanced to unbalanced operation
- Low insertion attenuation
- Low amplitude ripple
- High selectivity up to 6 GHz
- Usable passband 60 MHz




Features

- Package size 1.4 x 1.1 x 0.4 mm³
- Package code QCS5I
- RoHS compatible
- Approximate weight 0.003 g
- Package for **Surface Mount Technology (SMT)**
- Ni, gold-plated terminals
- **Electrostatic Sensitive Device (ESD)**



Pin configuration

- 1 Unbalanced input
- 4 Unbalanced output
- 2,3,5 To be grounded





SAW Components

B9433

SAW Rx filter

2140.0 MHz

Data Sheet



Characteristics

Temperature range for specification:	T = −30 °C to +85 °C
Terminating source impedance:	Z _S = 50Ω , 4.0 nH in parallel
Terminating load impedance:	Z _L = 50Ω , 1.3 nH in serial

		min.	typ. @ 25 °C	max.	
Center frequency	f _C	—	2140.0	—	MHz
Maximum insertion attenuation	α _{max}				
2110.0 ... 2170.0 MHz		—	2.0	2.3 ¹⁾	dB
Amplitude ripple (p-p)	Δα				
2110.0 ... 2170.0 MHz		—	0.6	1.0	dB
Input VSWR					
2110.0 ... 2170.0 MHz		—	1.5	1.9	
Output VSWR					
2110.0 ... 2170.0 MHz		—	1.5	1.9	
EVM					
2110.0 ... 2170.0 MHz		—	1.0	—	%
Attenuation	α				
100.0 ... 925.0 MHz		46	49	—	dB
925.0 ... 1300.0 MHz		40	44	—	dB
1300.0 ... 1800.0 MHz		38	43	—	dB
1800.0 ... 1920.0 MHz		38	43	—	dB
1920.0 ... 1980.0 MHz		43	49	—	dB
1980.0 ... 2025.0 MHz		30	45	—	dB
2025.0 ... 2050.0 MHz		17	24	—	dB
2050.0 ... 2075.0 MHz		5	9	—	dB
2210.0 ... 2255.0 MHz		12	32	—	dB
2255.0 ... 2300.0 MHz		20	33	—	dB
2300.0 ... 2400.0 MHz		31	38	—	dB
2400.0 ... 2500.0 MHz		35	41	—	dB
2500.0 ... 2800.0 MHz		37	47	—	dB
2800.0 ... 3200.0 MHz		35	39	—	dB
3200.0 ... 6000.0 MHz		40	54	—	dB

¹⁾ including a pcb loss of 0.2dB



SAW Components		B9433
SAW Rx filter		2140.0 MHz
Data Sheet	SMD	

Maximum ratings

Operable temperature range	T	−30/+85	°C	machine model, 10 pulses
Storage temperature range	T _{stg}	−40/+85	°C	
DC voltage	V _{DC}	5	V	
ESD voltage	V _{ESD}	50 ¹⁾	V	
Input power at				effective power in the on-state CW, +65°C 2000hr
WCDMA Band I	P _{IN}	0	dBm	
Tx band	P _{IN}	24	dBm	

¹⁾ acc. to JESD22-A115A (machine model), 10 negative & 10 positive pulses.



SAW Components

B9433


SAW Rx filter

2140.0 MHz


Data Sheet





Transfer function



Transfer function (wideband)



Please read *cautions and warnings* and *important notes* at the end of this document.





SAW Components	B9433
SAW Rx filter	2140.0 MHz
Data Sheet	SMD

References

Type	B9433
Ordering code	B39212-B9433-M410
Marking and package	C61157-A8-A3
Packaging	F61074-V8212-Z000
Date codes	L_1126
S-parameters	B9433_NB.s2p B9433_WB.s2p
Soldering profile	S_6001
RoHS compatible	defined as compatible with the following documents: "DIRECTIVE 2002/95/EC OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 27 January 2003 on the restriction of the use of certain hazardous substances in electrical and electronic equipment. 2005/618/EC from April 18th, 2005, amending Directive 2002/95/EC of the European Parliament and of the Council for the purposes of establishing the maximum concentration values for certain hazardous substances in electrical and electronic equipment."
Moldability	Before using in overmolding enviroment, please contact your EPCOS sales office.

For further information please contact your local EPCOS sales office or visit our webpage at www.epcos.com .

Published by EPCOS AG
Surface Acoustic Wave Components Division
P.O. Box 80 17 09, 81617 Munich, GERMANY

© EPCOS AG 2007. This brochure replaces the previous edition.

For questions on technology, prices and delivery please contact the Sales Offices of EPCOS AG or the international Representatives.

Due to technical requirements components may contain dangerous substances. For information on the type in question please also contact one of our Sales Offices.



Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of passive electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of a passive electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of a passive electronic component.
3. The warnings, cautions and product-specific notes must be observed.
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as "hazardous")**. Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available.
6. Unless otherwise agreed in individual contracts, **all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI)**.
7. The trade names EPCOS, CeraDiode, CSSP, PhaseCap, PhaseMod, SIFI, SIKOREL, Silver-Cap, SIMID, SIOV, SIP5D, SIP5K, TOPcap, UltraCap, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.