

3 A High-Speed MOSFET Drivers



As MOSFET drivers, the NCP4413/4414 can easily switch 1800 pF gate capacitance in 20 nsec with matched rise and fall times, and provide low enough impedance in both the ON and the OFF states to ensure the MOSFET's intended state will not be affected, even by large transients. The rise and fall time edges are matched to allow driving short-duration inputs with greater output accuracy.

- Latch-up Protected: Will Withstand 500 mA Reverse Current
- Input Will Withstand Negative Inputs Up to 5 V
- ESD Protected (4 kV)
- High Peak Output Current (3 A)
- Wide Operating Range (4.5 V to 16 V)
- High Capacitive Load Drive Capability (1800 pF in 20 nsec)
- Short Delay Time (35 nsec Typ)
- Consistent Delay Times with Changes in Supply Voltage
- Matched Delay Times
- Low Supply Current
 - With Logic “1” Input (500 μ A)
 - With Logic “0” Input (100 μ A)
- Low Output Impedance (2.7 Ω)


[illegible]

<http://onsemi.com>

SO-8
D SUFFIX
CASE 751



PDIP-8
P SUFFIX
CASE 626







x = Device Number (3 or 4)
YY, Y = Year
WW, W = Work Week
X = Assembly ID Code
Z = Subcontractor ID Code
CO = Country of Origin

Device	Package	Shipping
NCP4413DR2 Inverting	SO-8	2500 Tape & Reel
NCP4413P Inverting	PDIP-8	50 Units/Rail
NCP4414DR2 Non-Inverting	SO-8	2500 Tape & Reel
NCP4414P Non-Inverting	PDIP-8	50 Units/Rail

NCP4413, NCP4414

PIN CONNECTIONS



NC = NO INTERNAL CONNECTION

NCP4413, NCP4414

ABSOLUTE MAXIMUM RATINGS*

Rating	Symbol	Value	Unit
Supply Voltage	V_{DD}	+20	V
Input Voltage, IN A or IN B	V_{IN}	$V_{DD} + 0.3$ to GND – 5.0	V
Maximum Chip Temperature		+150	°C
Storage Temperature Range	T_{stg}	–65 to +150	°C
Lead Temperature (Soldering, 10 sec)	T_{SOI}	+300	°C
Package Thermal Resistance SOIC SOIC	$R_{\theta JA}$ $R_{\theta JC}$	155 45	°C/W
Operating Temperature Range	T_A	–40 to +85	°C
Power Dissipation ($T_A \leq 70^\circ\text{C}$) SOIC	P_D	470	mW

*Static-sensitive device. Unused devices must be stored in conductive material. Protect devices from static discharge and static fields. Stresses above those listed under “Absolute Maximum Ratings” may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions above those indicated in the operation section of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

ELECTRICAL CHARACTERISTICS (Over operating temperature range with $4.5\text{ V} \leq V_{DD} \leq 16\text{ V}$, unless otherwise specified. Typical values are measured at $T_A = 25^\circ\text{C}$; $V_{DD} = 16\text{ V}$.)

Characteristic	Symbol	Test Conditions	Min	Typ	Max	Unit
Input						
Logic 1 High Input Voltage	V_{IH}	–	2.0	–	–	V
Logic 0 Low Input Voltage	V_{IL}	–	–	–	0.8	V
Input Current	I_{IN}	$0\text{V} \leq V_{IN} \leq V_{DD}$ $T_A = 25^\circ\text{C}$ – $40^\circ\text{C} \leq T_A \leq 85^\circ\text{C}$	–1.0 –10	– –	1.0 10	μA
Output						
High Output Voltage	V_{OH}	DC Test	$V_{DD} - 0.025$	–	–	V
Low Output Voltage	V_{OL}	DC Test	–	–	0.025	v
Output Resistance	R_O	$V_{DD} = 16\text{ V}$, $I_O = 10\text{ mA}$ $T_A = 25^\circ\text{C}$ – $40^\circ\text{C} \leq T_A \leq 85^\circ\text{C}$	– –	2.7 3.3	4.0 5.0	Ω
Peak Output Current	I_{PK}	$V_{DD} = 16\text{ V}$	–	3.0	–	A
Latch-Up Protection Withstand Reverse Current	I_{REV}	Duty Cycle $\leq 2\%$ $t \leq 300\text{ }\mu\text{sec}$ $V_{DD} = 16\text{ V}$	0.5	–	–	A
Switching Time (Note 1.)						
Rise Time	t_R	Figure 1 $T_A = 25^\circ\text{C}$ – $40^\circ\text{C} \leq T_A \leq 85^\circ\text{C}$	– –	20 24	28 33	nsec
Fall Time	t_F	Figure 1 $T_A = 25^\circ\text{C}$ – $40^\circ\text{C} \leq T_A \leq 85^\circ\text{C}$	– –	20 24	28 33	nsec
Delay Time	t_{D1}	Figure 1 $T_A = 25^\circ\text{C}$ – $40^\circ\text{C} \leq T_A \leq 85^\circ\text{C}$	– –	35 40	45 50	nsec
Delay Time	t_{D2}	Figure 1 $T_A = 25^\circ\text{C}$ – $40^\circ\text{C} \leq T_A \leq 85^\circ\text{C}$	– –	35 40	45 50	nsec
Power Supply						
Power Supply Current	I_S	$V_{IN} = 3\text{ V}$ $V_{IN} = 0\text{ V}$ $V_{DD} = 16\text{ V}$	– –	0.5 0.1	1.0 0.15	mA

1. Switching times are guaranteed by design.

NCP4413, NCP4414




Figure 1. Switching Time Test Circuit




Figure 2. Thermal Derating Curves

TYPICAL CHARACTERISTICS




Figure 3. Quiescent Supply Current
vs. Supply Voltage
 $T_A = 25^\circ\text{C}$




Figure 4. Quiescent Supply Current
vs. Temperature
 $V_{\text{SUPPLY}} = 16\text{ V}$




Figure 5. Input Threshold vs. Supply Voltage
 $T_A = 25^\circ\text{C}$




Figure 6. Input Threshold vs. Temperature
 $V_{\text{SUPPLY}} = 16\text{ V}$




Figure 7. High-State Output Resistance




Figure 8. Low-State Output Resistance

TYPICAL CHARACTERISTICS




Figure 9. Rise Time vs. Supply Voltage
C_{LOAD} = 1800 pF




Figure 10. Fall Time vs. Supply Voltage
C_{LOAD} = 1800 pF




Figure 11. T_{D1} Propagation Delay
vs. Supply Voltage
C_{LOAD} = 1800 pF




Figure 12. T_{D2} Propagation Delay
vs. Supply Voltage
C_{LOAD} = 1800 pF




Figure 13. Rise and Fall Times
vs. Capacitive Load
 $T_A = 25^\circ\text{C}$, $V_{DD} = 16\text{ V}$





Figure 14. Propagation Delays
vs. Capacitive Load
 $T_A = 25^\circ\text{C}$, $V_{DD} = 16\text{ V}$

NCP4413, NCP4414

PACKAGE DIMENSIONS

PDIP-8
P SUFFIX
CASE 626-05
ISSUE K




NOTES:

1. DIMENSION L TO CENTER OF LEAD WHEN FORMED PARALLEL.
2. PACKAGE CONTOUR OPTIONAL (ROUND OR SQUARE CORNERS).
3. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.

DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	9.40	10.16	0.370	0.400
B	6.10	6.60	0.240	0.260
C	3.94	4.45	0.155	0.175
D	0.38	0.51	0.015	0.020
F	1.02	1.78	0.040	0.070
G	2.54 BSC		0.100 BSC	
H	0.76	1.27	0.030	0.050
J	0.20	0.30	0.008	0.012
K	2.92	3.43	0.115	0.135
L	7.62 BSC		0.300 BSC	
M	10°		10°	
N	0.76	1.01	0.030	0.040

SO-8
D SUFFIX
CASE 751-06
ISSUE T



NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. DIMENSIONS ARE IN MILLIMETER.
3. DIMENSION D AND E DO NOT INCLUDE MOLD PROTRUSION.
4. MAXIMUM MOLD PROTRUSION 0.15 PER SIDE.
5. DIMENSION B DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.127 TOTAL IN EXCESS OF THE B DIMENSION AT MAXIMUM MATERIAL CONDITION.

DIM	MILLIMETERS	
	MIN	MAX
A	1.35	1.75
A1	0.10	0.25
B	0.35	0.49
C	0.19	0.25
D	4.80	5.00
E	3.80	4.00
e	1.27 BSC	
H	5.80	6.20
h	0.25	0.50
L	0.40	1.25
θ	0°	7°

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer.

PUBLICATION ORDERING INFORMATION

NORTH AMERICA Literature Fulfillment:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: ONlit@hibbertco.com
Fax Response Line: 303-675-2167 or 800-344-3810 Toll Free USA/Canada

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

EUROPE: LDC for ON Semiconductor – European Support

German Phone: (+1) 303-308-7140 (M-F 1:00pm to 5:00pm Munich Time)
Email: ONlit-german@hibbertco.com
French Phone: (+1) 303-308-7141 (M-F 1:00pm to 5:00pm Toulouse Time)
Email: ONlit-french@hibbertco.com
English Phone: (+1) 303-308-7142 (M-F 12:00pm to 5:00pm UK Time)
Email: ONlit@hibbertco.com

EUROPEAN TOLL-FREE ACCESS*: 00-800-4422-3781

*Available from Germany, France, Italy, England, Ireland

CENTRAL/SOUTH AMERICA:

Spanish Phone: 303-308-7143 (Mon-Fri 8:00am to 5:00pm MST)
Email: ONlit-spanish@hibbertco.com

ASIA/PACIFIC: LDC for ON Semiconductor – Asia Support

Phone: 303-675-2121 (Tue-Fri 9:00am to 1:00pm, Hong Kong Time)
Toll Free from Hong Kong & Singapore:
001-800-4422-3781
Email: ONlit-asia@hibbertco.com

JAPAN: ON Semiconductor, Japan Customer Focus Center
4-32-1 Nishi-Gotanda, Shinagawa-ku, Tokyo, Japan 141-0031
Phone: 81-3-5740-2745
Email: r14525@onsemi.com

ON Semiconductor Website: <http://onsemi.com>

For additional information, please contact your local Sales Representative.