



For more Information
please call

1-800-Belden1



General Description:

Video Cable , Plenum-CMP, 5-25 AWG solid bare copper, foam FEP insulation, Beldfoil®+95% tinned copper interlocked serve, inner Flamarrest® jackets, Flamarrest® jacket

Usage (Overall)

Suitable Applications: Video

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
5	25	Solid	TC - Tinned Copper	0.018

Total Number of Conductors: 5

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
Gas-injected FEP - Foam FEP	0.074

Inner Shield

Inner Shield Material:

Layer #	Type	Inner Shield Material	Coverage (%)
1	Tape	Aluminum Foil-Polyester Tape	100.000
2	Serve	TC - Tinned Copper	95.000

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (in.)
PVC - Polyvinyl Chloride	0.104

Inner Jacket Color Code Chart:

Number	Color
1	Gray #1
2	Gray #2
3	Gray #3
4	Gray #4
5	Gray #5

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
Unjacketed

Overall Cable

Overall Cabling Fillers: Bonded Spline

Overall Nominal Diameter: 0.275 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: 0°C To +60°C

Bulk Cable Weight: 46 lbs/1000 ft.

Max. Recommended Pulling Tension: 20 lbs.

Min. Bend Radius (Each Coax): 1.250 in.

Min. Bend Radius (Overall): 3 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	NFPA 262 Plenum Flame Test (UL910)(FT6)
----------------	---

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	1397S5

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
75

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
17.0

Nominal Velocity of Propagation:

VP (%)
80

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
34

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
5.4

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	0.52
5	1.17
50	3.7
100	4.9
200	6.7
400	9.5
750	13.4
900	15.0
1000	15.8
3000	31.2

Max. Operating Voltage - UL:

Voltage
300 V RMS

Minimum Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
1.000	1000.000	15.000

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1398S5 0081000	1,000 FT	51.000 LB	GRAY		5X #25RGB COAX CMP BANANA PEEL
1398S5 008250	250 FT	14.750 LB	GRAY		5X #25RGB COAX CMP BANANA PEEL



1398S5 Coax - RGB Video Cable

1398S5 008500	500 FT	27.000 LB	GRAY		5X #25RGB COAX CMP BANANA PEEL
---------------	--------	-----------	------	--	--------------------------------

Revision Number: 2 Revision Date: 03-11-2013

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.