








MATERIAL NUMBER	ENGINEERING PART NUMBER	COUPLING NUT MATERIAL	COUPLING NUT FINISH
1300170020	1A4006-34	BRASS	NICKEL PLATED
1300170021	1A4006-348	STAINLESS STEEL	PASSIVATED



VOLTAGE RATING	600VAC/VDC
AMPERAGE RATING	16 AWG 13 AMPS 18AWG 8 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 80°C
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	NYLON	BLACK
2	PIN CONTACTS	COPPER ALLOY	GOLD PLATED
3	O-RING	NITRILE	BLACK
4	COUPLING NUT	SEE CHART	SEE CHART
5	MOLDED BODY	NYLON	BLACK
6	GROMMET	NITRILE	BLACK
7	CORD GRIP BODY	NYLON	BLACK

OD RANGE WAS .20-.48, WAS 10 AMPS		DESCRIPTION	QUALITY SYMBOL	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		
EC NO: ICG2013-1684				▽=0 ▽C=0				IN/MM		---	INCH		
DRWN: RSTONE						mm	INCH	DRAWN BY DATE		TITLE			
CH'KD: BW					4 PLACES	±---	±---	TWOEDGE 2009/08/25		MINI CHANGE ATTACHABLE 4-POLE MALE ST .20-.45 O.D. CABLE RANGE			
APPR: BWOODMAN2009/08/26					3 PLACES	±---	±.005	CHECKED BY DATE					
					2 PLACES	±0.13	±.01	BWOODMAN 2009/08/25		MOLEX INCORPORATED			
		1 PLACE	±0.3	±.020	APPROVED BY DATE								
			ANGULAR ±1/2°			JFMURPHY 2009/08/26		DOCUMENT NO.					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.		SHEET NO.					
						SEE CHART		SD-130017-008					
B		REV				SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
						C							