



SMD Power Inductor CDRH4D18




Halogen
Free



Dimension - [mm]



Land pattern and Schematics - [mm]



Description

- Ferrite drum core construction.
- Magnetically shielded.
- $L \times W \times H$: $5.0 \times 5.0 \times 2.0$ mm Max.
- Product weight: 137mg(Ref.)
- Moisture Sensitivity Level: 1
- RoHS compliance.
- Halogen Free available.

Environmental Data

- Operating temperature range: $-40^{\circ}\text{C} \sim +100^{\circ}\text{C}$ (including coil's self temperature rise)
- Storage temperature range: $-40^{\circ}\text{C} \sim +100^{\circ}\text{C}$
- Solder reflow temperature: 260°C peak.

Packaging

- Carrier tape and reel packaging
- 7.0" diameter reel
- 1000pcs per reel

Applications

- Ideally used in Mobile phone, PDA, MP3, HDD, DSC/DVC, Note book PC, etc as DC-DC converter inductors.

SMD Power Inductor

CDRH4D18



Electrical Characteristics

Part No.	Stamp	Inductance (μ H) [within] ※1	D.C.R.(Ω) Max. (Typ.) (at 20°C)	Rated Current (A) ※2
CDRH4D18NP-1R0NC	1R0	1.0 $\pm$ 30%	45m(35m)	1.72
CDRH4D18NP-2R2NC	2R2	2.2 $\pm$ 30%	75m(58m)	1.32
CDRH4D18NP-2R7NC	2R7	2.7 $\pm$ 30%	105m(80m)	1.28
CDRH4D18NP-3R3NC	3R3	3.3 $\pm$ 30%	110m(85m)	1.04
CDRH4D18NP-3R9NC	3R9	3.9 $\pm$ 30%	155m(120m)	0.88
CDRH4D18NP-4R7NC	4R7	4.7 $\pm$ 30%	162m(125m)	0.84
CDRH4D18NP-5R6NC	5R6	5.6 $\pm$ 30%	170m(130m)	0.80
CDRH4D18NP-6R8NC	6R8	6.8 $\pm$ 30%	200m(155m)	0.76
CDRH4D18NP-8R2NC	8R2	8.2 $\pm$ 30%	245m (190m)	0.68
CDRH4D18NP-100NC	100	10 $\pm$ 30%	200m (148m)	0.61
CDRH4D18NP-120NC	120	12 $\pm$ 30%	210m (156m)	0.56
CDRH4D18NP-150NC	150	15 $\pm$ 30%	240m (178m)	0.50
CDRH4D18NP-180NC	180	18 $\pm$ 30%	338m (250m)	0.48
CDRH4D18NP-220NC	220	22 $\pm$ 30%	397m (294m)	0.41
CDRH4D18NP-270NC	270	27 $\pm$ 30%	441m (327m)	0.35
CDRH4D18NP-330NC	330	33 $\pm$ 30%	694m (514m)	0.32
CDRH4D18NP-390NC	390	39 $\pm$ 30%	709m (525m)	0.30
CDRH4D18NP-470NC	470	47 $\pm$ 30%	922m (683m)	0.28
CDRH4D18NP-560NC	560	56 $\pm$ 30%	1.08 (800m)	0.26
CDRH4D18NP-680NC	680	68 $\pm$ 30%	1.30 (1.00)	0.24
CDRH4D18NP-820NC	820	82 $\pm$ 30%	1.56 (1.20)	0.22
CDRH4D18NP-101NC	101	100 $\pm$ 30%	1.73 (1.33)	0.20
CDRH4D18NP-121NC	121	120 $\pm$ 30%	2.39 (1.84)	0.18
CDRH4D18NP-151NC	151	150 $\pm$ 30%	2.67 (2.05)	0.15
CDRH4D18NP-181NC	181	180 $\pm$ 30%	4.00 (3.05)	0.14

※1. Inductance measuring condition: 1.0 μ H $\sim$ 8.2 μ H at 7.96 MHz
 10 μ H $\sim$ 180 μ H at 100 kHz


※2. Rated current: The DC current at which the inductance decreases to 65% of its nominal value or when $\Delta t=40^{\circ}\text{C}$, whichever is lower ($T_a=20^{\circ}\text{C}$).

SMD Power Inductor CDRH4D18



Saturation Current & Temperature Rise Graph

— L (20°C) — L (100°C) — ΔT















SMD Power Inductor CDRH4D18



Saturation Current & Temperature Rise Graph


— L (20°C) — L (100°C) — ΔT





SMD Power Inductor CDRH4D18



Saturation Current & Temperature Rise Graph



Solder Reflow Condition



Please refer to the sales offices on our website - <http://www.sumida.com>

Hong Kong

Tel. +852-2880-6781
FAX. +852-2565-9600
sales@hk.sumida.com

Saitama(Japan)

Tel. +81-48-691-7300
FAX. +81-48-691-7340
sales@jp.sumida.com

Chicago

Tel. +1-847-545-6700
FAX. +1-847-545-6720
sales@us.sumida.com

Shanghai

Tel. +86-21-5836-3299
FAX. +86-21-5836-3266
shanghai.sales@cn.sumida.com

Seoul

Tel. +82-2-6237-0777
FAX. +82-2-6237-0778
sales@kr.sumida.com

Obernzell

Tel. +49-8591-937-0
FAX. +49-8591-937-103
contact@eu.sumida.com

Shenzhen

Tel. +86-755-8291-0228
FAX. +86-755-8291-0338
shenzhen.sales@cn.sumida.com

Singapore

Tel. +65-6296-3388
FAX. +65-6841-4426
sales@sg.sumida.com

Neumarkt

Tel. +49-9181-4509-110
FAX. +49-9181-4509-310
infocomp@eu.sumida.com

Taipei

Tel. +886-2-8751-2737
FAX. +886-2-8751-2738
sales@tw.sumida.com

San Jose

Tel. +1-408-321-9660
FAX. +1-408-321-9308
sales@us.sumida.com