

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREDPORT, MINNESOTA

FED. MFR. CODE 91929

SWITCH - BASIC

CATALOG LISTING

4 HS12

4 HS12

M

DRAWING
NUMBER

ISSUE
3 10
X 2021

ISSUE

(M) 4 HS12
ISSUE 8

PAGE 1 OF 1
RELEASE NO. PR-2350

REPLACES

CHECK

REVISIONS

A CO-94122
TSM
12 MAR 99

CHECK

6 MAY 61

CHECK

REF

CHECK

6 MAY 61

CHECK

REF

CHECK

6 MAY 61

CHECK

REF

CHECK

6 MAY 61

CHECK

REF

CHECK

6 MAY 61

CHECK

REF

CHECK


6 MAY 61

CHECK

REF

CHECK

6 MAY 61



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA			SCALE FULL
OPERATING FORCE-----18-28 OZ	CONTACT ARRANGEMENT S P D T			DO NOT SCALE PRINT
RELEASE FORCE-----4 OZ MIN	LINE VOLTAGE	INDUCTIVE LOAD	RESISTIVE LOAD	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES
PRETRAVEL-----.085 MAX	28 VDC	8 AMP	15 AMP	TOLERANCES ARE:
DIFFERENTIAL TRAVEL-----.020 MAX	125 VAC	1 AMP	.5 AMP	ONE PLACE (.0) $\pm .030$
OVERTRAVEL-----.010 MIN				TWO PLACE (.00) $\pm .015$
				THREE PLACE (.000) $\pm .005$
				ANGLES $\pm$
				WEIGHT $\triangle 3$

FO-50378
FORMTEK