






MM 3D-MODEL: TM-11112-2410

BASE CAGE DETAILS
(APPLIES TO ALL CAGES IN THIS DRAWING)747540410
SHOWNNOTE:
EMI GASKET REMOVED FROM THIS VIEW FOR CLARITY.

360° SOFT ELASTOMERIC GASKET

INNER WALLS ARE CONED
OVER BASE AND COVER FOR
EXTRA RIGIDITYNOTE:
EMI GASKET REMOVED FROM
THIS VIEW FOR CLARITY.

INNER WALL TABS WELDED

PART NO. AND WEEK/YEAR DATE CODE TO BE PRINTED ON THE
SIDE OF COMPLETED CAGE ASSEMBLY APPROXIMATELY AS SHOWN.

WEEK/YEAR DATE CODE TABLE

WW	01 THRU 52 OR 53	EXAMPLE: 01 = FIRST WEEK OF YEAR	52 = LAST WEEK OF YEAR
YY	15, 16, 17 ETC.	EXAMPLE: YEAR 2015 = 15	

NOTES:

1. MATERIAL:




- CAGE: 0.25mm THICK COPPER ALLOY, NICKEL PLATED.
SPRING FINGERS: 0.10mm THICK COPPER ALLOY, NICKEL PLATED.
HEATSINK: ALUMINUM, NICKEL PLATED.
HEATSINK SPRING CLIP: STAINLESS STEEL.
2. PRESS FIT LEGS 3.05mm (.120 INCH) LONG:
3. PORTS ARE DESIGNED FOR SFP+ TRANSCEIVERS AND ARE COMPATIBLE WITH SFP TRANSCEIVERS.
THE TOP SURFACE OF THE MODULE MUST BE FLAT (NO PRODUCT LABEL RECESS) AND THERMALLY CONDUCTIVE TO FUNCTION OPTIMALLY.
4. WELD SPOT MAY SHOW SLIGHT MATERIAL DISCOLORATION.
5. NO ROHS EXEMPTIONS.
6. CUSTOM HEATSINKS AVAILABLE UPON REQUEST.
7. MOST OF P/N ARE WITH 14.05 REF EXCEPT 747540415 & 747540419 ARE 12.55 REF.

SEE REVISION TABLE EC NO: CPG2016-2975 DRAWN: CHENG03 CHKD: APPR: CHEN08 REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	DESCRIPTION 2016/02/04	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 3:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	TITLE SFP+ 1X4 CAGE, 3.05MM PRESS FIT, HEAT SINK, ELASTOMERIC GASKET molex SD-11112-2410	DOCUMENT NO.	SHEET NO. 1 OF 9
			mm	INCH	DRAWN BY JHATTON	DATE 2012/12/03						
			4 PLACES ± ---	± ---	CHECKED BY MCKERVEY	DATE 2012/12/07						
			3 PLACES ± ---	± ---	APPROVED BY KLLOYD	DATE 2012/12/20						
			2 PLACES ± 0.13	± ---								
			1 PLACE ± 0.25	± ---								
			0 PLACE ± ---	± ---								
			ANGULAR ± 1°		MATERIAL NO.							
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 3							
					SIZE D THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

OPTIONAL GEN 2 UNDER BELLY GASKET

100114-0410

SHOWN




1. OPTIONAL UNDER BELLY GASKET ATTACHED TO BOTTOM OF CAGE (SEE P/N TABLES FOR AVAILABLE ASSEMBLIES)

ENTER DESCRIPTION EC NO: CPG2016-2975 DRAWN BY: CHYD CHECKED BY: APPR: RCHEN08 DATE: 2016/02/04	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
				MM ONLY		3:1	METRIC		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
				SEE TABLE		SD-111112-2410		3 OF 9	
				SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			


PART NUMBER SELECTION

1111120410
SHOWN



OPEN TOP BASE CAGE FOR HEATSINK			
PART NO.	POLYIMIDE INSULATOR	# OF REAR LEGS PER PORT	
1111120410	---	1A, 1B	
1111120450	YES	1A, 1B	


1111122410
SHOWN



PIN FIELD HEATSINK OPTION			
PART NO.	POLYIMIDE INSULATOR	HEATSINK	# OF REAR LEGS PER PORT
1111121410	---	PCI	1A, 1B
1111121450	YES	PCI	1A, 1B
1111122410	---	SAN	1A, 1B
1111122450	YES	SAN	1A, 1B
1111123410	---	NET	1A, 1B
1111123450	YES	NET	1A, 1B


NOTE: PCI - 13 ROWS
SAN - 11 ROWS
NET - 10 ROWS

1111125410
SHOWN




LATERAL FIN HEATSINK OPTION			
PART NO.	POLYIMIDE INSULATOR	HEATSINK	# OF REAR LEGS PER PORT
1111124410	---	PCI	1A, 1B
1111124450	YES	PCI	1A, 1B
1111125410	---	SAN	1A, 1B
1111125450	YES	SAN	1A, 1B
1111126410	---	NET	1A, 1B
1111126450	YES	NET	1A, 1B

1111128410
SHOWN




WIDE GAP PIN FIELD HEATSINK OPTION			
PART NO.	POLYIMIDE INSULATOR	HEATSINK	# OF REAR LEGS PER PORT
1111127410	---	PCI	1A, 1B
1111127450	YES	PCI	1A, 1B
1111128410	---	SAN	1A, 1B
1111128450	YES	SAN	1A, 1B
1111129410	---	NET	1A, 1B
1111129450	YES	NET	1A, 1B

747540410
SHOWN



SFP+ CLOSED TOP BASE CAGE			
PART NO.	POLYIMIDE INSULATOR	# OF REAR LEGS PER PORT	ELASTOMERIC GASKET FLAMMABILITY RATING
747540410	---	1A, 1B	
747540411	---	3A	
747540415	---	1A, 1B	
747540419	---	1A, 1B	
747540470	---	1A, 1B	EQUATE TO UL94 V-0

1001140410
SHOWN



zSFP+ CLOSED TOP BASE CAGE W/ GEN 2 BELLY GASKET		
PART NO.	# OF REAR LEGS PER PORT	FLAMMABILITY RATING
1001140410	1A, 1B	N/A
1001144410	1A, 1B	UL94 V-0

SEE REVISION TABLE EC NO: CPG2016-2975 DRAWN: CHENG03 CHKD: CHENG03 APPR: CHENG03 DATE: 2016/02/03	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY	SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
		4 PLACES ± 0.13 mm 3 PLACES ± 0.25 mm 2 PLACES ± 0.50 mm 1 PLACE ± 1.00 mm 0 PLACE ± 1.50 mm		DRAWN BY: JHATTON DATE: 2012/12/03	CHECKED BY: MMCKERVEY DATE: 2012/12/07	APPROVED BY: KLOYD DATE: 2012/12/20	TITLE SFP+ 1X4 CAGE, 3.05MM PRESS FIT, HEAT SINK, ELASTOMERIC GASKET
		ANGULAR ± 1° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE TABLE	DOCUMENT NO. SD-11112-2410	SHEET NO. 4 OF 9	molex
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

PCB LAYOUT FOR SINGLE SIDE MOUNT

HATCHED AREA DENOTES COMPONENTS AND TRACE KEEP-OUT (EXCEPT CHASSIS GROUND)

CROSS HATCHED AREA GOES TO CHASSIS GROUND (NO OSP) 4 PLCS

14X $\phi 1.05 \pm 0.05$ (SHOWN AS $\oplus$)
 $\phi 0.05$ AB

THIS AREA DENOTES COMPONENT KEEP-OUT (TRACES ALLOWED)

20X $\phi 0.95 \pm 0.05$ (SHOWN AS $\oplus$)
 $\phi 0.05$ AB

4X $\phi 0.95 \pm 0.05$ (SHOWN AS $\oplus$)
 $\phi 0.05$ AB
(OPTIONAL HOLES FOR CAGES WITH 3 REAR LEGS PER PORT)

TOP LEFT HOLE OF ADJACENT CAGE AT MINIMUM SPACING

HOST CONNECTOR DETAIL


DETAIL 1
SCALE 8:1

NOTES:

1. PADS AND VIAS CONNECT TO CHASSIS GROUND (RECOMMENDED PADS TO BE 2.00mm SQUARE)
2. RECOMMENDED THRU HOLE PLATING INCLUDES HASL, OSP, OR IMMERSION (GOLD, SILVER, OR TIN)
3. CONNECTOR PAD LAYOUT PER SFP+ MSA WILL ACCOMMODATE MOLEX CONNECTOR SERIES 74441 OR EQUIVALENT
4. HOLE PATTERN REPEATS FOR EACH PORT, SPACING BETWEEN PORTS IS 14.25mm
5. MINIMUM PCB THICKNESS FOR SINGLE SIDED USE 1.57mm [0.062"].

SEE REVISION TABLE		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO:	CPG2016-2975	DATE	2016/02/03	mm	INCH	MM ONLY	DATE	5:1	METRIC				
DRAWN BY	JHATTON	CHECKED BY	MMCKERVEY	4 PLACES $\pm$ ---	$\pm$ ---		DATE						
CHKO:	APPROV: CHEN08	DATE	2012/12/07	3 PLACES $\pm$ ---	$\pm$ ---		DATE						
		DATE	2012/12/20	2 PLACES ± 0.13	$\pm$ ---								
				1 PLACE ± 0.25	$\pm$ ---								
				0 PLACE $\pm$ ---	$\pm$ ---								
				ANGULAR $\pm 1^\circ$		MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 3		SD-111112-2410		5 OF 9			
						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

PCB LAYOUT FOR BELLY TO BELLY MOUNTING




NOTE:
SEE SHEET 5 FOR HOST
CONNECTOR DETAIL

NOTES:

1. PADS AND VIAS CONNECT TO CHASSIS GROUND (RECOMMENDED PADS TO BE 2.00mm SQUARE)
2. RECOMMENDED THRU HOLE PLATING INCLUDES HASL, OSP, OR IMMERSION (GOLD, SILVER, OR TIN)
3. CONNECTOR PAD LAYOUT PER SFP+ MSA WILL ACCOMMODATE MOLEX CONNECTOR SERIES 74441 OR EQUIVALENT
4. HOLE PATTERN REPEATS FOR EACH PORT, SPACING BETWEEN PORTS IS 14.25mm
5. MINIMUM PCB THICKNESS FOR BELLY TO BELLY USE 3.00mm [0.118"]



SEE REVISION TABLE EC NO. (P52)016-2975 H CHKO- APPROVED 2016/02/03 REV	DESCRIPTION 2016/02/04	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE 5:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION			
					MM ONLY							
				mm	INCH	DRAWN BY				DATE	TITLE	
			$\nabla=0$	4 PLACES $\pm$	$\pm$	JHATTON				2012/12/03	SFP+ 1X4 CAGE, 3.05MM PRESS FIT, HEAT SINK, ELASTOMERIC GASKET	
			$\nabla=0$	3 PLACES $\pm$	$\pm$	CHECKED BY				DATE	molex SD-11112-2410	
			$\nabla=0$	2 PLACES ± 0.13	$\pm$	MMCKERVEY				2012/12/07		6 OF 9
			$\nabla=0$	1 PLACE ± 0.25	$\pm$	APPROVED BY				DATE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION
			$\nabla=0$	0 PLACE $\pm$	$\pm$	KLLOYD				2012/12/20		
			ANGULAR $\pm 1^\circ$		MATERIAL NO.					DOCUMENT NO.		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 3					SD-11112-2410		

POLYIMIDE INSULATOR COVERAGE AREA
(APPLIES TO SINGLE SIDED AND BELLY TO BELLY)





REVISION DATE DESCRIPTION APPROVED BY	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
				DRAWN BY JHATTON		DATE 2012/12/03	TITLE SFP+ 1X4 CAGE, 3.05MM PRESS FIT, HEAT SINK, ELASTOMERIC GASKET molex	
				CHECKED BY MMCKERVEY		DATE 2012/12/07		
				APPROVED BY KLLOYD		DATE 2012/12/20		
REVISION DATE DESCRIPTION APPROVED BY	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	ANGULAR ± 1 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 3		SD-11112-2410		7 OF 9
				SIZE D		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		

BEZEL AND BOARD POSITION DIMENSIONS FOR SINGLE SIDE MOUNTING
(ELASTOMERIC GASKET)



BEZEL AND BOARD POSITION DIMENSIONS FOR BELLY TO BELLY MOUNTING
(ELASTOMERIC GASKET)



- NOTE:
1. PCB THICKNESS VARIATION MUST BE CONSIDERED WHEN DETERMINING BEZEL OPENING LOCATION.
 2. CAGE LEG STANDOFF WILL PIERCE BELLY GASKET WHEN PROPERLY PRESSED INTO PCB.

SEE REVISION TABLE EC NO. : EP3204-2975 DRAWN: CHEN03 2016/02/03 CHKD: CHEN03 APPR: CHEN08 2016/02/04	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION					
					DRAWN BY JHATTON	DATE 2012/12/03	TITLE SFP+ 1X4 CAGE, 3.05MM PRESS FIT, HEAT SINK, ELASTOMERIC GASKET									
					CHECKED BY MMCKERVEY	DATE 2012/12/07	molex SEE SHEET 3SD-11112-2410									
					APPROVED BY KLLOYD	DATE 2012/12/20										
					MATERIAL NO.								DOCUMENT NO.		SHEET NO.	
					SIZE								8 OF 9			
					ANGULAR ± 1 °		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											

DATE	REV	DESCRIPTION
2012/12/03	A	1. INITIAL RELEASE
2013/01/23	B	1. REMOVED EMI GASKET FROM TOP, ØI16, AND RIGHT SIDE, ØE12, VIEWS FOR CLARITY. ADDED EMI GASKET UNCOMPRESSED OVERALL DIMENSIONS TO FRONT VIEW, ØE16. ADDED 9.98 REF DIM. TO SIDE VIEW. ADDED BACK VIEW W/INNER WALL WELD NOTE, ØE3. REMOVED BELLY ISO VIEW CHANGED ALL VIEWS ON SHEET 1 TO 747540410 CLOSED TOP BASE CAGE. MOVED MIN PCB THICKNESS NOTE TO RESPECTIVE PCB LAYOUT SHEETS. REMOVED INSERTION FORCE FROM NOTE 2. UPDATED PN/DATE CODE PRINTING CALLOUT ON SIDE VIEW. ADDED FIX TEXT OVERALL LENGTH TO DIM. 49.0 REF ØJ14. ADDED APPLICATION NOTE ØM10. ADDED TYP TO DIMENSION 3.05 REF ON SIDE VIEW ØE8 (SHEET 1). 2. ADDED 'REAR LEG OPTIONS' SECTION, ØB16. REMOVED CAGES FROM HEATSINK OPTIONS VIEWS & UPDATED TABLES, ØJ2, J6 & J11. MOVED BELLY VIEW TO, D9. ADDED BELLY VIEW ØD3. ADDED OPEN TOP VIEW Ø17. ADDED OVERALL HEATSINK NOTE TO TABLES Ø12, I6, & I11. ADDED ▽ & ▽ TO ISO BELLY VIEW ØD3. (SHEET 2). 3. ADDED PN'S 747540410, 747540411, 747540415, 747540419 & 1111110410 ADDING VIEWS AND PN TABLES. ADDED # OF REAR LEGS PER PORT COLUMN TO TABLES. (SHEET 3) 4. REMOVED BASIC TOLERANCE FROM DIMENSION 35.4 TYP, ØF8. ADDED MIN PCB THICKNESS NOTE. ADDED DIAMETER DIMENSION Ø0.95 ± 0.05 X4 ØD15. MOVED TYP FROM DIMENSION BOXES. ADDED DATUM A & DATUM B. ADDED NOTES 1 THRU 4. (SHEET 4) 5. REMOVED BASIC TOLERANCE FROM DIMENSION 35.4 TYP, ØF5. ADDED MIN PCB THICKNESS NOTE. REMOVED PAD ØF14. ADDED NOTES 1 THRU 4. (SHEET 5). 6. REMOVED BELLY TO BELLY PCB VIEW, CENTERED SINGLE SIDED VIEW AND ADDED APPLICATION NOTE TO SHEET TITLE. REMOVED DIMENSION 1.7 REF (SHEET 6) 7. CHANGED TOLERANCE ON DIMENSIONS 0.19 TO 0.19 ±0.10, ØD9 & F9. ADDED CENTER LINES TO BEZELS. REMOVED 'CUTAWAY'S FROM SIDE VIEWS. REMOVED 'SEE NOTE 1' FROM 10.6 ±0.1 BEZEL OPENING SIZE DIMENSIONS ØD10 & E10. REMOVED 'SIZE, AND' FROM NOTE 1. ADDED 'SEE NOTE 1' TO BELLY TO BELLY BEZEL OPENING PITCH. (SHEET 7) 8. MOVED NOTES TO BOTTOM LEFT CORNER AND INCREASED TEXT HEIGHT, (SHEETS 1, 4, 5 & 7). CHANGED DRAWING DIMENSION STYLE TO MM ONLY. CHANGED THE GENERAL ANGLE TOLERANCE TO 1° FOR ALL SHEETS.
2014/02/05	C	1. MOVED DATE CODE FROM VIEW ØE9 TO VIEW ØE5. REVISED NOTE 4 'WAS' WELD SPOT WILL SHOW SLIGHT MATERIAL DISCOLORATION. 'NOW READS' WELD SPOT MAY SHOW SLIGHT MATERIAL DISCOLORATION SHEET 1. 2. MOVED VIEW ØE4 SHEET 2 TO THE REVISED SHEET 3 ØK4. ADDED VIEW AND DATE CODE ØE5. 3. ADDED NEW SHEET 3: PREVIOUS SHEET 3-8 INCREASED BY ONE NUMBER. ADDED NOTE 1 ØA20. REMOVED NOTE FROM ISO VIEW ØI6. 4. ADDED VIEW ØF8 AND REVISED PART NUMBER 'WAS' 747540410. 'NOW READS' 1111110410 ØG12 SHEET 4.
2014/05/12	D	1. ADDED P/N 74754-0470 [SHEET 4]
2014/09/09	E	1. ADDED P/N 100114-4410. [SHEET 4]
2015/07/16	F	1. REVISED COLUMN LABEL UL RATING TO FLAMMABILTY RATING IN TABLE ØD7. 2. REVISED PART NO. 100114-4410 NOTES ØD7 'WAS' UL TESTING PENDING. 'NOW' UL94 V-0. SHEET 4 3. ADDED NOTE 2 ØA20. SHEET 8
2015/10/26	G	SHEET 1: A19: ADDED NOTE '7. MOST OF P/N ARE WITH 14.05 REF EXCEPT 747540415 & 747540419 ARE 12.55 REF'. E12: CHANGED '14.05 REF (ACROSS FRAME)' TO 'SEE NOTE 7. (ACROSS FRAME)'.
2016/02/03	H	1. SHEET 3 & 4: REMOVE 1111110410.

SEE REVISION TABLE EC NO. CPG2016-2975 DRAWN BY: CHEN CHKD: CHEN APPROVED BY: CHEN REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
					DRAWN BY JHATTON	DATE 2012/12/03	TITLE SFP+ 1X4 CAGE, 3.05MM PRESS FIT, HEAT SINK, ELASTOMERIC GASKET			
					CHECKED BY MMCKERVEY	DATE 2012/12/07	molex			
					APPROVED BY KLLOYD	DATE 2012/12/20				
			ANGULAR ± 1 °		MATERIAL NO. SEE SHEET 3		DOCUMENT NO. SD-111112-2410			SHEET NO. 9 OF 9
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					