



EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : DDF-511-033 REV: 1.0

0.56" Quadruple Digit Displays

MODEL NO : ELF-511UYOWA/S530-A2 ECN : Page: 1/5

■ Features :

- Industrial standard size.
- Low power consumption.
- Categorized for luminous intensity.

■ Applications:

- Audio equipment
- Instrument panels
- Digital readout display

■ Description :

- The ELT-512 series is a large 14.22mm (0.56")high seven segment display design for viewing distances up to 7 meters.
- These displays provide excellent reliability in bright ambient light.
- These device is made with white segments and gray surface.

PART NO	CHIP		C.C. or C.A.
	Material	Emitted Color	
ELF-511UYOWA/S530-A2	AlGaInP	Super Yellow Orange	C.C.

OFFICE : NO. 25,Lane 76,Sec.3, Chung Yang Rd., Tucheng 236, Taipei, Taiwan, R.O.C.

TEL : 886-2-2267-2000,2267-9936


FAX : 886-2-2267-6244,22676189,22676306

<http://www.everlight.com>


0.56" Quadruple Digit Displays

MODEL NO : ELF-511UYOWA/S530-A2 ECN : Page: 2/5

■ Package Dimension:



COMMON CATHODE
 1 ANODE E
 2 ANODE D
 3 ANODE DP
 4 ANODE C
 5 ANODE G
 6 COMMON CATHODE D4
 7 ANODE B
 8 COMMON CATHODE D3
 9 COMMON CATHODE D2
 10 ANODE F
 11 ANODE A
 12 COMMON CATHODE D1



■ NOTES:

- 1.All dimensions are millimeters , tolerance is 0.25mm unless otherwise noted.
 - 2.Above specification may be changed without notice.
- Supplier will reserve authority on material change for above specification.



0.56" Quadruple Digit Displays

MODEL NO : ELF-511UYOWA/S530-A2 ECN : Page: 3/5

■ Absolute maximum ratings at Ta = 25℃ :

Parameter	Symbol	Rating	Unit
Reverse Voltage	Vr	5	V
Forward Current	If	25	mA
Operating Temperature	Topr	-40 to +85	℃
Storage Temperature	Tstg	-40 to +100	℃
Soldering Temperature	Tsol	260 ± 5	℃
Electrostatic Discharge	ESD	2000	V
Power Dissipation	Pd	60	mW
Peak Forward Current(Duty 1/10 @ 1KHZ)	If(Peak)	160	mA

■ Electronic optical characteristics :

Parameter		Symbol	MIN.	TYP.	MAX.	Unit	Condition
Luminous	Per	Iv	0.75	2.6	----	mcd	If=2mA
	segment		5.60	17.0	----	mcd	If=10mA
Intensity	Per		0.28	1.40	----	mcd	If=2mA
	decimal point		2.80	7.80	----	mcd	If=10mA
Peak Wavelength		λ p	----	611	----	nm	If=20mA
Dominant Wavelength		λ d	----	605	----	nm	If=20mA
Spectrum Radiation Bandwidth		△ λ	----	17.0	----	nm	If=20mA
Forward Voltage		Vf	----	2.0	2.4	V	If=20mA
Reverse Current		Ir	----	----	10	μ A	Vr=5V



EVERLIGHT ELECTRONICS CO.,LTD.

Device Number :

DDF-511-033

REV:

1.0

0.56" Quadruple Digit Displays

MODEL NO : ELF-511UYOWA/S530-A2

ECN :

Page:

4/5

Reliability test item and condition:

NO	Item	Test Conditions	Test Hours/Cycle	Sample Size	Ac/Re
1	Solder Heat	TEMP : 260°C ± 5 °C	5 SEC	76 PCS	0/1
2	Temperature Cycle	H : +85°C 30min ∫ 5 min L : -55°C 30min	50 CYCLE	76 PCS	0/1
3	Thermal Shock	H : +100°C 5min ∫ 10 sec L : -10°C 5min	50 CYCLE	76 PCS	0/1
4	High Temperature Storage	TEMP : 100°C	1000 HRS	76 PCS	0/1
5	Low Temperature Storage	TEMP : -55°C	1000 HRS	76 PCS	0/1
6	DC Operating Life	If = 10 mA	1000 HRS	76 PCS	0/1
7	High Temperature / High Humidity	85°C/85% RH	1000 HRS	76 PCS	0/1



EVERLIGHT ELECTRONICS CO.,LTD.

Device Number :

DDF-511-033

REV:

1.0

0.56" Quadruple Digit Displays

MODEL NO: ELF-511UYOWA/S530-A2


ECN :

Page:


5/5

Typical Electro-Optical Characteristic Curves:

Forward Current Derating Curve
 $T_a=25^\circ$



Spectrum Distribution
 $T_a=25^\circ$



Forward Current vs. Forward Voltage

