

A			B			C			D			E			F			G			H		
DWG. NO.			ZONE			REV.			DESCRIPTION			DATE			APPROVED								
010-0X3						X1			CUSTOMER APPROVAL			12/22/98			C.V.								
						X2			CHANGE RETRACTED LENGTH FROM 13' TO 24'			12/29/98			C.V.								
						A			PRODUCTION RELEASE			01/04/99			C.V.								
						B			CHAGNE TO ROHS			02/15/06			M.G.								

NOTES: UNLESS OTHERWISE SPECIFIED.

1.0 MATERIAL AND SPECIFICATIONS

- 1.01 CONDUCTORS: 26 AWG (12/0.12 mm) STRANDED BARE COPPER.
- 1.02 INSULATION: POLYPROPYLENE
- 1.03 COLOR: PER CALLOUT

2.0 ELECTRICAL CHARACTERISTICS

- 2.01 TEMPERATURE & VOLTAGE RATING: 80°C 30 V
- 2.02 CONDUCTORS RESISTANCE: 148 OHMS/KM MAX. AT 20°C
- 2.03 INSULATION RESISTANCE: 100 MEGOHMS/KM MIN. AT 20°C
- 2.04 CAPACITANCE: 15 PF/FT (MAX)

2.05 DIELECTRIC TEST: AC-500V PER 1 MINUTE

3.0 PACKAGING SPECIFICATION

- 3.01 USE CLEAR TAPE TO BUNDLE 25 CABLES TOGETHER AT THE MID SECTION.
- 3.02 PLACE PLASTIC BAG IN SHIPPING BOX AND LAY 10 BUNDLE OR 250 PIECES MAX. PER SHIPPING BOX. CLOSE PLASTIC BAG AND SEAL BOX ALONG 3 SURFACES WITH TAPE.
- 3.03 MAX. DIMENSION OUTSIDE SHIPPING BOX IS L=13.00' x W=25.00' x H=9.00'.

GLF-121-010-003	10	SILVER SATIN	[0.748 REF.] 19.00 REF.
GLF-121-010-013	10	BLACK	[0.748 REF.] 19.00 REF.
GLF-121-010-023	10	WHITE	[0.748 REF.] 19.00 REF.
I/O INTERCONNECT	NUMBER OF CONDUCTORS	COLOR	ø "A"



THIRD ANGLE PROJECTION

UNLESS OTHERWISE NOTED:
1) DIMENSIONS ARE IN MILLIMETER [INCHES]
2) TOLERANCES:
X.X ± 0.20 [0.008]
X.XX ± 0.25 [0.010]

TR. BY: CHAU HAI TR. CHECKER: MEJ

TITLE: 26 AWG (12/0.12 mm) BARE COPPER, 500 FT EXTENDED, 10P 10C NON-UL, UNSHIELD, MODULAR CABLE

PART NO: GLF-121-010-0X3

DWG NO: GLF-121-010-0X3

CUSTOMER: DIGI KEY


REV: B

SCALE: NONE



SHEET 1 OF 1

I/O INTERCONNECT

SANTA ANA, CALIFORNIA



10 CONDUCTOR CABLE



BUNDLE SPECIFICATION