



CIRCUIT: SPDT

## CONTACT CONFIGURATION



| SWITCH FUNCTION                                                                     |                                                                                     |                                                                                     |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| POS. 1                                                                              | POS. 2                                                                              | POS. 3                                                                              |
|  |  |  |
| DN                                                                                  | NONE                                                                                | DN                                                                                  |
| 2-3                                                                                 | OPEN                                                                                | 2-1                                                                                 |



RECOMMENDED P.C.B. LAYOUT

NOTES:

1. ALL DIMENSIONS IN MM [INCH] [-200]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 3A @120VAC or 28VDC;  
1A @250VAC.



5. FIXED TERMINAL/MOVING CONTACT MATERIAL:  
COPPER ALLOY w/Silver plate.
6. ELECTRIC LIFE: 30,000 make-and-break cycles  
at full load.
7. INSULATION RESISTANCE: 1,000 M ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
9. OPERATING TEMP. -30°C to +85°C
10. ▲ DESIGNATE MAUDR FEATURE
11. ACTUATOR: NYLON, BLACK STD.

|                                    |  |                  |           |                |          |
|------------------------------------|--|------------------|-----------|----------------|----------|
| <b>E-SWITCH®</b>                   |  |                  |           |                |          |
| TITLE<br>400A WMSPP-1 R1 BLK M6 QE |  |                  |           |                |          |
| SCALE<br>2:1                       |  | DATE<br>10/17/02 | DR<br>CJB | DWG<br>T403110 | REV<br>B |