

HBL7506C -- Twist-Lock Connector Body




2P2W, 15A 125V, L1-15R, Black & White Nylon

Product Specifications

Product Type	 Twist-Lock Devices
Product Item	Connector Body
Wiring Scheme	2 Pole, 2 Wire Non-Grounding
Amperage	15A
Voltage	125V AC
NEMA Configuration	L1-15P
Item Style	Standard
Device Color	Black/White
Cord Dia.	.230"-.720" (5.8-18.3)
Terminal Retainer Material	Clear polycarbonate
Housing Material	Black nylon
Cord Clamp Material	Natural (white) nylon
Terminal Clamp Material	.062" cold rolled steel-nickel-plated
Terminal Screw Material	#8-32 Brass (white finish on neutral screw when used)
Cord Clamp Screw Material	Steel - zinc plated Multi-drive

Body Holding Screw Material	Steel, zinc plated Multi-drive
Body Contact Carrier Material	Natural White Nylon
Contact Spring Material	Brass
Spring Binding Plate Material	Brass
Ratings	Molded into face.
Catalog No.	Permanently ink marked on body.
Dielectric Voltage Withstand	2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
Cord Accommodation	Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62, CSA C22.2 No. 49.
Terminal Accommodation	15A #14AWG
Terminal Identification	Terminals identified in accordance with UL 498 (Black, White)
Flammability	UL 94 VO for Receptacles and Inlets. HB or better for Plugs and Connectors.
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)
Moisture Resistance	IP20
Listings	UL
Catalog Page	Click here for catalog page B3
Hubbellnet	Click here for Hubbellnet
Catalog Section	Click here for Section-B
UPC Number	78358517790
Weight in LBs	0.15



Hubbell Incorporated (Delaware)
185 Plains Road
Milford, CT 06460-2420
Ph: (203) 882-4800
Fax: (800) 255-1031

