Is Now Part of

ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at
www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

FAIRCHILD SEMICONDUCTOR™

January 2000
Revised June 2005

74VCX162373

Low Voltage 16-Bit Transparent Latch with 3.6V Tolerant Inputs and Outputs and 26Ω Series Resistors in Outputs

General Description

The VCX162373 contains sixteen non-inverting latches with 3-STATE outputs and is intended for bus oriented applications. The device is byte controlled. The flip-flops appear to be transparent to the data when the Latch enable (LE) is HIGH. When LE is LOW, the data that meets the setup time is latched. Data appears on the bus when the Output Enable ($\overline{OE}$) is LOW. When $\overline{OE}$ is HIGH, the outputs are in a high impedance state.

The VCX162373 is also designed with 26Ω resistors in the outputs. This design reduces line noise in applications such as memory address drivers, clock drivers and bus transceivers/transmitters.

The 74VCX162373 is designed for low voltage (1.4V to 3.6V) V_{CC} applications with I/O compatibility up to 3.6V.

The 74VCX162373 is fabricated with an advanced CMOS technology to achieve high speed operation while maintaining low CMOS power dissipation.

Features

- 1.4V–3.6V V_{CC} supply operation
- 3.6V tolerant inputs and outputs
- 26Ω series resistors in outputs
- t_{PD} (I_n to O_n)
  3.3 ns max for 3.0V to 3.6V V_{CC}
- Power-off high impedance inputs and outputs
- Support live insertion and withdrawal (Note 1)
- Static Drive (I_{OH}/I_{OL})
  ±12 mA @ 3.0V V_{CC}
- Uses proprietary noise/EMI reduction circuitry
- Latch-up performance exceeds 300 mA
- ESD performance:
  Human body model > 2000V
  Machine model > 200V

Note 1: To ensure the high-impedance state during power up or power down, $\overline{OE}$ should be tied to V_{CC} through a pull-up resistor; the minimum value of the resistor is determined by the current-sourcing capability of the driver.

Ordering Code:

Ordering Number	Package Number	Package Description
74VCX162373MTD	MTD48	48-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 6.1mm Wide

Devices also available in Tape and Reel. Specify by appending suffix letter "X" to the ordering code.

Logic Symbol



Pin Descriptions

Pin Names	Description
$\overline{OE}_n$	Output Enable Input (Active LOW)
LE_n	Latch Enable Input
I_0–I_{15}	Inputs
O_0–O_{15}	Outputs

Connection Diagram



Truth Tables

Inputs			Outputs
LE_1	$\overline{OE}_1$	I_0–I_7	O_0–O_7
X	H	X	Z
H	L	L	L
H	L	H	H
L	L	X	O_0

Inputs			Outputs
LE_2	$\overline{OE}_2$	I_8–I_{15}	O_8–O_{15}
X	H	X	Z
H	L	L	L
H	L	H	H
L	L	X	O_0

H = HIGH Voltage Level
L = LOW Voltage Level
X = Immaterial (HIGH or LOW, inputs may not float)
Z = High Impedance
O_0 = Previous O_0 before HIGH-to-LOW of Latch Enable

Functional Description

The 74VCX162373 contains sixteen edge D-type latches with 3-STATE outputs. The device is byte controlled with each byte functioning identically, but independent of the other. Control pins can be shorted together to obtain full 16-bit operation. The following description applies to each byte. When the Latch Enable (LE_n) input is HIGH, data on the I_n enters the latches. In this condition the latches are transparent, i.e., a latch output will change state each time its I input changes. When LE_n is LOW, the latches store information that was present on the I inputs a setup time preceding the HIGH-to-LOW transition on LE_n. The 3-STATE outputs are controlled by the Output Enable ($\overline{OE}_n$) input. When $\overline{OE}_n$ is LOW the standard outputs are in the 2-state mode. When $\overline{OE}_n$ is HIGH, the standard outputs are in the high impedance mode but this does not interfere with entering new data into the latches.

Logic Diagram



Please note that this diagram is provided only for the understanding of logic operations and should not be used to estimate propagation delays.

Absolute Maximum Ratings (Note 2)

Supply Voltage (V_{CC})	−0.5V to +4.6V
DC Input Voltage (V_I)	−0.5V to +4.6V
Output Voltage (V_O)	
Outputs 3-STATED	−0.5V to +4.6V
Outputs Active (Note 3)	−0.5V to V_{CC} +0.5V
DC Input Diode Current (I_{IK}) V_I < 0V	−50 mA
DC Output Diode Current (I_{OK})	
V_O < 0V	−50 mA
V_O > V_{CC}	+50 mA
DC Output Source/Sink Current	
(I_{OH}/I_{OL})	±50 mA
DC V_{CC} or GND Current per	
Supply Pin (I_{CC} or GND)	±100 mA
Storage Temperature Range (T_{STG})	−65°C to +150°C

Recommended Operating Conditions (Note 4)

Power Supply	
Operating	1.4V to 3.6V
Input Voltage	−0.3V to +3.6V
Output Voltage (V_O)	
Output in Active States	0V to V_{CC}
Output in "OFF" State	0.0V to 3.6V
Output Current in I_{OH}/I_{OL}	
V_{CC} = 3.0V to 3.6V	±12 mA
V_{CC} = 2.3V to 2.7V	±8 mA
V_{CC} = 1.65V to 2.3V	±3 mA
V_{CC} = 1.4V to 1.6V	±1 mA
Free Air Operating Temperature (T_A)	−40°C to +85°C
Minimum Input Edge Rate ($\Delta t/\Delta V$)	
V_{IN} = 0.8V to 2.0V, V_{CC} = 3.0V	10 ns/V

Note 2: The Absolute Maximum Ratings are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the Electrical Characteristics tables are not guaranteed at the Absolute Maximum Ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

Note 3: I_O Absolute Maximum Rating must be observed.

Note 4: Floating or unused inputs must be held HIGH or LOW.

DC Electrical Characteristics

Symbol	Parameter	Conditions	V_{CC} (V)	Min	Max	Units
V_{IH}	HIGH Level Input Voltage		2.7 - 3.6	2.0		V
			2.3 - 2.7	1.6		
			1.65 - 2.3	0.65 x V_{CC}		
			1.4 - 1.6	0.65 x V_{CC}		
V_{IL}	LOW Level Input Voltage		2.7 - 3.6		0.8	V
			2.3 - 2.7		0.7	
			1.65 - 2.3		0.35 x V_{CC}	
			1.4 - 1.6		0.35 x V_{CC}	
V_{OH}	HIGH Level Output Voltage	I_{OH} = −100 μA	2.7 - 3.6	V_{CC} - 0.2		V
		I_{OH} = −6 mA	2.7	2.2		
		I_{OH} = −8 mA	3.0	2.4		
		I_{OH} = −12 mA	3.0	2.2		
		I_{OH} = −100 μA	2.3 - 2.7	V_{CC} - 0.2		
		I_{OH} = −4 mA	2.3	2.0		
		I_{OH} = −6 mA	2.3	1.8		
		I_{OH} = −8 mA	2.3	1.7		
		I_{OH} = −100 μA	1.65 - 2.3	V_{CC} - 0.2		
		I_{OH} = −3 mA	1.65	1.25		
		I_{OH} = −100 μA	1.4 - 1.6	V_{CC} - 0.2		
		I_{OH} = −1 mA	1.4	1.05		

DC Electrical Characteristics (Continued)

Symbol	Parameter	Conditions	V_{CC} (V)	Min	Max	Units
V_{OL}	LOW Level Output Voltage	I_{OL} = 100 μA	2.7 - 3.6		0.2	
		I_{OL} = 6 mA	2.7		0.4	
		I_{OL} = 8 mA	3.0		0.55	
		I_{OL} = 12 mA	3.0		0.8	
		I_{OL} = 100 μA	2.3 - 2.7		0.2	
		I_{OL} = 6 mA	2.3		0.4	V
		I_{OL} = 8 mA	2.3		0.6	
		I_{OL} = 100 μA	1.65 - 2.3		0.2	
		I_{OL} = 3 mA	1.65		0.3	
		I_{OL} = 100 μA	1.4 - 1.6		0.2	
		I_{OL} = 1 mA	1.4		0.35	
I_I	Input Leakage Current	0 ≤ V_I ≤ 3.6V	1.4 - 3.6		±5.0	μA
I_{OZ}	3-STATE Output Leakage	0 ≤ V_O ≤ 3.6V, V_I = V_{IH} or V_{IL}	1.4 - 3.6		±10.0	μA
I_{OFF}	Power-OFF Leakage Current	0 ≤ (V_I, V_O) ≤ 3.6V	0		10.0	μA
I_{CC}	Quiescent Supply Current	V_I = V_{CC} or GND	1.4 - 3.6		20.0	μA
		V_{CC} ≤ (V_I, V_O) ≤ 3.6V (Note 5)	1.4 - 3.6		±20.0	μA
ΔI_{CC}	Increase in I_{CC} per Input	V_{IH} = V_{CC} –0.6V	2.7 - 3.6		750	μA

Note 5: Outputs disabled or 3-STATE only.

AC Electrical Characteristics (Note 6)

Symbol	Parameter	Conditions	V_{CC} (V)	T_A = −40°C to +85°C		Units	Figure Number
				Min	Max		
t_{PHL} t_{PLH}	Propagation Delay LE to O_n	C_L = 30 pF, R_L = 500Ω	3.3 ± 0.3	0.8	3.6	ns	Figures 1, 2
			2.5 ± 0.2	1.0	4.9		
			1.8 ± 0.15	1.5	9.8		
		C_L = 15 pF, R_L = 2kΩ	1.5 ± 0.1	1.0	19.6		Figures 7, 8
t_{PHL} t_{PLH}	Propagation Delay I_n to O_n	C_L = 30 pF, R_L = 500Ω	3.3 ± 0.3	0.8	3.3	ns	Figures 1, 2
			2.5 ± 0.2	1.0	4.5		
			1.8 ± 0.15	1.5	9.0		
		C_L = 15 pF, R_L = 2kΩ	1.5 ± 0.1	1.0	18.0		Figures 7, 8
t_{PZL} t_{PZH}	Output Enable Time	C_L = 30 pF, R_L = 500Ω	3.3 ± 0.3	0.8	3.9	ns	Figures 1, 3, 4
			2.5 ± 0.2	1.0	5.4		
			1.8 ± 0.15	1.5	9.8		
		C_L = 15 pF, R_L = 2kΩ	1.5 ± 0.1	1.0	19.6		Figures 7, 9, 10
t_{PLZ} t_{PHZ}	Output Disable Time	C_L = 30 pF, R_L = 500Ω	3.3 ± 0.3	0.8	4.0	ns	Figures 1, 3, 4
			2.5 ± 0.2	1.0	4.4		
			1.8 ± 0.15	1.5	7.9		
		C_L = 15 pF, R_L = 2kΩ	1.5 ± 0.1	1.0	15.8		Figures 7, 9, 10
t_S	Setup Time	C_L = 30 pF, R_L = 500Ω	3.3 ± 0.3	1.5		ns	Figures 1, 6
			2.5 ± 0.2	1.5			
			1.8 ± 0.15	2.5			
		C_L = 15 pF, R_L = 2kΩ	1.5 ± 0.1	3.0			Figures 6, 7
t_H	Hold Time	C_L = 30 pF, R_L = 500Ω	3.3 ± 0.3	1.0		ns	Figures 1, 6
			2.5 ± 0.2	1.0			
			1.8 ± 0.15	1.0			
		C_L = 15 pF, R_L = 2kΩ	1.5 ± 0.1	2.0			Figures 6, 7

AC Electrical Characteristics (Continued)

Symbol	Parameter	Conditions	V_{CC} (V)	$T_A = -40°C$ to $+85°C$		Units	Figure Number
				Min	Max		
t_W	Pulse Width	C_L = 30 pF, R_L = 500Ω	3.3 ± 0.3	1.5		ns	Figures 1, 5
			2.5 ± 0.2	1.5			
			1.8 ± 0.15	4.0			
		C_L = 15 pF, R_L = 2kΩ	1.5 ± 0.1	4.0			Figures 5, 7
t_{OSHL}	Output to Output Skew	C_L = 30 pF, R_L = 500Ω	3.3 ± 0.3		0.5	ns	
t_{OSLH}	(Note 7)		2.5 ± 0.2		0.5		
			1.8 ± 0.15		0.75		
		C_L = 15 pF, R_L = 2kΩ	1.5 ± 0.1		1.5		

Note 6: For $C_L = 50_P$F, add approximately 300 ps to the AC maximum specification.

Note 7: Skew is defined as the absolute value of the difference between the actual propagation delay for any two separate outputs of the same device. The specification applies to any outputs switching in the same direction, either HIGH-to-LOW (t_{OSHL}) or LOW-to-HIGH (t_{OSLH}).

Dynamic Switching Characteristics

Symbol	Parameter	Conditions	V_{CC} (V)	$T_A = +25°C$ Typical	Units
V_{OLP}	Quiet Output Dynamic Peak V_{OL}	C_L = 30 pF, $V_{IH} = V_{CC}$, V_{IL} = 0V	1.8	0.15	V
			2.5	0.25	
			3.3	0.35	
V_{OLV}	Quiet Output Dynamic Valley V_{OL}	C_L = 30 pF, $V_{IH} = V_{CC}$, V_{IL} = 0V	1.8	−0.15	V
			2.5	−0.25	
			3.3	−0.35	
V_{OHV}	Quiet Output Dynamic Valley V_{OH}	C_L = 30 pF, $V_{IH} = V_{CC}$, V_{IL} = 0V	1.8	1.55	V
			2.5	2.05	
			3.3	2.65	

Capacitance

Symbol	Parameter	Conditions	$T_A = +25°C$ Typical	Units
C_{IN}	Input Capacitance	V_{CC} = 1.8V, 2.5V or 3.3V, V_I = 0V or V_{CC}	6	pF
C_{OUT}	Output Capacitance	V_I = 0V or V_{CC}, V_{CC} = 1.8V, 2.5V or 3.3V	7	pF
C_{PD}	Power Dissipation Capacitance	V_I = 0V or V_{CC}, f = 10 MHz, V_{CC} = 1.8V, 2.5V or 3.3V	20	pF

AC Loading and Waveforms (V_{CC} 3.3V ± 0.3V to 1.8V ± 0.15V)



TEST	SWITCH
t_{PLH}, t_{PHL}	Open
t_{PZL}, t_{PLZ}	6V at V_{CC} = 3.3 ± 0.3V; V_{CC} x 2 at V_{CC} = 2.5 ± 0.2V; 1.8V ± 0.15V
t_{PZH}, t_{PHZ}	GND

FIGURE 1. AC Test Circuit



FIGURE 2. Waveform for Inverting and Non-Inverting Functions



FIGURE 3. 3-STATE Output HIGH Enable and Disable Times for Low Voltage Logic



FIGURE 4. 3-STATE Output LOW Enable and Disable Times for Low Voltage Logic



FIGURE 5. Propagation Delay, Pulse Width and t_{REC} Waveforms



FIGURE 6. Setup Time, Hold Time and Recovery Time for Low Voltage Logic

Symbol	V_{CC}		
	3.3V ± 0.3V	**2.5V ± 0.2V**	**1.8V ± 0.15V**
V_{mi}	1.5V	V_{CC}/2	V_{CC}/2
V_{mo}	1.5V	V_{CC}/2	V_{CC}/2
V_X	V_{OL} +0.3V	V_{OL} +0.15V	V_{OL} +0.15V
V_Y	V_{OH} −0.3V	V_{OH} −0.15V	V_{OH} −0.15V

AC Loading and Waveforms (V_{CC} 1.5V ± 0.1V)



TEST	SWITCH
t_{PLH}, t_{PHL}	Open
t_{PZL}, t_{PLZ}	V_{CC} x 2 at V_{CC} = 1.5V ± 0.1V
t_{PZH}, t_{PHZ}	GND

FIGURE 7. AC Test Circuit



FIGURE 8. Waveform for Inverting and Non-Inverting Functions



FIGURE 9. 3-STATE Output HIGH Enable and Disable Times for Low Voltage Logic



FIGURE 10. 3-STATE Output LOW Enable and Disable Times for Low Voltage Logic

Symbol	V_{CC}
	1.5V ± 0.1V
V_{mi}	$V_{CC}/2$
V_{mo}	$V_{CC}/2$
V_X	V_{OL} +0.1V
V_Y	V_{OH} −0.1V

Physical Dimensions inches (millimeters) unless otherwise noted



48-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 6.1mm Wide
Package Number MTD48

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

www.fairchildsemi.com

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Literature Distribution Center for ON Semiconductor
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA
Phone: 303−675−2175 or 800−344−3860 Toll Free USA/Canada
Fax: 303−675−2176 or 800−344−3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800−282−9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81−3−5817−1050

ON Semiconductor Website: **www.onsemi.com**

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative